





- ① MATERIAL:
CONTACT AND SHIELD: PHOS BRONZE
HOUSING AND CHICKLET: LCP, UL 94V-0, COLOR: BLACK
- ② FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS
OF THE PRODUCT SPECIFICATION 108-2303; BASED ON
TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY
LEVEL III, APPLICATIONS IN CONTROLLED
ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
SHIELD 1.27µm MIN NICKEL.
- ③ CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND STANDARD IN
APPROXIMATE AREA SHOWN.
- ④ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- ⑤ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- ⑦ REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED THRU
HOLE DIAMETER AND PLATING THICKNESS.
- ⑧ ALL GROUNDS IN ODD NUMBERED COLUMNS ARE COMMONED.
ALL GROUNDS IN EVEN NUMBERED COLUMNS, EXCEPT FOR ROW A ARE COMMONED.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: <u>W. SOURBEEF</u> 13AUG2007 CHK: <u>W. DAVIS</u> 13AUG2007 APPR: <u>B. PATTERSON</u> 12OCT2007		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME: RIGHT ANGLE HEADER ASSEMBLY, OPEN ENDED, 5 PAIR, 8 COLUMN, Z-PACK TinMan	
		Ø PLC ± PLC ± PLC ± PLC ± ANGLE ±		PRODUCT SPEC APPLICATION SPEC	
MATERIAL: 		FINISH: 		SIZE: A100779 CAGE CODE: C1934349 DRAWING NO: 1934349 RESTRICTED TO:	
		WEIGHT: -		SCALE: 6:1 SHEET 1 OF 1 REV C	
CUSTOMER DRAWING					