

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0440330501](#)
Status: **Obsolete**
Description: 12.30mm (.484") Pitch COMPODRE™ Micro-Fit 3.0™ Header Pod, Surface Mount Compatible, Dual Row, Right Angle, 6 Circuits, 3.18mm (.125") PCB Thickness, Tin (Sn) Plating
Replacement Part Number: NONE

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
TUV	R72081037
UL	E29179

General

Product Family	PCB Headers
Series	44033
Application	Power, Wire-to-Board
Comments	High Temperature Solder Type
Obsolete Date	2005/03/01
Product Name	COMPODRE™
Replacement Part Number	NONE

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Resin	Nylon
Number of Rows	2
Orientation	Right Angle
PC Tail Length	6.70mm (.264")
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	3.20mm (.126")
Packaging Type	Bag
Pitch - Mating Interface	12.30mm (.484")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	5A
Voltage - Maximum	250V

Solder Process Data




image - Reference only **Series**

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[44033Series](#)

Mates With

[43512](#)

Use With

[44041](#) COMPODRE Shroud, [44041](#)

Lead-free Process Capability

Wave Capable (TH only)

Material Info

This document was generated on 02/22/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION