

Radial Lead Type


Series: **KS** Type : **A**

■ **Features** Endurance: 85°C 1000 h
5 mm height

■ Specifications

Category temp. range	-40 to +85°C							
Rated W.V. Range	4 to 50 V .DC							
Nominal Cap. Range	0.1 to 330 μ F							
Capacitance Tolerance	±20 % (120Hz/+20°C)							
DC Leakage Current	$I \leq 0.01 CV$ or $3(\mu A)$ after 2 minutes (Whichever, greater)							
tan δ	Please see the attached standard products list.							
Characteristics at Low Temperature	W.V. (V)	4	6.3	10	16	25	35	50
	Z(-25°C)/Z(+20°C)	7	4	3	2	2	2	2
	Z(-40°C)/Z(+20°C)	15	8	6	4	4	3	3
(Impedance ratio at 120 Hz)								
Endurance	After applying rated working voltage for 1000 hours at +85°C and then being stabilized at +20°C, capacitors shall meet the following limits.							
	Capacitance change	± 20% of initial measured value (4V. : ±30%)						
	tan δ	≤200 % of initial specified value						
	DC leakage current	≤initial specified value						
Shelf Life	After storage for 1000 hours at +85±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance.(With voltage treatment)							

■ Dimensions in mm (not to scale)



Body Dia.φD	3	4	5	6.3	8
Lead Dia.φd	0.4	0.45	0.45	0.45	0.45
Lead Space P	1.0	1.5	2.0	2.5	2.5

■ Standard Products

W.V. (V)	Cap. ($\pm 20\%$) (μF)	Case size		Specification		Lead Length				Part No.	Min. Packaging Qty		
		Dia. (mm)	Length (mm)	Ripple current (120Hz) (+85°C) (mA)	$\tan \delta$ (120Hz) (+20°C)	Lead Dia. (mm)	Lead Space				Straight Leads (pcs)	Taping (pcs)	
							Straight (mm)	Taping *B (mm)	Taping *i (mm)				
4	22	3	5	19	0.35	0.40	1.0	5.0	2.5	ECEA0GKK220()	200	2000	
	33	4	5	26	0.35	0.45	1.5	5.0	2.5	ECEA0GKS330()	200	2000	
	47	4	5	34	0.35	0.45	1.5	5.0	2.5	ECEA0GKS470()	200	2000	
	100	5	5	61	0.35	0.45	2.0	5.0	2.5	ECEA0GKS101()	200	2000	
	220	6.3	5	82	0.35	0.45	2.5	5.0	2.5	ECEA0GKS221()	200	2000	
6.3	22	4	5	29	0.24	0.45	1.5	5.0	2.5	ECEA0JKS220()	200	2000	
	33	5	5	38	0.24	0.45	2.0	5.0	2.5	ECEA0JKS330()	200	2000	
	47	5	5	46	0.24	0.45	2.0	5.0	2.5	ECEA0JKS470()	200	2000	
	100	6.3	5	71	0.24	0.45	2.5	5.0	2.5	ECEA0JKS101()	200	2000	
	330	8	5	130	0.24	0.45	2.5		2.5	ECEA0JKS331()	200	1000	
		8	5	130	0.24	0.45		5.0		ECEA0JKS331Q		1000	
10	22	5	5	35	0.20	0.45	2.0	5.0	2.5	ECEA1AKS220()	200	2000	
	33	5	5	43	0.20	0.45	2.0	5.0	2.5	ECEA1AKS330()	200	2000	
	47	6.3	5	65	0.20	0.45	2.5	5.0	2.5	ECEA1AKS470()	200	2000	
	100	6.3	5	80	0.20	0.45	2.5	5.0	2.5	ECEA1AKS101()	200	2000	
	220	8	5	120	0.20	0.45	2.5		2.5	ECEA1AKS221()	200	1000	
		8	5	120	0.20	0.45		5.0		ECEA1AKS221Q		1000	
16	10	3	5	20									

■ Standard Products

W.V. (V)	Cap. (±20%) (μF)	Case size		Specification		Lead Length				Part No.	Min.PackagingQ' ty		
		Dia. (mm)	Length (mm)	Ripple current (120Hz) (+85°C) (mA)	tan δ (120Hz) (+20°C)	Lead Dia. (mm)	Lead Space				Straight Leads (pcs)	Taping (pcs)	
							Straight (mm)	Taping *B	Taping *i				
50	0.22	3	5	2	0.10	0.40	1.0	5.0	2.5	ECEA1HKKR22()	200	2000	
		4	5	2	0.10	0.45	1.5	5.0	2.5	ECEA1HKSR22()	200	2000	
	0.33	3	5	3	0.10	0.40	1.0	5.0	2.5	ECEA1HKKR33()	200	2000	
		4	5	3	0.10	0.45	1.5	5.0	2.5	ECEA1HKSR33()	200	2000	
	0.47	3	5	5	0.10	0.40	1.0	5.0	2.5	ECEA1HKKR47()	200	2000	
		4	5	5	0.10	0.45	1.5	5.0	2.5	ECEA1HKSR47()	200	2000	
	1	3	5	8	0.10	0.40	1.0	5.0	2.5	ECEA1HKK010()	200	2000	
		4	5	10	0.10	0.45	1.5	5.0	2.5	ECEA1HKS010()	200	2000	
	2.2	4	5	16	0.10	0.45	1.5	5.0	2.5	ECEA1HKS2R2()	200	2000	
	3.3	4	5	16	0.10	0.45	1.5	5.0	2.5	ECEA1HKS3R3()	200	2000	
	4.7	5	5	23	0.10	0.45	2.0	5.0	2.5	ECEA1HKS4R7()	200	2000	
	10	6.3	5	35	0.10	0.45	2.5	5.0	2.5	ECEA1HKS100()	200	2000	
	22	8	5	60	0.10	0.45	2.5		2.5	ECEA1HKS220()	200	1000	
		8	5	60	0.10	0.45		5.0		ECEA1HKS220Q		1000	

When requesting taped product, please put the letter "B" or "i" between the "()". Lead wire pitch B=5mm, i=2.5mm.
The taping dimentions are explained on p.188 of our Catalog. Please use it as a reference guide.
Endurance : 85°C 1000h