






PRODUCT NB	NB OF POS	DIM"A"	DIM"C"	DIM"D"
71993-320	2 X 20	43.18/1.700	48.26/1.900	50.72/1.997
71993-320LF	2 X 20	43.18/1.700	48.26/1.900	50.72/1.997



- NOTES:
- 1 - MATERIAL PCT COLOUR GREY 30% GLASS FILLED HIGH TEMPERATURE. FLAME RETARDANT PER UL-94 CATEGORY V0.
 - 2 - MATERIAL TERMINAL: PHOSPOR BRONZE 3/4 HARD
 - 3 - BURR LOCATED ON TOP OF TAIL - MAXI 0.08 mm
 - 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDS MAX IN A CONVECTION, INFRA-RED OR VAPOR PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-22-008



71993-320LF	0.75µm Au	Sn
71993-320	0.75µm Au	SnPb
PLATING CODE	CONTACT AREA	SOLDER TAIL
PLATING EXPLANATION		

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 416 ISO 1101	projection mm	product family DX HCC D.R.			
ltr	ecn na	dr	date	tolerances unless	otherwise specified	mm	title DUBOX HCC WITH LOCATING PEG			
C	F30974	PNZ	93.12.13	angles	Linear	±0.3	scale 5:1			
D	F50845	PNZ	95.11.15	±2°			FCI			
E	F80158	PNZ	98.03.13				dwg no			
F	F04-0347	DLE	04.11.08	dr	P.NIZZI	95.11.15	sheet 1 of 1			
G	F06-0204	DLE	06.06.20	enr	JM PHAMVAN	95.11.14	size			
				chr	P.NIZZI	95.11.14	71993			
				appd	JMP	95.11.14	A3			
sheet index				revision sheet				type		
								CUSTOMER		
								Drawing		



Copyright FCI