


Capacitor, film, 2200 pF, +/-5% Tol, -55/+105C, General Purpose, 630VDC@85C, Lead Spacing=7.5 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	10	+0.2
H	8	+0.1
T	3	+0.1
S	7.5	+/-0.4
LL	4	+1.5
F	0.5	+/-0.05

Notes:

-L,H,T are nominal dimensions and do not imply a minimum.

General Information	
Supplier:	KEMET

Specifications	
Capacitance:	2200 pF
Rated Temperature:	85C
Voltage @ rated temp:	630VDC
Voltage AC:	250VAC
Tolerance:	+/-5%
Body Type:	Radial Box
Dielectric:	Metallized Polypropylene
Construction:	Double Metallized
Application:	General Purpose
Sub Application:	AEC-Q200
Temperature Range:	-55/+105C
Dissipation Factor @ 1 kHz:	0.1%
Dissipation Factor @ 10 kHz:	0.06%
Dissipation Factor @ 100kHz:	0.1%
Insulation Resistance:	100 GOhm
Inductance:	8 nH
Maximum dVdT:	2800 v/us
Maximum K0:	3528000 V ² /us

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	1500