





LOC		DIST		REVISIONS						
HM		00		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					E	REV PER ECO-12-020239	03DEC2012	JM	MS	

1. DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
2. CABLE ASSEMBLY IS WIRED PER WIRING DIAGRAM.
3. MATERIAL:
- CONNECTOR HOUSINGS- POLYCARBONATE, UL 94V-0 RATED, NEMA GRAY.
- STRAIN RELIEFS- CARBON STEEL WITH NICKEL PLATING 5.08µm [0.000200] MINIMUM THICK.
- CONTACTS- COPPER ALLOY WITH SILVER PLATED STRIP 3.81µm [0.000150] MINIMUM THICK.
4. DIMENSION A SHALL BE MEASURED WITH CONDUIT IN THE RELAXED POSITION.
5. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
6. MANUFACTURING LOCATION, DATE CODE, PART NUMBER AND LENGTH SHALL BE INK STAMPED APPROXIMATELY WHERE INDICATED.
7. APPLICATION: AMPINERGY (TM) - MODULAR POWER DISTRIBUTION SYSTEM, A MANUFACTURED WIRING SYSTEM.
8. CABLE CONNECTOR MATES WITH DEDICATED NEUTRAL (3-3-2) POWER CONNECTOR CABLE ASSEMBLIES. KEYING FEATURE MAINTAINS CORRECT POLARITY OF MATING POWER CONNECTORS.
9. TABS FOR POSITIVE LATCHING TO MATING COMPONENTS.
10. USE GROUND WIRE INSPECTION WINDOW TO VERIFY BONDING AND GROUNDING CONDUCTOR.

304.8 [12]	15240.0-15316.2 [600.00-603.00]	5-1933403-0	15.24 [50.00]
304.8 [12]	12192.0-12268.2 [480.00-483.00]	4-1933403-0	12.19 [40.00]
304.8 [12]	9144.0-9220.2 [360.00-363.00]	3-1933403-0	9.14 [30.00]
304.8 [12]	7620.0-7696.2 [300.00-303.00]	2-1933403-5	7.62 [25.00]
304.8 [12]	6096.0-6146.8 [240.00-242.00]	2-1933403-0	6.10 [20.00]
304.8 [12]	4572.0-4622.8 [180.00-182.00]	1-1933403-5	4.57 [15.00]
304.8 [12]	3048.0-3073.4 [120.00-121.00]	1-1933403-0	3.05 [10.00]
304.8 [12]	1524.0-1543.0 [60.00-60.75]	1933403-5	1.52 [5.00]
304.8 [12]	1219.2-1231.9 [48.00-48.50]	1933403-4	1.22 [4.00]
304.8 [12]	914.4-927.1 [36.00-36.50]	1933403-3	0.91 [3.00]
304.8 [12]	609.6-622.3 [24.00-24.50]	1933403-2	0.61 [2.00]
304.8 [12]	304.8-317.5 [12.00-12.50]	1933403-1	0.30 [1.00]
B DIM	A DIM 4	PART NUMBER	REF DIM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J MCNEAL	08JAN2008	 TE Connectivity				
DIMENSIONS:		CHK	S JONES	08JAN2008					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	S JONES	08JAN2008	NAME CABLE ASSEMBLY, LINE ENTRY 3-3-2				
mm [INCHES]		PRODUCT SPEC		108-1234					
		APPLICATION SPEC		114-6039					
		WEIGHT		-					
		CUSTOMER DRAWING							
		SCALE		1:1					
		SHEET		1					
OF		1							
REV		E							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-1933403-0](#)