

THIS DRAWING IS UNPUBLISHED.
QUESTO DISEGNO NON E' PUBBLICATO.
© COPYRIGHT — By —

RELEASED FOR PUBLICATION
RILASCIATO PER PUBBLICAZIONE
ALL RIGHTS RESERVED.
TODOS LOS DERECHOS RESERVADOS.
TODOS LOS DERECHOS RESERVADOS.



LOC	DIST	REVISIONS REVISIONI			
FT	0	P	LTR REV	DESCRIPTION DESCRIZIONE	DATE DATA
			F	REVISED PER ECO-11-023401	01DEC11
					DWN DISEGNO
					APVD APPROVATO
					KH
					MS

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.
M3 SCREWS: ZINC PLATED STEEL.


ELECTRICAL:
RATED CURRENT: 10A.
OPERATING VOLTAGE: 300V.
WIRE RANGE: 16-30 AWG.

MECHANICAL:
PITCH (TERMINAL SPACING): .250"
OPERATING TEMP.: 120°C MAX.



- 1
- 2
- 3
- 4
- 5
- SEE FIGURE.
- M3 SCREWS BOTTOMED.
- RECOMMENDED PCB HOLE
DIAMETER: .090".
- PRELIMINARY PART NUMBER.
- OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI



1-1546119-4



3-1546099-2




5 1 OBSOLETE

4 1

5 2 OBSOLETE

7.25	30	3PCR-30-006	3-1546099-0
7.00	29	3PCR-29-006	2-1546099-9
6.75	28	3PCR-28-006	2-1546099-8
6.50	27	3PCR-27-006	2-1546099-7
6.25	26	3PCR-26-006	2-1546099-6
6.00	25	3PCR-25-006	2-1546099-5
5.75	24	3PCR-24-006	2-1546099-4
5.50	23	3PCR-23-006	2-1546099-3
5.25	22	3PCR-22-006	2-1546099-2
5.00	21	3PCR-21-006	2-1546099-1
4.75	20	3PCR-20-006	2-1546119-0
4.50	19	3PCR-19-006	1-1546119-9
4.25	18	3PCR-18-006	1-1546099-8
4.00	17	3PCR-17-006	1-1546099-7
3.75	16	3PCR-16-006	1-1546099-6
3.50	15	3PCR-15-006	1-1546099-5
3.25	14	3PCR-14-006	1-1546099-4
3.00	13	3PCR-13-006	1-1546099-3
2.75	12	3PCR-12-006	1-1546119-7
2.50	11	3PCR-11-006	1-1546119-6
2.25	10	3PCR-10-006	1-1546119-5
2.00	9	3PCR-09-256	1-1546119-4
2.00	9	3PCR-09-006	1-1546119-3
1.75	8	3PCR-08-310	3-1546099-2
1.75	8	3PCR-08-006	1-1546119-2
1.50	7	3PCR-07-006	1-1546119-0
1.25	6	3PCR-06-302	3-1546099-1
1.25	6	3PCR-06-006	1-1437646-2
1.00	5	3PCR-05-006	1437646-9
.75	4	3PCR-04-006	1546119-8
.50	3	3PCR-03-006	1546099-1
.25	2	3PCR-02-006	1546119-5

DIM "A"	NO OF POS	CATALOG NUMBER	TE PART NO.
------------	-----------------	-------------------	----------------



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT. QUESTO DISEGNO E' UN DOCUMENTO CONTROLLATO.		DWN/DISEGNO S. SCHLEGEL 4/22/03	TE Connectivity		
USE DIMENSIONS UNLESS OTHERWISE SPECIFIED. USARE DIMENSIONI A MENO DI SPECIFICAZIONE.		CHK/CONTROLLATO S. YODER 6/18/02			
DIMENSIONS: MISURE IN INCHES		APVD/APPROVATO S. YODER 6/18/02	NAME DISEGNO		
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLLERANZE A MENO DI SPECIFICAZIONE: 0 PLC/DWG: ± — 1 PLC/DWG: ± — 2 PLC/DWG: ± .02 3 PLC/DWG: ± .010 4 PLC/DWG: ± — ANGLES/ANGOLI ± —		PRODUCT SPEC SPECIFICAZIONE PRODOTTO —	3PCR-XX-006 ASSEMBLY		
MATERIAL MATERIALE —		FINISH/OBERFLAECHE/FARBE ACABAMENTO —	APPLICATION SPEC SPECIFICAZIONE APPLICAZIONE —		
		WEIGHT PESO APPROX. —	SIZE DIMENSIONE A3	CAGE CODE CODICE CAGE 00779	DRAWING NO DISEGNO -NR. C-1437646-9
		CUSTOMER DRAWING / DISEGNO CLIENTE		SCALE SCALA AS SHOWN	SHEET FOLIO 1 OF 1
				REV F	