








RECOMMEND P.C.B. HOLES



NOTES:

1. ALL DIMENSIONS IN MM
2. TERM. NOS. FOR REF ONLY
3. RATING: DC 120V, 50mA
4. TRAVEL: 0.25±0.1mm
5. CONTACT RESISTANCE: 100m Ohms Max.
6. LIFE: 100,000 CYCLES min
7. INSULATION RESISTANCE: 100M Ohms min
8. DIELECTRIC STRENGTH: 250V RMS min.

7. INSULATION RESISTANCE, 100M Ohms min			
8. DIELECTRIC STRENGTH, 250V RMS min.			
A	RELEASED FOR PRODUCTION		
REV.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TOLERANCES			
0.0		±0.4	
0.00		±0.25	
TITLE			
TL 1105 P F250 Q			
SCALE	DATE	DR	DWG
2:1	4/10/97	MM	P010020
		REV	A

E-SWITCH®

CIRCUIT, SPST
CONTACT CONFIGURATION