




- ▼ Low On-Resistance
- ▼ Fast Switching
- ▼ Simple Drive Requirement





BV_{DSS}	30V
$R_{DS(ON)}$	9mΩ
I_D	70A

Description

The Advanced Power MOSFETs from APEC provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The TO-252 package is universally preferred for all commercial-industrial surface mount applications and suited for low voltage applications such as DC/DC converters.



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	30	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^{\circ}C$	Continuous Drain Current, V_{GS} @ 10V	70	A
$I_D@T_C=100^{\circ}C$	Continuous Drain Current, V_{GS} @ 10V	45	A
I_{DM}	Pulsed Drain Current ¹	275	A
$P_D@T_C=25^{\circ}C$	Total Power Dissipation	69	W
	Linear Derating Factor	0.55	W/°C
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Value	Unit
Rthj-c	Thermal Resistance Junction-case Max.	1.8	°C/W
Rthj-a	Thermal Resistance Junction-ambient Max.	110	°C/W


Electrical Characteristics@T_j=25°C(unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	30	-	-	V
ΔBV _{DSS} /ΔT _j	Breakdown Voltage Temperature Coefficient	Reference to 25°C, I _D =1mA	-	0.035	-	V/°C
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V, I _D =35A	-	8	9	mΩ
		V _{GS} =4.5V, I _D =28A	-	11	14	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250uA	1	-	3	V
g _{fs}	Forward Transconductance	V _{DS} =10V, I _D =35A	-	38	-	S
I _{DSS}	Drain-Source Leakage Current (T _j =25°C)	V _{DS} =30V, V _{GS} =0V	-	-	1	uA
	Drain-Source Leakage Current (T _j =150°C)	V _{DS} =24V, V _{GS} =0V	-	-	25	uA
I _{GSS}	Gate-Source Leakage	V _{GS} = ± 20V	-	-	±100	nA
Q _g	Total Gate Charge ²	I _D =35A	-	30	-	nC
Q _{gs}	Gate-Source Charge	V _{DS} =24V	-	7	-	nC
Q _{gd}	Gate-Drain ("Miller") Charge	V _{GS} =5V	-	15	-	nC
t _{d(on)}	Turn-on Delay Time ²	V _{DS} =15V	-	8	-	ns
t _r	Rise Time	I _D =35A	-	85	-	ns
t _{d(off)}	Turn-off Delay Time	R _G =3.3Ω, V _{GS} =10V	-	30	-	ns
t _f	Fall Time	R _D =0.43Ω	-	45	-	ns
C _{iss}	Input Capacitance	V _{GS} =0V	-	1600	-	pF
C _{oss}	Output Capacitance	V _{DS} =25V	-	700	-	pF
C _{rss}	Reverse Transfer Capacitance	f=1.0MHz	-	280	-	pF

Source-Drain Diode

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
I _S	Continuous Source Current (Body Diode)	V _D =V _G =0V , V _S =1.3V	-	-	70	A
I _{SM}	Pulsed Source Current (Body Diode) ¹		-	-	275	A
V _{SD}	Forward On Voltage ²	T _j =25°C, I _S =70A, V _{GS} =0V	-	-	1.3	V

Notes:

- 1.Pulse width limited by safe operating area.
- 2.Pulse width ≤300us , duty cycle ≤2%.




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. On-Resistance v.s. Gate Voltage




Fig 4. Normalized On-Resistance v.s. Junction Temperature




Fig 5. Maximum Drain Current v.s. Case Temperature




Fig 6. Typical Power Dissipation




Fig 7. Maximum Safe Operating Area








Fig 8. Effective Transient Thermal Impedance






Fig 13. Switching Time Circuit




Fig 14. Switching Time Waveform




Fig 15. Gate Charge Circuit




Fig 16. Gate Charge Waveform