

10

9

8

7

6



5

4





3

2

1



RECOMMENDED P.C.B HOLE LAYOUT



REVISION OF DRAWING MAY BE
CHANGED DURING FINAL RELEASED
FOR PRODUCTION.

ib_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

NOTES:

1. MATERIAL:

HSG: LCP, GLASS-FILLED, UL94V-0,
COLOR: BLACK

PIN: 0.64MM SQ PIN, COPPER ALLOY

2. PLATING TYPE:

- (1) : 0.0254 μ m GOLD FLASH OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (2) : 0.025 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (3) : 0.25 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (4) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (5) : 0.75 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (6) : 2.50 μ m MIN. TIN OVER 1.25 μ m MIN. NICKEL OVERALL.
 - (7) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
2.50 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (8) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
0.05 μ m MIN. GOLD FLASH ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - (9) : 0.05 - 0.25 μ m MIN. GOLD FLASH OVER
1.25 μ m MIN. NICKEL OVERALL.
3. PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION
4. THE ABOVE 14 CKT IS FOR ILLUSTRATION PURPOSE ONLY.
5. FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.
6. RECOMMENDED PCB THICKNESS 1.60MM.
7. PRODUCT SPECIFICATION: PS-87920-019
8. WAFER TO BE FLAT WITHIN 0.003mm/mm
9. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION
IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN
BODY IS NOT ACCEPTABLE.
10. PARTS ARE NOT STACKABLE ON 2.54 CENTER
11. CAP TO BE PLACED AS CENTRAL OF PART AS POSSIBLE
WITH THE TOP SURFACE FLAT FOR PICK AND PLACE.
12. PACKAGING SPECIFICATION:
TRAY: PK-89990-489
BULK: PK-89990-491

SEE SHEET 14
EC NO: S2015-1512
DRAWN: RAKRISHNA 2015/06/25
CHKD: ATSEE 2015/06/25
APPR: KPRASAD 2015/07/15

DESCRIPTION
REV

QUALITY
SYMBOLS

$F_A=0$

$F_G=0$

$F_P=0$

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± ---	± ---
0 PLACE	±	±

ANGULAR $\pm 3^\circ$
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
KCHO	2004/11/05
CHECKED BY	DATE
PTLIM	2004/12/08
APPROVED BY	DATE
MLONG	2010/09/06

MATERIAL NO.
SEE TABLE

SIZE
A3

SCALE
NTS

TITLE

DOCUMENT NO.

DESIGN UNITS
METRIC

2.54MM PITCH
DUAL ROW HEADER
SINGLE WAFER, T/H
molex

SD-87914-013

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

A

	10		9	8	7		6		5		4		3		2		1				
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
									A	B	F	M	P								
F	87914-0211	-----	-----	-----	-----	2	-----	1	2.54	----	10.92	5.84	2.79					F			
	87914-0221	-----	-----	-----	-----	2	-----	1	2.54	----	12.25	7.00	2.96								
	87914-0231	-----	-----	-----	-----	2	-----	1	2.54	----	13.38	6.09	5.00								
	87914-0212	-----	-----	-----	-----	2	-----	2	2.54	----	10.92	5.84	2.79								
	87914-0222	-----	-----	-----	-----	2	-----	2	2.54	----	12.25	7.00	2.96								
	87914-0232	-----	-----	-----	-----	2	-----	2	2.54	----	13.38	6.09	5.00								
E	87914-0213	-----	-----	-----	-----	2	-----	3	2.54	----	10.92	5.84	2.79					E			
	87914-0223	-----	-----	-----	-----	2	-----	3	2.54	----	12.25	7.00	2.96								
	87914-0233	-----	-----	-----	-----	2	-----	3	2.54	----	13.38	6.09	5.00								
	87914-0214	-----	-----	-----	-----	2	-----	4	2.54	----	10.92	5.84	2.79								
	87914-0224	-----	-----	-----	-----	2	-----	4	2.54	----	12.25	7.00	2.96								
	87914-0234	-----	-----	-----	-----	2	-----	4	2.54	----	13.38	6.09	5.00								
D	87914-0215	-----	-----	-----	-----	2	-----	5	2.54	----	10.92	5.84	2.79					D			
	87914-0225	-----	-----	-----	-----	2	-----	5	2.54	----	12.25	7.00	2.96								
	87914-0235	-----	-----	-----	-----	2	-----	5	2.54	----	13.38	6.09	5.00								
	87914-0216	-----	-----	-----	-----	2	-----	6	2.54	----	10.92	5.84	2.79								
	87914-0226	-----	-----	-----	-----	2	-----	6	2.54	----	12.25	7.00	2.96								
	87914-0236	-----	-----	-----	-----	2	-----	6	2.54	----	13.38	6.09	5.00								
C																		C			
B																		B			
A							SEE SHEET 14 IEC NO: S2015-1512 DRAWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION					
									4 PLACES	± ---	± ---	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex							
									3 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08								
									2 PLACES	± 0.20	± ---	APPROVED BY MLONG	DATE 2010/09/06								
									1 PLACE	± ---	± ---	MATERIAL NO.	DOCUMENT NO.					SHEET NO.			
									0 PLACE	±	±	SEE TABLE		SD-87914-013		2 OF 45					
									ANGULAR ± 3 °												
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								
	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6			5	4	3	2	1								

	10		9		8		7		6		5		4		3		2		1									
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																			
									A	B	F	M	P															
F	87914-0411	-----	-----	-----	-----	4	-----	1	5.08	2.54	10.92	5.84	2.79								F							
	87914-0421	-----	-----	-----	-----	4	-----	1	5.08	2.54	12.25	7.00	2.96															
	87914-0431	-----	-----	-----	-----	4	-----	1	5.08	2.54	13.38	6.09	5.00															
	87914-0412	-----	-----	-----	-----	4	-----	2	5.08	2.54	10.92	5.84	2.79															
	87914-0422	-----	-----	-----	-----	4	-----	2	5.08	2.54	12.25	7.00	2.96															
	87914-0432	-----	-----	-----	-----	4	-----	2	5.08	2.54	13.38	6.09	5.00															
E	87914-0413	-----	-----	-----	-----	4	-----	3	5.08	2.54	10.92	5.84	2.79								E							
	87914-0423	-----	-----	-----	-----	4	-----	3	5.08	2.54	12.25	7.00	2.96															
	87914-0433	-----	-----	-----	-----	4	-----	3	5.08	2.54	13.38	6.09	5.00															
	87914-0414	-----	-----	-----	-----	4	-----	4	5.08	2.54	10.92	5.84	2.79															
	87914-0424	-----	-----	-----	-----	4	-----	4	5.08	2.54	12.25	7.00	2.96															
	87914-0434	-----	-----	-----	-----	4	-----	4	5.08	2.54	13.38	6.09	5.00															
D	87914-0415	-----	-----	-----	-----	4	-----	5	5.08	2.54	10.92	5.84	2.79								D							
	87914-0425	-----	-----	-----	-----	4	-----	5	5.08	2.54	12.25	7.00	2.96															
	87914-0435	-----	-----	-----	-----	4	-----	5	5.08	2.54	13.38	6.09	5.00															
	87914-0416	-----	-----	-----	-----	4	-----	6	5.08	2.54	10.92	5.84	2.79															
	87914-0426	-----	-----	-----	-----	4	-----	6	5.08	2.54	12.25	7.00	2.96															
	87914-0436	-----	-----	-----	-----	4	-----	6	5.08	2.54	13.38	6.09	5.00															
C																					C							
B																					B							
A	SEE SHEET 14 EC NO: S2015-1512 DRWN:IRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 DESCRIPTION REV D15								QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		molex		DOCUMENT NO. SD-87914-013		SHEET NO. 3 OF 45	
									▽_A=0 ▽_G=0 ▽_P=0				MM ONLY		NTS		METRIC											
									4 PLACES		± ---	± ---	DRAWN BY DATE		TITLE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		molex		DOCUMENT NO. SD-87914-013		SHEET NO. 3 OF 45					
									3 PLACES		± ---	± ---	KCHO 2004/11/05															
									2 PLACES		± 0.20	± ---	CHECKED BY DATE															
									1 PLACE		± ---	± ---	PTLIM 2004/12/08		APPROVED BY DATE													
									0 PLACE		±	±	MLONG 2010/09/06		MATERIAL NO.													
									ANGULAR ± 3 °																			
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SEE TABLE													
									SIZE A3																			

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

	9	8	7	6	5	4	3	2	1	
--	---	---	---	---	---	---	---	---	---	--

[illegible]

[illegible]

[illegible]

	10		9		8		7		6		5		4		3		2		1		
F	PART NO. FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F							
									A	B	F	M	P								
	87914-0841	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.51	8.75	2.47								
	87914-0842	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.51	8.75	2.47								
	87914-0843	-----	-----	-----	-----	8	-----	3	10.16	7.62	13.51	8.75	2.47								
	87914-0844	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.51	8.75	2.47								
E	87914-0845	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.51	8.75	2.47	E							
	87914-0005	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.51	8.75	2.47								
	87914-0108	-----	-----	-----	-----	8	-----	6	10.16	7.62	16.50	11.11	3.10								
	87914-0847	-----	-----	-----	-----	8	-----	6	10.16	7.62	26.70	20.76	3.65								
D														D							
C														C							
B														B							
A														A							
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1											
SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV		QUALITY SYMBOLS $F_A=0$ $F_C=0$ $F_P=0$		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES $\pm$ --- $\pm$ --- 3 PLACES $\pm$ --- $\pm$ --- 2 PLACES $\pm$ 0.20 $\pm$ --- 1 PLACE $\pm$ --- $\pm$ --- 0 PLACE $\pm$ $\pm$ ANGULAR $\pm$ 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		DOCUMENT NO. SD-87914-013		SHEET NO. 7 OF 45		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

ib_frame_A3_P_AM_T

Rev. G 2012/01/11

	10		9		8		7		6		5		4		3		2		1		
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	PART NO. FOR BULK PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
										A	B	F	M	P	G						
F	87914-1011	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	10.92	5.84	2.79	----						
	87914-1021	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	12.25	7.00	2.96	----						
	87914-1031	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	13.38	6.09	5.00	----						
	87914-1012	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	10.92	5.84	2.79	----						
	87914-1022	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	12.25	7.00	2.96	----						
	87914-1032	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	13.38	6.09	5.00	----						
E	87914-1013	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	10.92	5.84	2.79	----						
	87914-1023	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	12.25	7.00	2.96	----						
	87914-1033	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	13.38	6.09	5.00	----						
	87914-1014	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	10.92	5.84	2.79	----						
	87914-1024	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	12.25	7.00	2.96	----						
	87914-1034	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	13.38	6.09	5.00	----						
D	87914-1015	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	10.92	5.84	2.79	----						
	87914-1025	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	12.25	7.00	2.96	----						
	87914-1035	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	13.38	6.09	5.00	----						
	87914-1016	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	10.92	5.84	2.79	----						
	87914-1026	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	12.25	7.00	2.96	----						
	87914-1036	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	13.38	6.09	5.00	----						
C	87914-0001	-----	-----	-----	-----	-----	10	-----	7	12.70	10.16	12.07	5.97	3.81	----						
	-----	-----	-----	-----	-----	87914-1037	10	9	4	12.70	10.16	10.92	5.84	2.79	----						
B																					

A	SEE SHEET 14 EC NO: S2015-1512 DRAWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_B=0 F_C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex	DOCUMENT NO. SD-87914-013	SHEET NO. 8 OF 45	A								
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
				ANGULAR ± 3 °		MATERIAL NO.																
				0 PLACE ±		±		APPROVED BY MLONG							DATE 2010/09/06							
				2 PLACES ± 0.20		± ---		PTLIM							DATE 2004/12/08							
3 PLACES ± ---		± ---		CHECKED BY		DATE																
4 PLACES ± ---		± ---		KCHO		DATE 2004/11/05																
mm		INCH																				
fb_frame_A3_P_AM_T Rev. G 2012/01/11																						
9		8		7		6		5		4		3		2		1						

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-1211	-----	-----	-----	-----	12	-----	1	15.24	12.70	10.92	5.84	2.79						
	-----	87914-1291	-----	-----	-----	12	-----	9	15.24	12.70	10.92	5.84	2.79						
	87914-1221	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.25	7.00	2.96						
	87914-1231	-----	-----	-----	-----	12	-----	1	15.24	12.70	13.38	6.09	5.00						
	87914-1212	-----	-----	-----	-----	12	-----	2	15.24	12.70	10.92	5.84	2.79						
E	87914-1222	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.25	7.00	2.96						
	87914-1232	-----	-----	-----	-----	12	-----	2	15.24	12.70	13.38	6.09	5.00						
	87914-1213	-----	-----	-----	-----	12	-----	3	15.24	12.70	10.92	5.84	2.79						
	87914-1223	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.25	7.00	2.96						
	87914-1233	-----	-----	-----	-----	12	-----	3	15.24	12.70	13.38	6.09	5.00						
D	87914-1214	-----	-----	-----	-----	12	-----	4	15.24	12.70	10.92	5.84	2.79						
	87914-1224	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.25	7.00	2.96						
	87914-1234	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.38	6.09	5.00						
	87914-1215	-----	-----	-----	-----	12	-----	5	15.24	12.70	10.92	5.84	2.79						
	87914-1225	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.25	7.00	2.96						
C	87914-1235	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.38	6.09	5.00						
	87914-1216	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79						
	87914-1226	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96						
	87914-1236	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.38	6.09	5.00						
B																			
A																			

SEE SHEET 14 EC NO: S2015-1512 DRAWN:RAVAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		  	4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.20 ± --- ±	INCH ± --- ± --- ± --- ±	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		
						CHECKED BY PTLIM	DATE 2004/12/08			
						APPROVED BY MLONG	DATE 2010/09/06			
						MATERIAL NO.				
						DOCUMENT NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 9 OF 45			

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1							
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																	
								A	B	F	M	P													
F	87914-1251	-----	-----	-----	-----	12	-----	1	15.24	12.70	18.40	13.08	3.03												
	87914-1252	-----	-----	-----	-----	12	-----	2	15.24	12.70	18.40	13.08	3.03												
	87914-1253	-----	-----	-----	-----	12	-----	3	15.24	12.70	18.40	13.08	3.03												
	87914-1254	-----	-----	-----	-----	12	-----	4	15.24	12.70	18.40	13.08	3.03												
	87914-1255	-----	-----	-----	-----	12	-----	5	15.24	12.70	18.40	13.08	3.03												
	87914-1256	-----	-----	-----	-----	12	-----	6	15.24	12.70	18.40	13.08	3.03												
E	87914-1241	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.50	6.95	3.26												
	87914-1242	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.50	6.95	3.26												
	87914-1243	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.50	6.95	3.26												
	87914-1244	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.50	6.95	3.26												
	87914-1245	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.50	6.95	3.26												
	87914-1246	-----	-----	-----	-----	12	-----	6	15.24	12.70	29.26	23.32	3.65												
D																									
C																									
B																									
A																									
SEE SHEET 14		EC NO: S2015-1512		DRAWN: MRAKRI / SHINA 2015/06/25		CHKD: ATSEE 2015/06/25		APPR: KPRASAD 2015/07/15		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
D15																		MM ONLY		NTS		METRIC		⊙	
																		DRAWN BY		DATE		TITLE			
																		KCHO		2004/11/05		2.54MM PITCH			
																		CHECKED BY		DATE		DUAL ROW HEADER			
																		PTL IM		2004/12/08		SINGLE WAFER, T/H			
																		APPROVED BY		DATE		molex			
																		MLONG		2010/09/06					
																		MATERIAL NO.		DOCUMENT NO.		SD-87914-013		SHEET NO.	
																		SEE TABLE				10 OF 45			
																		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
A3																									

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-1411	-----	-----	-----	-----	14	-----	1	17.78	15.24	10.92	5.84	2.79						
	87914-1421	-----	-----	-----	-----	14	-----	1	17.78	15.24	12.25	7.00	2.96						
	87914-1431	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.38	6.09	5.00						
	87914-1412	-----	-----	-----	-----	14	-----	2	17.78	15.24	10.92	5.84	2.79						
	87914-1422	-----	-----	-----	-----	14	-----	2	17.78	15.24	12.25	7.00	2.96						
E	87914-1432	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.38	6.09	5.00						
	87914-1413	-----	-----	-----	-----	14	-----	3	17.78	15.24	10.92	5.84	2.79						
	87914-1423	-----	-----	-----	-----	14	-----	3	17.78	15.24	12.25	7.00	2.96						
	87914-1433	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.38	6.09	5.00						
	87914-1414	-----	-----	-----	-----	14	-----	4	17.78	15.24	10.92	5.84	2.79						
D	87914-1424	-----	-----	-----	-----	14	-----	4	17.78	15.24	12.25	7.00	2.96						
	87914-1434	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.38	6.09	5.00						
	87914-1415	-----	-----	-----	-----	14	-----	5	17.78	15.24	10.92	5.84	2.79						
	87914-1425	-----	-----	-----	-----	14	-----	5	17.78	15.24	12.25	7.00	2.96						
	87914-1435	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.38	6.09	5.00						
C	87914-1416	-----	-----	-----	-----	14	-----	6	17.78	15.24	10.92	5.84	2.79						
	87914-1426	-----	-----	-----	-----	14	-----	6	17.78	15.24	12.25	7.00	2.96						
	87914-1436	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.38	6.09	5.00						
	87914-0007	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.42	8.08	3.05						

										10					9					8					7					6					5					4					3					2					1																																							
										PART NO. FOR TRAY PACKAGING					PART NO. FOR TUBE WITHOUT CAP PACKAGING					PART NO. FOR TUBE WITH CAP PACKAGING					PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING					PART NO. FOR TAPE & REEL WITH CAP PACKAGING					CKT SIZE					VOID POSITION					PLATING TYPE					DIMENSION																																												
																																																		A		B		F		M		P																																				
F										87914-1441					-----					-----					-----					-----					14					-----					1					17.78		15.24		13.42		8.08		3.05		F																																		
										87914-1442					-----					-----					-----					-----					14					-----					2					17.78		15.24		13.42		8.08		3.05																																				
										87914-1443					-----					-----					-----					-----					14					-----					3					17.78		15.24		13.42		8.08		3.05																																				
										87914-1444					-----					-----					-----					-----					14					-----					4					17.78		15.24		13.42		8.08		3.05																																				
										87914-1445					-----					-----					-----					-----					14					-----					5					17.78		15.24		13.42		8.08		3.05																																				
E																																																																																E														
D																																																																																					D									
C																																																																																					C									

	10	9	8	7	6	5	4	3	2	1				
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F
									A	B	F	M	P	
	87914-1611	-----	-----	-----	-----	16	-----	1	20.32	17.78	10.92	5.84	2.79	
	87914-1621	-----	-----	-----	-----	16	-----	1	20.32	17.78	12.25	7.00	2.96	
	87914-1631	-----	-----	-----	-----	16	-----	1	20.32	17.78	13.38	6.09	5.00	
	87914-1612	-----	-----	-----	-----	16	-----	2	20.32	17.78	10.92	5.84	2.79	
	87914-1622	-----	-----	-----	-----	16	-----	2	20.32	17.78	12.25	7.00	2.96	
	87914-1632	-----	-----	-----	-----	16	-----	2	20.32	17.78	13.38	6.09	5.00	
E	87914-1613	-----	-----	-----	-----	16	-----	3	20.32	17.78	10.92	5.84	2.79	E
	87914-1623	-----	-----	-----	-----	16	-----	3	20.32	17.78	12.25	7.00	2.96	
	87914-1633	-----	-----	-----	-----	16	-----	3	20.32	17.78	13.38	6.09	5.00	
	87914-1614	-----	-----	-----	-----	16	-----	4	20.32	17.78	10.92	5.84	2.79	
	87914-1624	-----	-----	-----	-----	16	-----	4	20.32	17.78	12.25	7.00	2.96	
	87914-1634	-----	-----	-----	-----	16	-----	4	20.32	17.78	13.38	6.09	5.00	
D	87914-1615	-----	-----	-----	-----	16	-----	5	20.32	17.78	10.92	5.84	2.79	D
	87914-1625	-----	-----	-----	-----	16	-----	5	20.32	17.78	12.25	7.00	2.96	
	87914-1635	-----	-----	-----	-----	16	-----	5	20.32	17.78	13.38	6.09	5.00	
	87914-1616	-----	-----	-----	-----	16	-----	6	20.32	17.78	10.92	5.84	2.79	
	87914-1626	-----	-----	-----	-----	16	-----	6	20.32	17.78	12.25	7.00	2.96	
	87914-1636	-----	-----	-----	-----	16	-----	6	20.32	17.78	13.38	6.09	5.00	
C	87914-1600	-----	-----	-----	-----	16	-----	6	20.32	17.78	9.49	4.50	2.70	C
	87914-1637	-----	-----	-----	-----	16	-----	6	20.32	17.78	15.79	10.45	3.05	
B														B
													</	

10			9		8		7		6		5		4		3		2		1			
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION														
								A	B	F	M	P	G									
F	87914-1811	-----	-----	-----	-----	18	-----	1	22.86	20.32	10.92	5.84	2.79	----								
	87914-1821	-----	-----	-----	-----	18	-----	1	22.86	20.32	12.25	7.00	2.96	----								
	87914-1831	-----	-----	-----	-----	18	-----	1	22.86	20.32	13.38	6.09	5.00	----								
	87914-1812	-----	-----	-----	-----	18	-----	2	22.86	20.32	10.92	5.84	2.79	----								
	87914-1822	-----	-----	-----	-----	18	-----	2	22.86	20.32	12.25	7.00	2.96	----								
87914-1832	-----	-----	-----	-----	18	-----	2	22.86	20.32	13.38	6.09	5.00	----	E								
87914-1813	-----	-----	-----	-----	18	-----	3	22.86	20.32	10.92	5.84	2.79	----									
87914-1823	-----	-----	-----	-----	18	-----	3	22.86	20.32	12.25	7.00	2.96	----									
87914-1833	-----	-----	-----	-----	18	-----	3	22.86	20.32	13.38	6.09	5.00	----	D								
87914-1814	-----	-----	-----	-----	18	-----	4	22.86	20.32	10.92	5.84	2.79	----									
87914-1824	-----	-----	-----	-----	18	-----	4	22.86	20.32	12.25	7.00	2.96	----									
87914-1834	-----	-----	-----	-----	18	-----	4	22.86	20.32	13.38	6.09	5.00	----									
87914-1815	-----	-----	-----	-----	18	-----	5	22.86	20.32	10.92	5.84	2.79	----									
87914-1825	-----	-----	-----	-----	18	-----	5	22.86	20.32	12.25	7.00	2.96	----	C								
87914-1835	-----	-----	-----	-----	18	-----	5	22.86	20.32	13.38	6.09	5.00	----									
87914-1816	-----	-----	-----	-----	18	-----	6	22.86	20.32	10.92	5.84	2.79	----									
87914-1826	-----	-----	-----	-----	18	-----	6	22.86	20.32	12.25	7.00	2.96	----									
87914-1836	-----	-----	-----	-----	18	-----	6	22.86	20.32	13.38	6.09	5.00	----									
-----	-----	87914-1807	-----	-----	18	-----	6	22.86	20.32	17.02	11.05	3.68	18.02	B								
B															A							
ADD P/N: 87914-1807 EC NO: S2015-1512 DRAWN:MRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15									QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO. SD-87914-013		SHEET NO. 14 OF 45							

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

[illegible]

	10		9		8		7		6		5		4		3		2		1					
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION															
									A	B	F	M	P											
F	87914-2211	-----	-----	-----	-----	22	-----	1	27.94	25.40	10.92	5.84	2.79								F			
	87914-2221	-----	-----	-----	-----	22	-----	1	27.94	25.40	12.25	7.00	2.96											
	87914-2231	-----	-----	-----	-----	22	-----	1	27.94	25.40	13.38	6.09	5.00											
	87914-2212	-----	-----	-----	-----	22	-----	2	27.94	25.40	10.92	5.84	2.79											
	87914-2222	-----	-----	-----	-----	22	-----	2	27.94	25.40	12.25	7.00	2.96											
	87914-2232	-----	-----	-----	-----	22	-----	2	27.94	25.40	13.38	6.09	5.00											
E	87914-2213	-----	-----	-----	-----	22	-----	3	27.94	25.40	10.92	5.84	2.79								E			
	87914-2223	-----	-----	-----	-----	22	-----	3	27.94	25.40	12.25	7.00	2.96											
	87914-2233	-----	-----	-----	-----	22	-----	3	27.94	25.40	13.38	6.09	5.00											
	87914-2214	-----	-----	-----	-----	22	-----	4	27.94	25.40	10.92	5.84	2.79											
	87914-2224	-----	-----	-----	-----	22	-----	4	27.94	25.40	12.25	7.00	2.96											
	87914-2234	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.38	6.09	5.00											
D	87914-2215	-----	-----	-----	-----	22	-----	5	27.94	25.40	10.92	5.84	2.79								D			
	87914-2225	-----	-----	-----	-----	22	-----	5	27.94	25.40	12.25	7.00	2.96											
	87914-2235	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.38	6.09	5.00											
	87914-2216	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79											
	87914-2226	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96											
	87914-2236	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.38	6.09	5.00											
C																					C			
B																					B			
A									SEE SHEET 14 IEC NO: S2015-1512 DRAWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15		QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION			
									D15				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1						

10			9		8		7		6		5		4		3		2		1					
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																
								A	B	F	M	P												
F	87914-2411	-----	-----	-----	-----	24	-----	1	30.48	27.94	10.92	5.84	2.79											
	87914-2421	-----	-----	-----	-----	24	-----	1	30.48	27.94	12.25	7.00	2.96											
	87914-2431	-----	-----	-----	-----	24	-----	1	30.48	27.94	13.38	6.09	5.00											
	87914-2412	-----	-----	-----	-----	24	-----	2	30.48	27.94	10.92	5.84	2.79											
	87914-2422	-----	-----	-----	-----	24	-----	2	30.48	27.94	12.25	7.00	2.96											
	87914-2432	-----	-----	-----	-----	24	-----	2	30.48	27.94	13.38	6.09	5.00											
E	87914-2413	-----	-----	-----	-----	24	-----	3	30.48	27.94	10.92	5.84	2.79											
	87914-2423	-----	-----	-----	-----	24	-----	3	30.48	27.94	12.25	7.00	2.96											
	87914-2433	-----	-----	-----	-----	24	-----	3	30.48	27.94	13.38	6.09	5.00											
	87914-2414	-----	-----	-----	-----	24	-----	4	30.48	27.94	10.92	5.84	2.79											
	87914-2424	-----	-----	-----	-----	24	-----	4	30.48	27.94	12.25	7.00	2.96											
	87914-2434	-----	-----	-----	-----	24	-----	4	30.48	27.94	13.38	6.09	5.00											
D	87914-2415	-----	-----	-----	-----	24	-----	5	30.48	27.94	10.92	5.84	2.79											
	87914-2425	-----	-----	-----	-----	24	-----	5	30.48	27.94	12.25	7.00	2.96											
	87914-2435	-----	-----	-----	-----	24	-----	5	30.48	27.94	13.38	6.09	5.00											
	87914-2416	-----	-----	-----	-----	24	-----	6	30.48	27.94	10.92	5.84	2.79											
	87914-2426	-----	-----	-----	-----	24	-----	6	30.48	27.94	12.25	7.00	2.96											
	87914-2436	-----	-----	-----	-----	24	-----	6	30.48	27.94	13.38	6.09	5.00											
C																								
B																								
A	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV DESCRIPTION							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °			DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-87914-013	SHEET NO. 17 OF 45
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
	fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1					

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-2611	-----	-----	-----	-----	26	-----	1	33.02	30.48	10.92	5.84	2.79						
	87914-2621	-----	-----	-----	-----	26	-----	1	33.02	30.48	12.25	7.00	2.96						
	87914-2631	-----	-----	-----	-----	26	-----	1	33.02	30.48	13.38	6.09	5.00						
	87914-2612	-----	-----	-----	-----	26	-----	2	33.02	30.48	10.92	5.84	2.79						
	87914-2622	-----	-----	-----	-----	26	-----	2	33.02	30.48	12.25	7.00	2.96						
	87914-2632	-----	-----	-----	-----	26	-----	2	33.02	30.48	13.38	6.09	5.00						
E	87914-2613	-----	-----	-----	-----	26	-----	3	33.02	30.48	10.92	5.84	2.79	E					
	87914-2623	-----	-----	-----	-----	26	-----	3	33.02	30.48	12.25	7.00	2.96						
	87914-2633	-----	-----	-----	-----	26	-----	3	33.02	30.48	13.38	6.09	5.00						
	87914-2614	-----	-----	-----	-----	26	-----	4	33.02	30.48	10.92	5.84	2.79						
	87914-2624	-----	-----	-----	-----	26	-----	4	33.02	30.48	12.25	7.00	2.96						
	87914-2634	-----	-----	-----	-----	26	-----	4	33.02	30.48	13.38	6.09	5.00						
D	87914-2615	-----	-----	-----	-----	26	-----	5	33.02	30.48	10.92	5.84	2.79	D					
	87914-2625	-----	-----	-----	-----	26	-----	5	33.02	30.48	12.25	7.00	2.96						
	87914-2635	-----	-----	-----	-----	26	-----	5	33.02	30.48	13.38	6.09	5.00						
	87914-2616	-----	-----	-----	-----	26	-----	6	33.02	30.48	10.92	5.84	2.79						
	87914-2626	-----	-----	-----	-----	26	-----	6	33.02	30.48	12.25	7.00	2.96						
	87914-2636	-----	-----	-----	-----	26	-----	6	33.02	30.48	13.38	6.09	5.00						
C														C					
B														B					

	10		9		8		7		6		5		4		3		2		1																	
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																											
									A	B	F	M	P																							
F	87914-3011	-----	-----	-----	-----	30	-----	1	38.10	35.56	10.92	5.84	2.79							F																
	87914-3021	-----	-----	-----	-----	30	-----	1	38.10	35.56	12.25	7.00	2.96																							
	87914-3031	-----	-----	-----	-----	30	-----	1	38.10	35.56	13.38	6.09	5.00																							
	87914-3012	-----	-----	-----	-----	30	-----	2	38.10	35.56	10.92	5.84	2.79																							
	87914-3022	-----	-----	-----	-----	30	-----	2	38.10	35.56	12.25	7.00	2.96																							
	87914-3032	-----	-----	-----	-----	30	-----	2	38.10	35.56	13.38	6.09	5.00																							
E	87914-3013	-----	-----	-----	-----	30	-----	3	38.10	35.56	10.92	5.84	2.79							E																
	87914-3023	-----	-----	-----	-----	30	-----	3	38.10	35.56	12.25	7.00	2.96																							
	87914-3033	-----	-----	-----	-----	30	-----	3	38.10	35.56	13.38	6.09	5.00																							
	87914-3014	-----	-----	-----	-----	30	-----	4	38.10	35.56	10.92	5.84	2.79																							
	87914-3024	-----	-----	-----	-----	30	-----	4	38.10	35.56	12.25	7.00	2.96																							
	87914-3034	-----	-----	-----	-----	30	-----	4	38.10	35.56	13.38	6.09	5.00																							
D	87914-3015	-----	-----	-----	-----	30	-----	5	38.10	35.56	10.92	5.84	2.79							D																
	87914-3025	-----	-----	-----	-----	30	-----	5	38.10	35.56	12.25	7.00	2.96																							
	87914-3035	-----	-----	-----	-----	30	-----	5	38.10	35.56	13.38	6.09	5.00																							
	87914-3016	-----	-----	-----	-----	30	-----	6	38.10	35.56	10.92	5.84	2.79																							
	87914-3026	-----	-----	-----	-----	30	-----	6	38.10	35.56	12.25	7.00	2.96																							
	87914-3036	-----	-----	-----	-----	30	-----	6	38.10	35.56	13.38	6.09	5.00																							
C																				C																
B																				B																
A									SEE SHEET 14		IEC NO: S2015-1512		DRW:KPRASAD		CHKD:ATSEE		APPR:KPRASAD		REV		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION					
									D15		DESCRIPTION		F=0		F=0		F=0						4 PLACES		mm		INCH		DRAWN BY		DATE		TITLE		2.54MM PITCH	
													F=0		F=0		F=0						3 PLACES						CHECKED BY		DATE		DUAL ROW HEADER			
													F=0		F=0		F=0						2 PLACES		±0.20		±---		PTLIM		2004/12/08		SINGLE WAFER, T/H			
													F=0		F=0		F=0						1 PLACE		±---		±---		APPROVED BY		DATE		molex			
													F=0		F=0		F=0						0 PLACE		±		±		MLONG		2010/09/06					
																											ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.		SD-87914-013		SHEET NO.	
																											DRAFT WHERE APPLICABLE		SEE TABLE						20 OF 45	
																											SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX						INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
																											A3									
fb_frame_A3_P_AM_T		9		8		7		6		5		4		3		2		1																		

										10			9			8			7			6			5			4			3			2			1
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																												
									A	B	F	M	P																								
F	87914-3211	-----	-----	-----	-----	32	-----	1	40.64	38.10	10.92	5.84	2.79																								
	87914-3221	-----	-----	-----	-----	32	-----	1	40.64	38.10	12.25	7.00	2.96																								
	87914-3231	-----	-----	-----	-----	32	-----	1	40.64	38.10	13.38	6.09	5.00																								
E	87914-3212	-----	-----	-----	-----	32	-----	2	40.64	38.10	10.92	5.84	2.79																								
	87914-3222	-----	-----	-----	-----	32	-----	2	40.64	38.10	12.25	7.00	2.96																								
	87914-3232	-----	-----	-----	-----	32	-----	2	40.64	38.10	13.38	6.09	5.00																								
D	87914-3213	-----	-----	-----	-----	32	-----	3	40.64	38.10	10.92	5.84	2.79																								
	87914-3223	-----	-----	-----	-----	32	-----	3	40.64	38.10	12.25	7.00	2.96																								
	87914-3233	-----	-----	-----	-----	32	-----	3	40.64	38.10	13.38	6.09	5.00																								
C	87914-3214	-----	-----	-----	-----	32	-----	4	40.64	38.10	10.92	5.84	2.79																								
	87914-3224	-----	-----	-----	-----	32	-----	4	40.64	38.10	12.25	7.00	2.96																								
	87914-3234	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.38	6.09	5.00																								
B	87914-3215	-----	-----	-----	-----	32	-----	5	40.64	38.10	10.92	5.84	2.79																								
	87914-3225	-----	-----	-----	-----	32	-----	5	40.64	38.10	12.25	7.00	2.96																								
	87914-3235	-----	-----	-----	-----	32	-----	5	40.64	38.10	13.38	6.09	5.00																								
A	87914-3216	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79																								
	87914-3226	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96																								
	87914-3236	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.38	6.09	5.00																								
</																																					

	10		9	8	7	6	5	4	3	2	1																																																													
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																															
									A	B	F	M	D																																																											
F	87914-3411	-----	-----	-----	-----	34	-----	1	43.18	40.64	10.92	5.84	2.79	F																																																										
	87914-3421	-----	-----	-----	-----	34	-----	1	43.18	40.64	12.25	7.00	2.96																																																											
	87914-3431	-----	-----	-----	-----	34	-----	1	43.18	40.64	13.38	6.09	5.00																																																											
	87914-3412	-----	-----	-----	-----	34	-----	2	43.18	40.64	10.92	5.84	2.79																																																											
	87914-3422	-----	-----	-----	-----	34	-----	2	43.18	40.64	12.25	7.00	2.96																																																											
	87914-3432	-----	-----	-----	-----	34	-----	2	43.18	40.64	13.38	6.09	5.00																																																											
E	87914-3413	-----	-----	-----	-----	34	-----	3	43.18	40.64	10.92	5.84	2.79	E																																																										
	87914-3423	-----	-----	-----	-----	34	-----	3	43.18	40.64	12.25	7.00	2.96																																																											
	87914-3433	-----	-----	-----	-----	34	-----	3	43.18	40.64	13.38	6.09	5.00																																																											
	87914-3414	-----	-----	-----	-----	34	-----	4	43.18	40.64	10.92	5.84	2.79																																																											
	87914-3424	-----	-----	-----	-----	34	-----	4	43.18	40.64	12.25	7.00	2.96																																																											
	87914-3434	-----	-----	-----	-----	34	-----	4	43.18	40.64	13.38	6.09	5.00																																																											
D	87914-3415	-----	-----	-----	-----	34	-----	5	43.18	40.64	10.92	5.84	2.79	D																																																										
	87914-3425	-----	-----	-----	-----	34	-----	5	43.18	40.64	12.25	7.00	2.96																																																											
	87914-3435	-----	-----	-----	-----	34	-----	5	43.18	40.64	13.38	6.09	5.00																																																											
	87914-3416	-----	-----	-----	-----	34	-----	6	43.18	40.64	10.92	5.84	2.79																																																											
	87914-3426	-----	-----	-----	-----	34	-----	6	43.18	40.64	12.25	7.00	2.96																																																											
	87914-3436	-----	-----	-----	-----	34	-----	6	43.18	40.64	13.38	6.09	5.00																																																											
C														C																																																										
B																																																																								
A	<table><tr><td rowspan="10">SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15</td><td rowspan="10">QUALITY SYMBOLS F=0 F=0 F=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2" rowspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="2">4 PLACES</td><td>± ---</td><td>± ---</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="3" rowspan="2">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY</td><td>DATE 2004/12/08</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td>PTLIM</td><td>DATE</td><td colspan="3" rowspan="2">molex</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td>APPROVED BY</td><td>DATE 2010/09/06</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td>MLONG</td><td>MATERIAL NO.</td><td colspan="2" rowspan="2">DOCUMENT NO. SD-87914-013</td><td rowspan="2">SHEET NO. 22 OF 45</td></tr><tr><td colspan="3">ANGULAR ± 3 °</td><td colspan="2">SEE TABLE</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="7">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>											SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES	± ---	± ---	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			3 PLACES	± ---	± ---	CHECKED BY	DATE 2004/12/08	2 PLACES	± 0.20	± ---	PTLIM	DATE	molex			1 PLACE	± ---	± ---	APPROVED BY	DATE 2010/09/06	0 PLACE	±	±	MLONG	MATERIAL NO.	DOCUMENT NO. SD-87914-013		SHEET NO. 22 OF 45	ANGULAR ± 3 °			SEE TABLE		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
	SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																															
			4 PLACES	± ---	± ---	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																
				3 PLACES	± ---	± ---	CHECKED BY				DATE 2004/12/08																																																													
			2 PLACES	± 0.20	± ---	PTLIM	DATE	molex																																																																
			1 PLACE	± ---	± ---	APPROVED BY	DATE 2010/09/06																																																																	
			0 PLACE	±	±	MLONG	MATERIAL NO.	DOCUMENT NO. SD-87914-013		SHEET NO. 22 OF 45																																																														
			ANGULAR ± 3 °			SEE TABLE																																																																		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																	
			fb_frame_A3_P_AM_T Rev. G 2012/01/11																																																																					
			9		8		7		6		5		4		3		2		1																																																					

10		9		8		7		6		5		4		3		2		1																																																											
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																					
								A	B	F	M	P																																																																	
F	87914-3811	-----	-----	-----	-----	38	----	1	48.26	45.72	10.92	5.84	2.79																																																																
	87914-3821	-----	-----	-----	-----	38	----	1	48.26	45.72	12.25	7.00	2.96																																																																
	87914-3831	-----	-----	-----	-----	38	----	1	48.26	45.72	13.38	6.09	5.00																																																																
	87914-3812	-----	-----	-----	-----	38	----	2	48.26	45.72	10.92	5.84	2.79																																																																
	87914-3822	-----	-----	-----	-----	38	----	2	48.26	45.72	12.25	7.00	2.96																																																																
	87914-3832	-----	-----	-----	-----	38	----	2	48.26	45.72	13.38	6.09	5.00																																																																
E	87914-3813	-----	-----	-----	-----	38	----	3	48.26	45.72	10.92	5.84	2.79																																																																
	87914-3823	-----	-----	-----	-----	38	----	3	48.26	45.72	12.25	7.00	2.96																																																																
	87914-3833	-----	-----	-----	-----	38	----	3	48.26	45.72	13.38	6.09	5.00																																																																
	87914-3814	-----	-----	-----	-----	38	----	4	48.26	45.72	10.92	5.84	2.79																																																																
D	87914-3824	-----	-----	-----	-----	38	----	4	48.26	45.72	12.25	7.00	2.96																																																																
	87914-3834	-----	-----	-----	-----	38	----	4	48.26	45.72	13.38	6.09	5.00																																																																
	87914-3815	-----	-----	-----	-----	38	----	5	48.26	45.72	10.92	5.84	2.79																																																																
	87914-3825	-----	-----	-----	-----	38	----	5	48.26	45.72	12.25	7.00	2.96																																																																
	87914-3835	-----	-----	-----	-----	38	----	5	48.26	45.72	13.38	6.09	5.00																																																																
	87914-3816	-----	-----	-----	-----	38	----	6	48.26	45.72	10.92	5.84	2.79																																																																
C	87914-3826	-----	-----	-----	-----	38	----	6	48.26	45.72	12.25	7.00	2.96																																																																
	87914-3836	-----	-----	-----	-----	38	----	6	48.26	45.72	13.38	6.09	5.00																																																																
B																																																																													
A	<table><tr><td rowspan="10">SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV</td><td rowspan="10">QUALITY SYMBOLS F=0 F=0 F=0</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="4">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td colspan="2">DOCUMENT NO.</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td>SHEET NO. 24 OF 45</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td></td></tr><tr><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></</td></tr></table>																		SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08	3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06	2 PLACES	± 0.20	± ---	DOCUMENT NO.		1 PLACE	± ---	± ---	SEE TABLE		SD-87914-013		SHEET NO. 24 OF 45	0 PLACE	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									</	
	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																			
				mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																																					
			4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08																																																																						
			3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06																																																																						
			2 PLACES	± 0.20	± ---	DOCUMENT NO.																																																																							
			1 PLACE	± ---	± ---	SEE TABLE		SD-87914-013		SHEET NO. 24 OF 45																																																																			
			0 PLACE	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																					
									</																																																																				

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
F	87914-4011	-----	-----	-----	-----	40	-----	1	50.80	48.26	10.92	5.84	2.79							F
	87914-4021	-----	-----	-----	-----	40	-----	1	50.80	48.26	12.25	7.00	2.96							
	87914-4031	-----	-----	-----	-----	40	-----	1	50.80	48.26	13.38	6.09	5.00							
	87914-4012	-----	-----	-----	-----	40	-----	2	50.80	48.26	10.92	5.84	2.79							
	87914-4022	-----	-----	-----	-----	40	-----	2	50.80	48.26	12.25	7.00	2.96							
	87914-4032	-----	-----	-----	-----	40	-----	2	50.80	48.26	13.38	6.09	5.00							
E	87914-4013	-----	-----	-----	-----	40	-----	3	50.80	48.26	10.92	5.84	2.79							E
	87914-4023	-----	-----	-----	-----	40	-----	3	50.80	48.26	12.25	7.00	2.96							
	87914-4033	-----	-----	-----	-----	40	-----	3	50.80	48.26	13.38	6.09	5.00							
	87914-4014	-----	-----	-----	-----	40	-----	4	50.80	48.26	10.92	5.84	2.79							
	87914-4024	-----	-----	-----	-----	40	-----	4	50.80	48.26	12.25	7.00	2.96							
	87914-4034	-----	-----	-----	-----	40	-----	4	50.80	48.26	13.38	6.09	5.00							
D	87914-4015	-----	-----	-----	-----	40	-----	5	50.80	48.26	10.92	5.84	2.79							D
	87914-4025	-----	-----	-----	-----	40	-----	5	50.80	48.26	12.25	7.00	2.96							
	87914-4035	-----	-----	-----	-----	40	-----	5	50.80	48.26	13.38	6.09	5.00							
	87914-4016	-----	-----	-----	-----	40	-----	6	50.80	48.26	10.92	5.84	2.79							
	87914-4026	-----	-----	-----	-----	40	-----	6	50.80	48.26	12.25	7.00	2.96							
	87914-4036	-----	-----	-----	-----	40	-----	6	50.80	48.26	13.38	6.09	5.00							
C																				C
B																				B

[illegible]

	10		9		8		7		6		5		4		3		2		1										
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																				
									A	B	F	M	P																
F	87914-4411	-----	-----	-----	-----	44	----	1	55.88	53.34	10.92	5.84	2.79																
	87914-4421	-----	-----	-----	-----	44	----	1	55.88	53.34	12.25	7.00	2.96																
	87914-4412	-----	-----	-----	-----	44	----	2	55.88	53.34	10.92	5.84	2.79																
	87914-4422	-----	-----	-----	-----	44	----	2	55.88	53.34	12.25	7.00	2.96																
	87914-4413	-----	-----	-----	-----	44	----	3	55.88	53.34	10.92	5.84	2.79																
E	87914-4423	-----	-----	-----	-----	44	----	3	55.88	53.34	12.25	7.00	2.96																
	87914-4414	-----	-----	-----	-----	44	----	4	55.88	53.34	10.92	5.84	2.79																
	87914-4424	-----	-----	-----	-----	44	----	4	55.88	53.34	12.25	7.00	2.96																
	87914-4415	-----	-----	-----	-----	44	----	5	55.88	53.34	10.92	5.84	2.79																
	87914-4425	-----	-----	-----	-----	44	----	5	55.88	53.34	12.25	7.00	2.96																
D	87914-4416	-----	-----	-----	-----	44	----	6	55.88	53.34	10.92	5.84	2.79																
	87914-4426	-----	-----	-----	-----	44	----	6	55.88	53.34	12.25	7.00	2.96																
C																													
B																													
A																													
										SEE SHEET 14 IEC NO: S2015-1512 DRW:KPRASAD CHKD:ATSEE APPR:KPRASAD 2015/06/25 2015/07/15		QUALITY SYMBOLS ▽ _F =0 ▽ _E =0 ▽ _P =0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO.		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		DOCUMENT NO. SD-87914-013		SHEET NO. 27 OF 45	
tb_frame_A3_P_AM_T Rev. G 2012/01/11										D15		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
	9		8		7		6		5		4		3		2		1												

[illegible]

10		9		8		7		6		5		4		3		2		1						
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																
								A	B	F	M	P												
F	87914-4811	-----	-----	-----	-----	48	----	1	60.96	58.42	10.92	5.84	2.79											
	87914-4821	-----	-----	-----	-----	48	----	1	60.96	58.42	12.25	7.00	2.96											
	87914-4812	-----	-----	-----	-----	48	----	2	60.96	58.42	10.92	5.84	2.79											
	87914-4822	-----	-----	-----	-----	48	----	2	60.96	58.42	12.25	7.00	2.96											
	87914-4813	-----	-----	-----	-----	48	----	3	60.96	58.42	10.92	5.84	2.79											
	87914-4823	-----	-----	-----	-----	48	----	3	60.96	58.42	12.25	7.00	2.96											
E	87914-4814	-----	-----	-----	-----	48	----	4	60.96	58.42	10.92	5.84	2.79											
	87914-4824	-----	-----	-----	-----	48	----	4	60.96	58.42	12.25	7.00	2.96											
	87914-4815	-----	-----	-----	-----	48	----	5	60.96	58.42	10.92	5.84	2.79											
	87914-4825	-----	-----	-----	-----	48	----	5	60.96	58.42	12.25	7.00	2.96											
	87914-4816	-----	-----	-----	-----	48	----	6	60.96	58.42	10.92	5.84	2.79											
	87914-4826	-----	-----	-----	-----	48	----	6	60.96	58.42	12.25	7.00	2.96											
D																								
C																								
B																								
A	SEE SHEET 14		EC NO: S2015-1512		DRWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		REV		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
																	MM ONLY		NTS		METRIC			
																	DRAWN BY		DATE		TITLE			
																	KCHO		2004/11/05		2.54MM PITCH			
																	CHECKED BY		DATE		DUAL ROW HEADER			
																	PTL IM		2004/12/08		SINGLE WAFER, T/H			
																	APPROVED BY		DATE					
																	MLONG		2010/09/06					
																	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
																	SEE TABLE		SD-87914-013		29 OF 45			
																SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
																A3								

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-5011	-----	-----	-----	-----	50	-----	1	63.50	60.96	10.92	5.84	2.79						
	87914-5021	-----	-----	-----	-----	50	-----	1	63.50	60.96	12.25	7.00	2.96						
	87914-5012	-----	-----	-----	-----	50	-----	2	63.50	60.96	10.92	5.84	2.79						
	87914-5022	-----	-----	-----	-----	50	-----	2	63.50	60.96	12.25	7.00	2.96						
	87914-5013	-----	-----	-----	-----	50	-----	3	63.50	60.96	10.92	5.84	2.79						
E	87914-5023	-----	-----	-----	-----	50	-----	3	63.50	60.96	12.25	7.00	2.96						
	87914-5014	-----	-----	-----	-----	50	-----	4	63.50	60.96	10.92	5.84	2.79						
	87914-5024	-----	-----	-----	-----	50	-----	4	63.50	60.96	12.25	7.00	2.96						
	87914-5015	-----	-----	-----	-----	50	-----	5	63.50	60.96	10.92	5.84	2.79						
	87914-5025	-----	-----	-----	-----	50	-----	5	63.50	60.96	12.25	7.00	2.96						
D	87914-5016	-----	-----	-----	-----	50	-----	6	63.50	60.96	10.92	5.84	2.79						
	87914-5026	-----	-----	-----	-----	50	-----	6	63.50	60.96	12.25	7.00	2.96						
	87914-0002	-----	-----	-----	-----	50	-----	8	63.50	60.96	18.54	11.58	4.47						
C																			
B																			
A																			

SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS ⌵ =0 ⌴ =0 ⌶ =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY	DATE	TITLE				
		4 PLACES	± ---	± ---	KCHO	2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
		3 PLACES	± ---	± ---	CHECKED BY	DATE					
		2 PLACES	± 0.20	± ---	PTL IM	2004/12/08					
		1 PLACE	± ---	± ---	APPROVED BY	DATE					
		0 PLACE	±	±	MLONG	2010/09/06	SD-87914-013				
		ANGULAR ± 3 °									
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					MATERIAL NO.		DOCUMENT NO.		SHEET NO. 30 OF 45
							SEE TABLE				
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1							
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																	
								A	B	F	M	P													
F	87914-5211	-----	-----	-----	-----	52	-----	1	66.04	63.50	10.92	5.84	2.79												
	87914-5221	-----	-----	-----	-----	52	-----	1	66.04	63.50	12.25	7.00	2.96												
	87914-5212	-----	-----	-----	-----	52	-----	2	66.04	63.50	10.92	5.84	2.79												
	87914-5222	-----	-----	-----	-----	52	-----	2	66.04	63.50	12.25	7.00	2.96												
	87914-5213	-----	-----	-----	-----	52	-----	3	66.04	63.50	10.92	5.84	2.79												
	87914-5223	-----	-----	-----	-----	52	-----	3	66.04	63.50	12.25	7.00	2.96												
E	87914-5214	-----	-----	-----	-----	52	-----	4	66.04	63.50	10.92	5.84	2.79												
	87914-5224	-----	-----	-----	-----	52	-----	4	66.04	63.50	12.25	7.00	2.96												
	87914-5215	-----	-----	-----	-----	52	-----	5	66.04	63.50	10.92	5.84	2.79												
	87914-5225	-----	-----	-----	-----	52	-----	5	66.04	63.50	12.25	7.00	2.96												
	87914-5216	-----	-----	-----	-----	52	-----	6	66.04	63.50	10.92	5.84	2.79												
	87914-5226	-----	-----	-----	-----	52	-----	6	66.04	63.50	12.25	7.00	2.96												
D																									
C																									
B																									
A																									
SEE SHEET 14		EC NO: S2015-1512		DRAWN:MRAMAKRISHNA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
D15																		MM ONLY		NTS		METRIC		◎ THIRD ANGLE PROJECTION	
																		DRAWN BY DATE		TITLE					
																		KCHO 2004/11/05		2.54MM PITCH					
																		CHECKED BY DATE		DUAL ROW HEADER					
																		PTLIM 2004/12/08		SINGLE WAFER, T/H					
																		APPROVED BY DATE							
																		MLONG 2010/09/06							
																		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
																		SEE TABLE		SD-87914-013				31 OF 45	
																		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX					
																		A3		INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

987654321

	10		9		8		7		6		5		4		3		2		1																																																												
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																						
									A	B	F	M	P																																																																		
F	87914-5411	-----	-----	-----	-----	54	----	1	68.58	66.04	10.92	5.84	2.79																																																																		
	87914-5421	-----	-----	-----	-----	54	----	1	68.58	66.04	12.25	7.00	2.96																																																																		
	87914-5412	-----	-----	-----	-----	54	----	2	68.58	66.04	10.92	5.84	2.79																																																																		
	87914-5422	-----	-----	-----	-----	54	----	2	68.58	66.04	12.25	7.00	2.96																																																																		
	87914-5413	-----	-----	-----	-----	54	----	3	68.58	66.04	10.92	5.84	2.79																																																																		
E	87914-5423	-----	-----	-----	-----	54	----	3	68.58	66.04	12.25	7.00	2.96																																																																		
	87914-5414	-----	-----	-----	-----	54	----	4	68.58	66.04	10.92	5.84	2.79																																																																		
	87914-5424	-----	-----	-----	-----	54	----	4	68.58	66.04	12.25	7.00	2.96																																																																		
	87914-5415	-----	-----	-----	-----	54	----	5	68.58	66.04	10.92	5.84	2.79																																																																		
	87914-5425	-----	-----	-----	-----	54	----	5	68.58	66.04	12.25	7.00	2.96																																																																		
D	87914-5416	-----	-----	-----	-----	54	----	6	68.58	66.04	10.92	5.84	2.79																																																																		
	87914-5426	-----	-----	-----	-----	54	----	6	68.58	66.04	12.25	7.00	2.96																																																																		
C																																																																															
B																																																																															
A																																																																															
<table><tr><td rowspan="5">SEE SHEET 14 IEC NO: S2015-1512 DRW:MRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV</td><td rowspan="5">QUALITY SYMBOLS ⌀ F =0 ⌀ F =0 ⌀ F =0 </td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="5"> THIRD ANGLE PROJECTION </td><td colspan="2" rowspan="5">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex </td><td colspan="2" rowspan="5">SD-87914-013</td><td colspan="2" rowspan="5">SHEET NO. 32 OF 45</td></tr><tr><td colspan="2">4 PLACES</td><td colspan="2">DRAWN BY DATE</td><td colspan="2" rowspan="4">SEE TABLE</td></tr><tr><td colspan="2">3 PLACES</td><td colspan="2">CHECKED BY DATE</td></tr><tr><td colspan="2">2 PLACES</td><td colspan="2">PTL IM 2004/12/08</td></tr><tr><td colspan="2">1 PLACE</td><td colspan="2">APPROVED BY DATE</td><td colspan="2" rowspan="3">MATERIAL NO.</td><td colspan="2" rowspan="3">DOCUMENT NO.</td><td colspan="2" rowspan="3"></td></tr><tr><td colspan="2">0 PLACE</td><td colspan="2">MLONG 2010/09/06</td></tr><tr><td colspan="2">ANGULAR ± 3 °</td><td colspan="2"></td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																				SEE SHEET 14 IEC NO: S2015-1512 DRW:MRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS ⌀ F =0 ⌀ F =0 ⌀ F =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SD-87914-013		SHEET NO. 32 OF 45		4 PLACES		DRAWN BY DATE		SEE TABLE		3 PLACES		CHECKED BY DATE		2 PLACES		PTL IM 2004/12/08		1 PLACE		APPROVED BY DATE		MATERIAL NO.		DOCUMENT NO.				0 PLACE		MLONG 2010/09/06		ANGULAR ± 3 °				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SEE SHEET 14 IEC NO: S2015-1512 DRW:MRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS ⌀ F =0 ⌀ F =0 ⌀ F =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SD-87914-013		SHEET NO. 32 OF 45																																																																		
		4 PLACES		DRAWN BY DATE		SEE TABLE																																																																									
		3 PLACES		CHECKED BY DATE																																																																											
		2 PLACES		PTL IM 2004/12/08																																																																											
		1 PLACE		APPROVED BY DATE											MATERIAL NO.		DOCUMENT NO.																																																														
0 PLACE		MLONG 2010/09/06																																																																													
ANGULAR ± 3 °																																																																															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																												
fb_frame_A3_P_AM_T Rev. G 2012/01/11	9		8		7		6		5		4		3		2		1																																																														

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					A	B	F	M	P		
								A	B	F	M	P							
F	87914-5611	-----	-----	-----	-----	56	----	1	71.12	68.58	10.92	5.84	2.79						
	87914-5621	-----	-----	-----	-----	56	----	1	71.12	68.58	12.25	7.00	2.96						
	87914-5612	-----	-----	-----	-----	56	----	2	71.12	68.58	10.92	5.84	2.79						
	87914-5622	-----	-----	-----	-----	56	----	2	71.12	68.58	12.25	7.00	2.96						
	87914-5613	-----	-----	-----	-----	56	----	3	71.12	68.58	10.92	5.84	2.79						
E	87914-5623	-----	-----	-----	-----	56	----	3	71.12	68.58	12.25	7.00	2.96						
	87914-5614	-----	-----	-----	-----	56	----	4	71.12	68.58	10.92	5.84	2.79						
	87914-5624	-----	-----	-----	-----	56	----	4	71.12	68.58	12.25	7.00	2.96						
	87914-5615	-----	-----	-----	-----	56	----	5	71.12	68.58	10.92	5.84	2.79						
	87914-5625	-----	-----	-----	-----	56	----	5	71.12	68.58	12.25	7.00	2.96						
D	87914-5616	-----	-----	-----	-----	56	----	6	71.12	68.58	10.92	5.84	2.79						
	87914-5626	-----	-----	-----	-----	56	----	6	71.12	68.58	12.25	7.00	2.96						
C																			
B																			
A																			

SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS ▽ _F =0 ▽ _F =0 ▽ _F =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE			
		4 PLACES	± ---	± ---	CHECKED BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			
		3 PLACES	± ---	± ---	PTLIM	2004/12/08				
		2 PLACES	± 0.20	± ---	APPROVED BY	DATE				
		1 PLACE	± ---	± ---	MLONG	2010/09/06				
		0 PLACE	±	±	MATERIAL NO.	DOCUMENT NO.				
		ANGULAR ± 3 °				SEE TABLE			SD-87914-013	SHEET NO. 33 OF 45
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F						
	A	B	F	M	P															
	87914-5811	-----	-----	-----	-----	58	-----	1	73.66	71.12	10.92	5.84	2.79							
	87914-5821	-----	-----	-----	-----	58	-----	1	73.66	71.12	12.25	7.00	2.96							
	87914-5812	-----	-----	-----	-----	58	-----	2	73.66	71.12	10.92	5.84	2.79							
	87914-5822	-----	-----	-----	-----	58	-----	2	73.66	71.12	12.25	7.00	2.96							
	87914-5813	-----	-----	-----	-----	58	-----	3	73.66	71.12	10.92	5.84	2.79							
	87914-5823	-----	-----	-----	-----	58	-----	3	73.66	71.12	12.25	7.00	2.96							
E	87914-5814	-----	-----	-----	-----	58	-----	4	73.66	71.12	10.92	5.84	2.79	E						
	87914-5824	-----	-----	-----	-----	58	-----	4	73.66	71.12	12.25	7.00	2.96							
	87914-5815	-----	-----	-----	-----	58	-----	5	73.66	71.12	10.92	5.84	2.79							
	87914-5825	-----	-----	-----	-----	58	-----	5	73.66	71.12	12.25	7.00	2.96							
	87914-5816	-----	-----	-----	-----	58	-----	6	73.66	71.12	10.92	5.84	2.79							
	87914-5826	-----	-----	-----	-----	58	-----	6	73.66	71.12	12.25	7.00	2.96							
D														D						

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-6011	-----	-----	-----	-----	60	----	1	76.20	73.66	10.92	5.84	2.79						
	87914-6021	-----	-----	-----	-----	60	----	1	76.20	73.66	12.25	7.00	2.96						
	87914-6012	-----	-----	-----	-----	60	----	2	76.20	73.66	10.92	5.84	2.79						
	87914-6022	-----	-----	-----	-----	60	----	2	76.20	73.66	12.25	7.00	2.96						
	87914-6013	-----	-----	-----	-----	60	----	3	76.20	73.66	10.92	5.84	2.79						
	87914-6023	-----	-----	-----	-----	60	----	3	76.20	73.66	12.25	7.00	2.96						
E	87914-6014	-----	-----	-----	-----	60	----	4	76.20	73.66	10.92	5.84	2.79	E					
	87914-6024	-----	-----	-----	-----	60	----	4	76.20	73.66	12.25	7.00	2.96						
	87914-6015	-----	-----	-----	-----	60	----	5	76.20	73.66	10.92	5.84	2.79						
	87914-6025	-----	-----	-----	-----	60	----	5	76.20	73.66	12.25	7.00	2.96						
	87914-6016	-----	-----	-----	-----	60	----	6	76.20	73.66	10.92	5.84	2.79						
	87914-6026	-----	-----	-----	-----	60	----	6	76.20	73.66	12.25	7.00	2.96						
D														D					
C														C					
B														B					

10		9		8		7		6		5		4		3		2		1					
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION															
								A	B	F	M	P											
F	87914-6211	-----	-----	-----	-----	62	-----	1	78.74	76.20	10.92	5.84	2.79										
	87914-6221	-----	-----	-----	-----	62	-----	1	78.74	76.20	12.25	7.00	2.96										
	87914-6212	-----	-----	-----	-----	62	-----	2	78.74	76.20	10.92	5.84	2.79										
	87914-6222	-----	-----	-----	-----	62	-----	2	78.74	76.20	12.25	7.00	2.96										
	87914-6213	-----	-----	-----	-----	62	-----	3	78.74	76.20	10.92	5.84	2.79										
	87914-6223	-----	-----	-----	-----	62	-----	3	78.74	76.20	12.25	7.00	2.96										
E	87914-6214	-----	-----	-----	-----	62	-----	4	78.74	76.20	10.92	5.84	2.79										
	87914-6224	-----	-----	-----	-----	62	-----	4	78.74	76.20	12.25	7.00	2.96										
	87914-6215	-----	-----	-----	-----	62	-----	5	78.74	76.20	10.92	5.84	2.79										
	87914-6225	-----	-----	-----	-----	62	-----	5	78.74	76.20	12.25	7.00	2.96										
	87914-6216	-----	-----	-----	-----	62	-----	6	78.74	76.20	10.92	5.84	2.79										
	87914-6226	-----	-----	-----	-----	62	-----	6	78.74	76.20	12.25	7.00	2.96										
D																							
C																							
B																							
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mmINCH 4 PLACES± --- ± --- 3 PLACES± --- ± --- 2 PLACES± 0.20 ± --- 1 PLACE± --- ± --- 0 PLACE± ± ANGULAR ± 3 °			DIMENSION STYLE MM ONLY DRAWN BYDATE KCHO2004/11/05 CHECKED BYDATE PTLIM2004/12/08 APPROVED BYDATE MLONG2010/09/06		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			DOCUMENT NO. SD-87914-013		SHEET NO. 36 OF 45
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

987654321

	10		9		8		7		6		5		4		3		2		1																																																																											
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																					
									A	B	F	M	P																																																																																	
F	87914-6411	-----	-----	-----	-----	64	----	1	81.28	78.74	10.92	5.84	2.79								F																																																																									
	87914-6421	-----	-----	-----	-----	64	----	1	81.28	78.74	12.25	7.00	2.96																																																																																	
	87914-6412	-----	-----	-----	-----	64	----	2	81.28	78.74	10.92	5.84	2.79																																																																																	
	87914-6422	-----	-----	-----	-----	64	----	2	81.28	78.74	12.25	7.00	2.96																																																																																	
	87914-6413	-----	-----	-----	-----	64	----	3	81.28	78.74	10.92	5.84	2.79																																																																																	
	87914-6423	-----	-----	-----	-----	64	----	3	81.28	78.74	12.25	7.00	2.96																																																																																	
E	87914-6414	-----	-----	-----	-----	64	----	4	81.28	78.74	10.92	5.84	2.79								E																																																																									
	87914-6424	-----	-----	-----	-----	64	----	4	81.28	78.74	12.25	7.00	2.96																																																																																	
	87914-6415	-----	-----	-----	-----	64	----	5	81.28	78.74	10.92	5.84	2.79																																																																																	
	87914-6425	-----	-----	-----	-----	64	----	5	81.28	78.74	12.25	7.00	2.96																																																																																	
	87914-6416	-----	-----	-----	-----	64	----	6	81.28	78.74	10.92	5.84	2.79																																																																																	
	87914-6426	-----	-----	-----	-----	64	----	6	81.28	78.74	12.25	7.00	2.96																																																																																	
D																					D																																																																									
C																					C																																																																									
B																					B																																																																									
A																					A																																																																									
<table><tr><td rowspan="5">SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAWAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15</td><td rowspan="5">QUALITY SYMBOLS =0 =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td><td colspan="4" rowspan="2">DOCUMENT NO. SD-87914-013</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td colspan="2"></td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td colspan="2"></td><td colspan="4" rowspan="2">SHEET NO. 37 OF 45</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td colspan="2"></td></tr><tr><td colspan="4">ANGULAR ± 3 °</td><td colspan="2">SEE TABLE</td><td colspan="4"></td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="7">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																					SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAWAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08	3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06	DOCUMENT NO. SD-87914-013				2 PLACES	± 0.20	± ---			1 PLACE	± ---	± ---			SHEET NO. 37 OF 45				0 PLACE	±	±			ANGULAR ± 3 °				SEE TABLE						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAWAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																						
			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																																																							
		4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08																																																																																								
		3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06	DOCUMENT NO. SD-87914-013																																																																																							
		2 PLACES	± 0.20	± ---																																																																																										
1 PLACE	± ---	± ---			SHEET NO. 37 OF 45																																																																																									
0 PLACE	±	±																																																																																												
ANGULAR ± 3 °				SEE TABLE																																																																																										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																									
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1																																																																																				

[illegible]

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-6811	-----	-----	-----	-----	68	-----	1	86.36	83.82	10.92	5.84	2.79						
	87914-6821	-----	-----	-----	-----	68	-----	1	86.36	83.82	12.25	7.00	2.96						
	87914-6812	-----	-----	-----	-----	68	-----	2	86.36	83.82	10.92	5.84	2.79						
	87914-6822	-----	-----	-----	-----	68	-----	2	86.36	83.82	12.25	7.00	2.96						
	87914-6813	-----	-----	-----	-----	68	-----	3	86.36	83.82	10.92	5.84	2.79						
	87914-6823	-----	-----	-----	-----	68	-----	3	86.36	83.82	12.25	7.00	2.96						
E	87914-6814	-----	-----	-----	-----	68	-----	4	86.36	83.82	10.92	5.84	2.79						
	87914-6824	-----	-----	-----	-----	68	-----	4	86.36	83.82	12.25	7.00	2.96						
	87914-6815	-----	-----	-----	-----	68	-----	5	86.36	83.82	10.92	5.84	2.79						
	87914-6825	-----	-----	-----	-----	68	-----	5	86.36	83.82	12.25	7.00	2.96						
	87914-6816	-----	-----	-----	-----	68	-----	6	86.36	83.82	10.92	5.84	2.79						
	87914-6826	-----	-----	-----	-----	68	-----	6	86.36	83.82	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV DESCRIPTION QUALITY SYMBOLS =0 =0 =0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. DOCUMENT NO. SEE TABLE SD-87914-013 SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION SCALE NTS DESIGN UNITS METRIC THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex SHEET NO. 39 OF 45							9	8	7	6	5	4	3	2	1			

10		9		8		7		6		5		4		3		2		1					
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION															
								A	B	F	M	P											
F	87914-7011	-----	-----	-----	-----	70	----	1	88.90	86.36	10.92	5.84	2.79										
	87914-7021	-----	-----	-----	-----	70	----	1	88.90	86.36	12.25	7.00	2.96										
	87914-7012	-----	-----	-----	-----	70	----	2	88.90	86.36	10.92	5.84	2.79										
	87914-7022	-----	-----	-----	-----	70	----	2	88.90	86.36	12.25	7.00	2.96										
	87914-7013	-----	-----	-----	-----	70	----	3	88.90	86.36	10.92	5.84	2.79										
	87914-7023	-----	-----	-----	-----	70	----	3	88.90	86.36	12.25	7.00	2.96										
E	87914-7014	-----	-----	-----	-----	70	----	4	88.90	86.36	10.92	5.84	2.79										
	87914-7024	-----	-----	-----	-----	70	----	4	88.90	86.36	12.25	7.00	2.96										
	87914-7015	-----	-----	-----	-----	70	----	5	88.90	86.36	10.92	5.84	2.79										
	87914-7025	-----	-----	-----	-----	70	----	5	88.90	86.36	12.25	7.00	2.96										
	87914-7016	-----	-----	-----	-----	70	----	6	88.90	86.36	10.92	5.84	2.79										
	87914-7026	-----	-----	-----	-----	70	----	6	88.90	86.36	12.25	7.00	2.96										
D																							
C																							
B																							
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV DESCRIPTION							QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION							
								 =0 =0 =0		mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex									
									4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08										
									3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06										
									2 PLACES	± 0.20	± ---												
									1 PLACE	± ---	± ---												
								0 PLACE	±	±			MATERIAL NO.		DOCUMENT NO.	SHEET NO.							
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
								fb_frame_A3_P_AM_T Rev. G 2012/01/11							9	8	7	6	5	4	3	2	1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-7211	-----	-----	-----	-----	72	-----	1	91.44	88.90	10.92	5.84	2.79						
	87914-7221	-----	-----	-----	-----	72	-----	1	91.44	88.90	12.25	7.00	2.96						
	87914-7212	-----	-----	-----	-----	72	-----	2	91.44	88.90	10.92	5.84	2.79						
	87914-7222	-----	-----	-----	-----	72	-----	2	91.44	88.90	12.25	7.00	2.96						
	87914-7213	-----	-----	-----	-----	72	-----	3	91.44	88.90	10.92	5.84	2.79						
	87914-7223	-----	-----	-----	-----	72	-----	3	91.44	88.90	12.25	7.00	2.96						
E	87914-7214	-----	-----	-----	-----	72	-----	4	91.44	88.90	10.92	5.84	2.79						
	87914-7224	-----	-----	-----	-----	72	-----	4	91.44	88.90	12.25	7.00	2.96						
	87914-7215	-----	-----	-----	-----	72	-----	5	91.44	88.90	10.92	5.84	2.79						
	87914-7225	-----	-----	-----	-----	72	-----	5	91.44	88.90	12.25	7.00	2.96						
	87914-7216	-----	-----	-----	-----	72	-----	6	91.44	88.90	10.92	5.84	2.79						
	87914-7226	-----	-----	-----	-----	72	-----	6	91.44	88.90	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV DESCRIPTION D15							QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
								 =0 =0 =0		mm	INCH	DRAWN BY	DATE	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex					
									4 PLACES	± ---	± ---	KCHO	2004/11/05						
									3 PLACES	± ---	± ---	CHECKED BY	DATE						
									2 PLACES	± 0.20	± ---	PTL IM	2004/12/08						
									1 PLACE	± ---	± ---	APPROVED BY	DATE						
								0 PLACE	±	±	MLONG	2010/09/06							
								ANGULAR ± 3 °			MATERIAL NO.	DOCUMENT NO.							
								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-87914-013		SHEET NO. 41 OF 45				
								SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1									

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-7411	-----	-----	-----	-----	74	-----	1	93.98	91.44	10.92	5.84	2.79						
	87914-7421	-----	-----	-----	-----	74	-----	1	93.98	91.44	12.25	7.00	2.96						
	87914-7412	-----	-----	-----	-----	74	-----	2	93.98	91.44	10.92	5.84	2.79						
	87914-7422	-----	-----	-----	-----	74	-----	2	93.98	91.44	12.25	7.00	2.96						
	87914-7413	-----	-----	-----	-----	74	-----	3	93.98	91.44	10.92	5.84	2.79						
	87914-7423	-----	-----	-----	-----	74	-----	3	93.98	91.44	12.25	7.00	2.96						
E	87914-7414	-----	-----	-----	-----	74	-----	4	93.98	91.44	10.92	5.84	2.79						
	87914-7424	-----	-----	-----	-----	74	-----	4	93.98	91.44	12.25	7.00	2.96						
	87914-7415	-----	-----	-----	-----	74	-----	5	93.98	91.44	10.92	5.84	2.79						
	87914-7425	-----	-----	-----	-----	74	-----	5	93.98	91.44	12.25	7.00	2.96						
	87914-7416	-----	-----	-----	-----	74	-----	6	93.98	91.44	10.92	5.84	2.79						
	87914-7426	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96						
D																			
											</								

[illegible]

10		9		8		7		6		5		4		3		2		1		
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
								A	B	F	M	P								
F	87914-7811	-----	-----	-----	-----	78	-----	1	99.06	96.52	10.92	5.84	2.79							
	87914-7821	-----	-----	-----	-----	78	-----	1	99.06	96.52	12.25	7.00	2.96							
	87914-7812	-----	-----	-----	-----	78	-----	2	99.06	96.52	10.92	5.84	2.79							
	87914-7822	-----	-----	-----	-----	78	-----	2	99.06	96.52	12.25	7.00	2.96							
	87914-7813	-----	-----	-----	-----	78	-----	3	99.06	96.52	10.92	5.84	2.79							
	87914-7823	-----	-----	-----	-----	78	-----	3	99.06	96.52	12.25	7.00	2.96							
E	87914-7814	-----	-----	-----	-----	78	-----	4	99.06	96.52	10.92	5.84	2.79							
	87914-7824	-----	-----	-----	-----	78	-----	4	99.06	96.52	12.25	7.00	2.96							
	87914-7815	-----	-----	-----	-----	78	-----	5	99.06	96.52	10.92	5.84	2.79							
	87914-7825	-----	-----	-----	-----	78	-----	5	99.06	96.52	12.25	7.00	2.96							
D	87914-7816	-----	-----	-----	-----	78	-----	6	99.06	96.52	10.92	5.84	2.79							
	87914-7826	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96							
C																				
B																				
A	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO.		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 44 OF 45	
	D15							SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

982

879

781

652

584

479

396

296

1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSIONS											
								A	B	F	M	P							
F	87914-8011	-----	-----	-----	-----	80	-----	1	101.60	99.06	10.92	5.84	2.79						
	87914-8021	-----	-----	-----	-----	80	-----	1	101.60	99.06	12.25	7.00	2.96						
	87914-8012	-----	-----	-----	-----	80	-----	2	101.60	99.06	10.92	5.84	2.79						
	87914-8022	-----	-----	-----	-----	80	-----	2	101.60	99.06	12.25	7.00	2.96						
	87914-8013	-----	-----	-----	-----	80	-----	3	101.60	99.06	10.92	5.84	2.79						
	87914-8023	-----	-----	-----	-----	80	-----	3	101.60	99.06	12.25	7.00	2.96						
E	87914-8014	-----	-----	-----	-----	80	-----	4	101.60	99.06	10.92	5.84	2.79						
	87914-8024	-----	-----	-----	-----	80	-----	4	101.60	99.06	12.25	7.00	2.96						
	87914-8015	-----	-----	-----	-----	80	-----	5	101.60	99.06	10.92	5.84	2.79						
	87914-8025	-----	-----	-----	-----	80	-----	5	101.60	99.06	12.25	7.00	2.96						
	87914-8016	-----	-----	-----	-----	80	-----	6	101.60	99.06	10.92	5.84	2.79						
	87914-8026	-----	-----	-----	-----	80	-----	6	101.60	99.06	12.25	7.00	2.96						
D																			
C																			
B																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN: HRAKRI SHNA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV DESCRIPTION QUALITY SYMBOLS F=0 F=0 F=0 GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							DIMENSION STYLE MM ONLY		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 45 OF 45	
								DRAWN BY KCHO		DATE 2004/11/05		TITLE							
								CHECKED BY PTL IM		DATE 2004/12/08									
								APPROVED BY MLONG		DATE 2010/09/06									
								MATERIAL NO.		DOCUMENT NO.		SD-87914-013							
								SEE TABLE											

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1