

REVISION AA

DO NOT
SCALE FROM
THIS PRINT

TABLE 1								
STYLE	TERMINAL	"A"	"B"	"C"	"D"	"E"	"F"	"G" REF
-01	T-1S8-01-T	.175 [4.45]	.450 [11.43]	N/A	N/A	.213 [5.41]	.412 [10.46]	.462 [11.73]
-02	T-1S8-02-T	.175 [4.45]	.500 [12.70]	.100 [2.54]	.175 [4.45]	.213 [5.41]	.462 [11.73]	.512 [13.00]
-04	T-1S8-04-T	.156 [3.96]	.809 [3.96]	.195 [4.95]	.156 [3.96]	.213 [5.41]	.752 [19.10]	.802 [20.37]
-05	T-1S8-05-T	.156 [3.96]	1.069 [27.15]	.195 [4.95]	.156 [3.96]	.213 [5.41]	1.012 [25.70]	1.062 [26.97]

HFWJ-XX-XX-XX-X-XX-X

No OF POSITIONS
-01 THRU -24


LEAD STYLE
SEE TABLE 1

PLATING SPECIFICATION
-T: TIN (USE T-1S8-XX-T)
-TM: MATTE TIN
(USE T-1S8-XX-T)




OPTION
-P: PICK & PLACE PAD
(USE PPP-47, SEE FIG 2)
(-VS ONLY, 3 POSITION MIN)

OPTION
-RA: RIGHT ANGLE (POST)
(N/A WITH -VS OPTION)
-VS: VERTICAL SURFACE MOUNT
(N/A ON -01 POSITION)


ROW SPECIFICATION
-S: SINGLE (USE HFWJ-24-156)
LEAD STYLES 01, 02, 04 & 05




- NOTES:
1. MAX PIN ROTATION IN BODY : 2 DEGREES
 2. MINIMUM PUSHOUT FORCE: .5 LB.
 3. BURR ALLOWANCE: .0015 MAX.
 4. STANDARD & -RA PARTS TO BE BULK PACKAGED.
 5. SURFACE MOUNT (-VS) TO BE PACKAGED AS FOLLOWS:
POSITIONS -04 THRU -20 TO BE TUBE PACKAGED.
POSITIONS -02 & -03 TO BE LAYER PACKAGED.
 6. MAXIMUM CUT FLASH: .020.
 7. MAX HEIGHT VARIATION BETWEEN PINS: .005[.13]
 8. POSITIONS -02 THRU -16 TO BE .008[.20]
 9. POSITIONS -17 THRU -24 TO BE .010[.25]
 10. C3 REPRESENTS A CRITICAL DIMENSION.
 11. -01 POSITION PARTS TO BE BULK PACKAGED.
 12. BANDOLIER AREA ON T-1S8 MUST NOT BE ENTIRELY LOCATED IN THE CONTACT AREA. POSITION ABOUT OR TOWARDS STANDOFF SIDE OF BODY.
 13. BANDOLIER AREA MUST NOT BE LOCATED IN CONTACT AREA.



PACKAGING VIEW



TUBE: PT-1-24-01-26
PLUG: TP-25
(SEE NOTE 5)



NOTE:
"R" = No OF POS x .156[3.96] REF
"S" = {("R" - .450[11.43]) / 2} ±.020[12.90]

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.3]
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.051]

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 1.5:1
INSULATOR: VECTRA E130I, COLOR: NATURAL
CONTACT OR TERMINAL: PHOS BRONZE, 510
MAX FLASH ALLOWED: .002
MAX GATE VESTIGE: .002
F:\DWG\MISC\MKTG\HFWJ-XX-XX-XX-X-MKT.SLDDRW

520 PARK EAST BLVD. NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
.156[3.96] PWER BLOCK ASSEMBLY

DWG. NO.
HFWJ-XX-XX-XX-X-XX-X

BY: T.WERNE 06/06/2002 SHEET 1 OF 1