




Notes :

- Machined contact
- The extraction tool is RX20D44
- Crimping tool : S20RCM

Material :

- Contact body:high conductive copper alloy
- :plating: K : 0.4 micron gold over nickel
- Retaining spring:stainless steel

Performance Characteristics :

- Contact retention in the body:50N max
- Contact insertion force:5N max
- Contact separation force:2N min
- Current rating:7.5 Amps
- Contact resistance:6mΩ max
- Dielectric withstanding voltage:1500 Vrms min
- Diameter over insulation 1.20 mm min up to 2.10 mm max
- Section of wire 0.50 mm² min up to 0.82 mm² max
- Wire strip length : 4.8 mm

P/N : RC18W3K

d	20/04/11	Update of section of wire		21654
ISS	DATE	Latest modification - by:	MOREAU F.	MOD N°
Designed by:		C.PROVOST	Date: 20/04/11	CUSTOMER DRAWING
TITLE		Female crimp contact AWG 20 - 18 Connector UT0W		
Scale	8/1		General linear Tolerances: ± 0.1	NPRDS / PROJECT RC
		WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A3	SOURIAU DRG N° RC18W3K-C01		
				SHEET 1 / 1