




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MAX. BUNDLE DIA [mm]	LENGTH ±.1 [2]
MSC4W63T15-L6	4" [102]	18.0" [457]
MSC6W63T15-L6	6" [152]	24.4" [620]
MSC8W63T15-L6	8" [203]	30.7" [780]
MSC10W63T15-L6	10" [254]	37.0" [940]



NOTES:

1. APPLICATION TOOLS: BT2MS75, BT2HT
2. BRACKETS [] DENOTES DIMENSIONS IN MILLIMETERS AND ARE FOR REFERENCE ONLY
3. BASE MATERIAL: 316 STAINLESS STEEL.
4. 100% COATED WITH BLACK NYLON OR POLYESTER.
5. COATING THICKNESS: .003/ .005[.076/ .127]PER SIDE.
6. TOLERANCES(UNLESS OTHERWISE SPECIFIED):
 - .X ± .03[.8]
 - .XX ± .02[.5]
 - .XXX ± .007[.18]

							TITLE COATED METAL STRAPPING .625" [15.88] WIDE			
							CUSTOMER DRAWING ITEM REVISION NAME N41169BS/01			
							DATASET FILE NAME N41169BS_BS/01A			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION			
01A	4/13	JAMB	MIM	RGR0	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01047	MATERIAL: SEE NOTES			
00A	10/08	JAMB	SKB	---	ORIG CAD FILE SPEC WAS S41169BS_00. NOTE #1: APPLICATION TOOL BT1HT REPLACED BY BT2HT	-----	DRAWING NUMBER: N41169BS_DC			
00	10/03	BRH	EJD	JJB	DRAWING RELEASED	11159	DRAWN BY BRH DATE 10/03 CHK EJD SCALE 1:1			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	SHT 1 OF 1 SIZE A			