

# Features

## Unregulated Converter

- Industry Standard Pinout
- 1kVDC or 2kVDC Isolation
- UL94V-0 Package Material
- Optional Continuous Short Circuit Protected
- Fully Encapsulated
- Custom Solutions Available
- Efficiency to 85 %

### Description

The RE DC/DC converters are typically used in general purpose power isolation and voltage matching applications, and feature a full industrial operating temperature range of -40°C to +85°C without derating.

### Selection Guide

| Part Number<br>SIP 7 | (2kV) | Input Voltage<br>(VDC) | Output Voltage<br>(VDC) | Output Current<br>(mA) | Efficiency<br>(%) | Max Capacitive Load <sup>(1)</sup> |
|----------------------|-------|------------------------|-------------------------|------------------------|-------------------|------------------------------------|
| RE-xx3.3S            | (H)   | 3.3, 5, 12, 15, 24     | 3.3                     | 303                    | 75                | 2200µF                             |
| RE-xx05S             | (H)   | 3.3, 5, 12, 15, 24     | 5                       | 200                    | 78-80             | 1000µF                             |
| RE-xx09S             | (H)   | 3.3, 5, 12, 15, 24     | 9                       | 111                    | 78-80             | 1000µF                             |
| RE-xx12S             | (H)   | 3.3, 5, 12, 15, 24     | 12                      | 83                     | 80-84             | 470µF                              |
| RE-xx15S             | (H)   | 3.3, 5, 12, 15, 24     | 15                      | 66                     | 80-84             | 470µF                              |
| RE-xx24S             | (H)   | 3.3, 5, 12, 15, 24     | 24                      | 42                     | 78-85             | 220µF                              |

xx = Input Voltage (other input and output voltage combinations available on request)

\* add Suffix "P" for Continuous Short Circuit Protection, e.g. RE-0505S/P, RE-0505S/HP

### Specifications (measured at T<sub>A</sub> = 25°C, nominal input voltage, full load and after warm-up)

|                                                   |                                                           |                                                 |
|---------------------------------------------------|-----------------------------------------------------------|-------------------------------------------------|
| Input Voltage Range                               |                                                           | ±10%                                            |
| Output Voltage Accuracy                           |                                                           | ±5%                                             |
| Line Voltage Regulation                           |                                                           | 1.2%/1% of Vin typ.                             |
| Load Voltage Regulation                           | 3.3V output type                                          | 20% max.                                        |
| (10% to 100% full load)                           | 5V output type                                            | 15% max.                                        |
|                                                   | 9V, 12V, 15V, 24V output types                            | 10% max.                                        |
| Output Ripple and Noise (20MHz limited)           |                                                           | 100mVp-p max.                                   |
| Operating Frequency                               |                                                           | 50kHz min. / 100kHz typ. / 105kHz max.          |
| Efficiency at Full Load                           |                                                           | 70% min. / 80% typ.                             |
| Minimum Load = 0%                                 |                                                           | Specifications valid for 10% minimum load only. |
| Isolation Voltage                                 | (tested for 1 second)                                     | 1000VDC                                         |
|                                                   | (rated for 1 minute**)                                    | 500VAC / 60Hz                                   |
| Isolation Voltage                                 | H-Suffix (tested for 1 second)                            | 2000VDC                                         |
|                                                   | H-Suffix (rated for 1 minute**)                           | 1000VAC / 60Hz                                  |
| Isolation Capacitance                             |                                                           | 20pF min. / 75pF max.                           |
| Isolation Resistance                              |                                                           | 10 GΩ min.                                      |
| Short Circuit Protection                          |                                                           | 1 Second                                        |
| P-Suffix                                          |                                                           | Continuous                                      |
| Operating Temperature Range (free air convection) |                                                           | -40°C to +85°C (see Graph)                      |
| Storage Temperature Range                         |                                                           | -55°C to +125°C                                 |
| Relative Humidity                                 |                                                           | 95% RH                                          |
| Package Weight                                    |                                                           | 2.2g                                            |
| Packing Quantity                                  |                                                           | 25 pcs per Tube                                 |
| MTBF (+25°C)                                      | Detailed Information see Application Notes chapter "MTBF" | using MIL-HDBK 217F 992 x 10 <sup>3</sup> hours |
| (+85°C)                                           |                                                           | using MIL-HDBK 217F 145 x 10 <sup>3</sup> hours |

continued on next page

\*\*Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

# ECONOLINE

## DC/DC-Converter


with 3 year Warranty

RECOM

1 Watt

SIP7


Single Output



EN-60950-1 Certified  
UL-60950-1 Certified

RE

## Derating-Graph (Ambient Temperature)



Refer to Application Notes

### Specifications (measured at $T_A = 25^\circ\text{C}$ , nominal input voltage, full load and after warm-up)

#### Certifications

CB Test Report

Report: US/15348/UL

IEC 60950-1:2005 2nd Edition

UL General Safety

Report: E358085

UL 60950-1 2nd Edition

EN General Safety

Report: SPCLVD1109103



EN60950-1:2006 + A12:2011

#### Notes



Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.

### Typical Characteristics



## RE-xx05S



## RE-xx12S





## RE-xx15S





### Package Style and Pinning (mm)

#### 7 PIN SIP Package



#### Recommended Footprint Details



#### RE Pin Connections

| Pin # | Single                |
|-------|-----------------------|
| 1     | +Vin                  |
| 2     | -Vin                  |
| 4     | -Vout                 |
| 6     | +Vout                 |
| XX.X  | $\pm 0.5 \text{ mm}$  |
| XX.XX | $\pm 0.25 \text{ mm}$ |

The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.