

4820 B



Versions

4820 B	black w/foam
4820 BE	black empty
4820 G	mil. green w/foam
4820 GE	mil. green empty
4820 O	orange w/foam
4820 OE	orange empty

- Made of Copolymer Polypropylene compound
- Waterproof, resistant to chemicals, humidity, dust
- Resistant to harsh temperatures (-33°C / +90°C)
- Jam-free purge valve and latches
- Recommended for professional applications

- 100% made in Italy: Italian design and proven functionality
- First to achieve the new military standard qualifications
- Recognized as the most versatile case to customize
- Widest choice of accessories to customize your experience
- Incorporate a number of patented innovations


Technical Features		L	W	D		
		Length	Width	Depth	Lid	Base
Internal dim.	mm	480	370	205	50	155
External dim.	mm	520	435	230		

Weight empty	Kg 4,64
Weight w/foam	Kg 5,40
Weight w/multi	Kg ---

Volume	lt 36
Buoyancy	Kg/max 24,70

Temp. rating	°C min -33 max +90
--------------	--------------------

Certifications
2002/95/EC Conformity with the Directive 2002/95/EC
DEF STAN 81-41 (level J)
IP67 Dustproof - Waterproof
MIL-STD 810G Mod. 4820
STANAG 4280 (edition 2)



Accessories 4820 B



PANRING48.USA



KIT.EXPL.PLUGS



LIDFOAM.48



KIN.0481 - SILICA BOX



FOAM.4820



BACKPACK L



PANEXPL48



KIT SUPP.EXPL.



BAG-F



PANRING48



EXPL COMBILOCK



EXPL PADLOCK



KIT SUPP.PLAST.



BAG-PC48



EXPL TSA.DIGILOCK