

FREQUENCY MIXERS

Surface Mount

LEVEL 13 150 kHz to 6 GHz



ADE



ALY



† JMS



† LRMS-J



MBA

+13 dBm LO, up to +9 dBm RF

	MODEL NO.	FREQUENCY MHz		CONVERSION LOSS dB			LO-RF ISOLATION, dB					LO-IF ISOLATION, dB					IP3@ center band Typ. (dBm)	CASE STYLE	CONNECTION	PRICE \$
		LO/RF f _L -f _U	IF	Mid-Band x σ ^m Max.	Total Range Max.	L Typ. Min.	M Typ. Min.	U Typ. Min.	L Typ. Min.	M Typ. Min.	U Typ. Min.	Qty. (10-49)								
NEW	◆ ADE-1MH**	2-500	DC-500	5.2 .10	6.5	8.0	60 45	50 35	48 25	55 40	45 30	40 22	17	CD542	ht	5.95				
	◆ ADE-1MHW**	0.5-600	DC-600	5.2 .10	6.9	8.0	63 50	53 32	43 20	56 40	44 25	30 20	17	CD636	ht	6.45				
	◆ ADE-10MH**	800-1000	10-200	7.0 0.2	—	8.5	34 (Typ.) 20 (Min.)			29 (Typ.) 20 (Min.)			26	CD636	ht	6.95				
	◆ ADE-12MH**	10-1200	DC-1200	6.3 .10	8.0	8.5	62 45	45 32	40 26	68 40	42 27	30 20	22	CD542	ht	6.45				
	◆ ADE-25MH**	5-2500	5-1500	6.9 .10	8.5	9.8	47 28	34 23	34 23	34 23	32 20	23 17	18	CD542	ht	6.95				
	◆ ADE-35MH**	5-3500	5-2500	6.9 .10	9.3	10.5	47 28	33 23	38 18	34 23	28 18	23 17	18	CD542	ht	9.95				
	◆ ADE-42MH**	5-4200	5-3500	7.5 .20	9.8	11.8	47 28	29 20	30 15	34 23	26 17	23 17	17	CD542	ht	14.95				
	◆ MBA-9MH*	800-1000	DC-200	6.7 0.1	—	9.0	25 (Typ.) 20 (Min.)		18 (Typ.) 12 (Min.)		15	SM2	lc	7.95						
	◆ MBA-12MH*	800-2500	DC-500	7.5 0.1	—	9.5	30 (Typ.) 20 (Min.)		15 (Typ.) 7 (Min.)		15	SM2	lc	7.95						
	◆ MBA-15MH*	1400-2400	DC-600	5.5 0.1	—	8.5	28 (Typ.) 16 (Min.)		16 (Typ.) 8 (Min.)		18	SM2	ld	7.95						
	◆ MBA-18MH*	1600-3200	DC-650	5.5 0.1	—	8.0	35 (Typ.) 18 (Min.)		18 (Typ.) 10 (Min.)		16	SM2	ld	7.95						
	◆ MBA-25MH*	2000-3000	DC-500	6.5 0.1	—	8.6	36 (Typ.) 18 (Min.)		20 (Typ.) 7 (Min.)		16	SM2	ld	7.95						
	◆ MBA-35MH*	3000-4000	DC-700	5.1 0.1	—	8.7	22 (Typ.) 15 (Min.)		14 (Typ.) 8 (Min.)		15	SM2	ld	7.95						
	◆ ALY-44MH	2400-4400	DC-1400	7.5 .20	—	8.9	30 (Typ.) 20 (Min.)		20 (Typ.) 10 (Min.)		—	CB518	ly	18.95						
	◆ ALY-44MHW	1800-4900	DC-1400	7.5 .20	—	9.2	30 (Typ.) 20 (Min.)		14 (Typ.) 8 (Min.)		—	CB518	ly	19.95						
	JMS-1MH	2-500	DC-500	5.75 .10	7.0	8.0	70 55	60 40	44 25	55 42	45 25	35 20	—	BH292	ht	9.45				
	JMS-2MH	20-1000	DC-1000	7.0 .15	8.4	9.5	63 40	50 28	35 20	56 30	47 22	37 20	—	BH292	ht	10.45				
	JMS-5MH	5-1500	DC-1000	5.7 .10	8.0	9.5	67 40	57 25	35 20	60 40	35 18	15 8	—	BH292	ht	11.95				
	◆ LRMS-1MHJ	2-500	DC-500	5.65 .08	7.0	8.0	58 45	44 25	30 20	55 40	36 25	28 17	—	QQQ569	w	8.95				
	◆ LRMS-2MHJ	5-1000	DC-1000	6.72 .08	8.5	9.5	55 40	39 20	22 16	52 35	30 17	18 12	—	QQQ569	w	9.95				
	◆ LRMS-2UMHJ	10-1000	20-500	7.0 .10	8.5	9.5	52 40	43 30	33 25	53 30	44 25	39 22	—	QQQ569	w	14.45				
	◆ LRMS-5MHJ	10-1500	DC-900	5.67 .09	9.0	9.5	58 40	40 20	26 18	50 30	38 18	17 8	—	QQQ569	w	15.95				

L = low range [f_L to $10 f_L$]

M = mid range [$10 f_L$ to $f_U/2$]
m = mid band [$2 f_L$ to $f_U/2$]

U = upper range [$f_U/2$ to f_U]

NOTES:

- Average of conversion loss at center of mid-band frequency ($f_L + f_U/4$)
- σ Standard deviation
- ◆ Aqueous washable. For non-aqueous requirements, LRMS units available in case style QQQ130.
- Non-hermetic
- † Phase detection, positive polarity
- ‡ Conversion loss increases up to 6 dB higher as IF frequency decreases from 5 MHz to DC.
- ⊕ Frequency Specified RMS-42MH m=1000 - 2000 MHz, L=800 - 2100 MHz, U=2100 - 4200 MHz; TUF-2MHSM L=50-100 MHz M=100-500 MHz
- * BLUE CELL™ mixers protected by U.S. Patents 5,534,830 5,640,132 5,640,134 5,640,699
- ** Protected under U.S. Patent 6133525
- *** Prices for quantities 10-49
- A. Environmental specifications and re-flow soldering information available in General Information Section.
- B. Units are non-hermetic unless otherwise noted. For details on case dimensions & finishes see "Case Styles & Outline Drawings".
- C. Prices and Specifications subject to change without notice.
- 1. Absolute maximum power, voltage and current ratings:
1a. RF power 200mW; 1b. Peak IF current, 40mA



NSN GUIDE

MCL NO.	NSN
ROK-186MH	5895-01-392-2276
SRA-1MH	5895-01-391-0113
TFM-3MH	5895-01-302-7047
TFM-42MH	5895-01-408-6093




+13 dBm LO, up to +9 dBm RF

MODEL NO.	FREQUENCY MHz		CONVERSION LOSS dB				LO-RF ISOLATION, dB					LO-IF ISOLATION, dB					IP3@ center band Typ. (dBm)	CASE STYLE	CONNECTION	PRICE \$		
	LO/RF f _L -f _U	IF	Mid-Band			Total Range Max.	L M U			L M U												
			x	m	Max.		Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.	Typ. Min.										
RMS-1MH	2-500	DC-500	5.65	.08	7.0	8.0	58	45	44	25	30	20	55	40	36	25	28	17	—	TT240	w	8.95
RMS-2MH	5-1000	DC-1000	6.72	.08	8.5	9.5	55	40	39	20	22	16	52	35	30	17	18	12	—	TT100	w	9.95
RMS-5MH	10-1500	DC-900	5.67	.09	9.0	9.5	58	40	40	20	26	18	50	30	38	18	17	8	—	TT240	w	15.95
NEW RMS-25MH	5-2500	5-1500	7.0	.20	8.5	9.8	54	28	32	23	32	20	34	23	32	25	28	17	—	TT240	w	9.95
	5-2500	5-2200	7.0	0.1	8.5	9.8	54	28	32	23	32	20	34	23	32	25	28	17	—	TT240	w	7.95
	800-4200	DC-800	5.3	.20	9.0	10.8	35	25	—	—	28	17	18	10	—	—	15	7	—	TT240	w	24.95
SKY-53MHR	2800-5300	DC-500	5.7	.20	—	9.5	28	(Typ.)			15	(Min.)	12	(Typ.)			8	(Min.)	19	BJ398	hp	17.95
SKY-60MH	2500-6000	DC-1500	6.2	.20	—	9.5	28	(Typ.)			17	(Min.)	14	(Typ.)			8	(Min.)	19	BJ398	je	17.95
SYM-11MH	50-2000	50-1000	6.6	.10	8.0	9.9	55	35	44	25	30	20	40	25	36	20	29	20	—	TTT167	x	15.95
SYM-25DMHW	40-2500	DC-1000†	6.6	.10	8.0	9.0	47	32	37	27	35	22	38	28	35	25	38	20	26	TTT167	x	8.95***
SYM-1020MH	1000-2000	DC-800	6.5	.55	—	9.8	32	(Typ.)			20	(Min.)	20	(Typ.)			10	(Min.)	18	TTT167	lq	9.95
SYM-8022MH	800-2200	DC-800	7.6	0.3	—	9.8	26	(Typ.)			18	(Min.)	20	(Typ.)			9	(Min.)	18	TTT167	lp	11.95
TUF-1MHSM	2-600	DC-600	6.3	.12	7.0	8.0	68	50	50	30	43	25	65	45	48	30	37	22	—	NNN150	z	8.25
	50-1000	DC-1000	6.0	.25	7.5	9.0	58	40	47	30	37	25	55	35	47	20	32	18	—	NNN150	z	9.20
	0.15-400	DC-400	5.0	.33	7.0	8.0	60	50	46	30	35	25	60	40	42	25	35	20	—	NNN150	z	10.20
	20-1500	DC-1000	7.0	.25	8.5	9.0	50	40	41	30	35	25	38	25	28	18	20	8	—	NNN150	z	13.45
TUF-11AMHSM	1400-1900	40-500	7.4	.20	8.6	8.6	33	(Typ.)			20	(Min.)	24	(Typ.)			15	(Min.)	—	NNN150	z	21.95
TUF-2500MHSM	400-2500	30-800	7.3	.15	8.5	10.0	32	(Typ.)			24	(Min.)	27	(Typ.)			17	(Min.)	—	NNN150	z	26.95

L = low range [f_L to $10 f_L$]

M = mid range [$10 f_L$ to $f_U/2$]
m = mid band [$2f_L$ to $f_U/2$]

U = upper range [$f_U/2$ to f_U]



pin and coaxial connections see case style outline drawings

PORT	w	x	z	hp	ht	je	jv	lc	ld	lp	lq
LO	1	2	4	5	6	1	1	10	10	3	3
RF	4	1	1	1	3	5	6	5	5	1	2
IF	5	3	2	7	2	7	10	3	3	2	1
GND EXT.	2,3,6	4,5,6	3	2,3,4,6,8	1,4,5	2,3,4,6,8	all others	1,4,7,8,9	1,2,4,6,7,8,9	4,5,6	4,5,6
ISOLATE	—	—	—	—	—	—	—	2,6	—	—	—
DEMO BOARD	TB-03	TB-12	—	TB-11	TB-03	TB-11	—	TB-117	TB-99	—	—



The Design Engineers Search Engine
Provides Actual Data Instantly
At: <http://www.minicircuits.com>

In Stock... Immediate Delivery
For Custom Versions Of Standard Models
Consult Our Applications Dept.

