

TX299K & TX293K

Uncooled 10G InAlGaAs TOSAs



Product Brief



Description

Avago Technologies' 10G Transmit Optical Sub-Assemblies (TOSA) are compliant to the XMD MSA. With class-leading electro-optic performance and exceptionally low power consumption, these TOSAs are designed for integration into SFP, SFP+ and XFP and other transceiver and transponder modules, as well as optical line cards addressing Metropolitan Network applications.

Avagos' 1.3 μm uncooled 10G Fabry-Perot (FP) and Direct Modulated (DML) lasers are suitable for wide-temperature Time-Division-Multiplexing (TDM) and Coarse-wave-length-Division-Multiplexing (CWDM) applications in Access, Metro and LAN/Datacenter applications.

Features & Advantages:

- Low Threshold Current
- Wide Operating temperature -25°C to $+90^{\circ}\text{C}$
- Using InAlGaAs chip technology, FP and DFB chips
- Internal optical isolator
- Supports up to 10.7 Gb/s to 10km (LR1 SONET/ SDH OC-192/STM-64, 10GBE & 10G Fiber Channel)

Ordering Information

Code	Rate	Laser Type	Output power	Package	Operation Temp.
TX299KL	10Gb/s	1310nm FP	-4.5 dBm	LC receptacle	$-25 \sim 90^{\circ}\text{C}$
TX299KS	10Gb/s	1310nm FP	-4.5 dBm	SC receptacle	$-25 \sim 90^{\circ}\text{C}$
TX293KCxxxx	10Gb/s	1310nm DFB	+1 dBm	LC,SC receptacle	$-5 \sim 85^{\circ}\text{C}$
				Pigtailed LC/SC/FC connector	$-5 \sim 95^{\circ}\text{C}$
					$-25 \sim 95^{\circ}\text{C}$
TX293KFxxxx	10Gb/s	1310nm DFB	-2.5 dBm	LC,SC receptacle	$-5 \sim 85^{\circ}\text{C}$
				Pigtailed LC/SC/FC connector	$-5 \sim 95^{\circ}\text{C}$
					$-25 \sim 95^{\circ}\text{C}$
TX293-1xx	10Gb/s CWDM	1270nm, 1290nm, 1310nm, 1330nm CWDM DFB	+1 dBm	LC,SC receptacle	$-5 \sim 75^{\circ}\text{C}$
			-2.5 dBm	Pigtailed LC/SC/FC connector	$-20 \sim 85^{\circ}\text{C}$

For product information and a complete list of distributors, please go to our web site: www.avagotech.com

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries.
CyOptics and the CyOptics logo are trademarks of CyOptics, Inc. in the United States and other countries.
Data subject to change. Copyright © 2005-2013 CyOptics, Inc. All rights reserved.
AV02-4140EN - June 5, 2013

