


THIS DRAWING IS A CONTROLLED DOCUMENT
REV 01 1906079



Left Side
Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Slate
Geom. Spec: N/A

Fiber Path
A - _____ - B
B - _____ - A

Right Side
Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

- Notes:
- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
 - 2 Includes dust caps (not shown on print).
 - 3 IL tested at 1300nm.
 - 4 Label 2 will not be present on any cable assembly less than 5 meters long.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS TO BE USED ONLY BY THE PERSONNEL TO WHOM IT HAS BEEN DISCLOSED. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	4/21/2009	-	JB			
P	LTR	REVISION	RECORD	DATE	DIN	APVD			

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± .
	1 PLC ± .
	2 PLC ± .
	3 PLC ± .
	4 PLC ± .

Restricted To:

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
CHK	James Barry		
APVD	James Barry		
NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 1906079	1 of 4
			REV A

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	4/21/2009	-	JE
P	LTR		REVISION RECORD	DATE	DIN	AP

Qty	U of M	Description	Item No.
2	piece	Trace Label	10
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	SC Duplex Clip	7
AR	meter	2 Fiber, XG-50/125, 2.0mm, Twinzip, Aqua, OFNR (Riser)	6
2	piece	2.5mm ferrule cover	5
2	piece	SC Simplex Housing, Beige	4
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	3
1	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

DIMENSIONS: meters 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± . 4 PLC ± .		P/N Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
				CHK James Barry		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
Restricted To:		APVD James Barry		NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex Secure to SC-Duplex					
		SCALE NTS				DRAWING NO C- 1960679			

5- Restricted To:

THIS DRAWING IS A CONTROLLED DOCUMENT

DWG NO

CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	4/21/2009	-
P	LTR	REVISION RECORD		DATE	DIN

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

Restricted To:

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
B6C-ND

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1




Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.



DIMENSIONS:
meters

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 P.L.C.
1 P.L.C.
2 P.L.C.
3 P.L.C.
4 P.L.C.

±
±
±
±
±

DIN Cable Assy Configurator

OK James Barry

APVD James Barry

NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex
Secure to SC-Duplex

SCALE NTS

SIZE A2

DRAWING NO C- 1906079

SHEET 4 of 4

REV A

MATERIAL HEAT TREAT

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

D

C

B

A