


D

C

B

A



MTC100-XHX-XXX-XXX

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 19DEC2013	TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK K.HOGAN 12-19-13			
		APVD K.HOGAN 12-19-13	NAME SHELL, PLUG AND RECEPTACLE MTC100 SERIES		
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=MTC100-XHX-XXX-XXX
0 PLC ± -		—	RESTRICTED TO		—
1 PLC ± -		—	SCALE NTS		
2 PLC ± .02 [0.5]		—			
3 PLC ± .005 [0.13]		—	SHEET 1 of 3		
4 PLC ± -		—			
ANGLES ± -		—	REV W		
FINISH		—			
MATERIAL		WEIGHT	CUSTOMER DRAWING		

1. PART NUMBER VARIABLES: (NOT ALL POSSIBLE CONFIGURATIONS SHOWN ON THIS DRAWING ARE AVAILABLE AS STANDARD PRODUCTS. PLEASE CHECK WITH RAYCHEM TO CONFIRM AVAILABILITY.)

MTC100-XHX-XXX-XXX

- MODIFICATIONS (see table I) (THIS SPACE BLANK IF NO MODIFICATION IS APPLICABLE)

- 1= W/O CABLE CLAMP AND W/O EARS ON SHELL
2= WITH CABLE CLAMP AND EARS ON SHELL
3= W/O CABLE CLAMP AND WITH EARS
4= WITH FLAT CABLE CLAMP (SEE VIEW V) AND EARS ON SHELL

- 1= BLACK ANODIZED (WHITE MARKING)
2= ELECTROLESS NICKEL (BLACK MARKING)
3= CADMIUM OVER NICKEL UNDERPLATE (BLACK MARKING)

- P= PLUG
 R= FLANGELESS RECEPTACLE
 F= FLANGED RECEPTACLE: STANDARD ("J" TYPE) HAS NON CONDUCTIVE FLUOROSILICONE GASKET
 SHIELDED ("S" TYPE) HAS CONDUCTIVE FLUOROSILICONE GASKET

- 1= 1 INCH
2= 2 INCH

- J= STANDARD TYPE
S= SHIELDED

- Y= SPECIAL TYPE: REFER TO INDIVIDUAL SPECIFICATION CONTROL DRAWINGS FOR DESCRIPTIONS

2. MATERIAL:

- | | |
|---------------------------------------|---|
| A) SHELL | ALUMINUM ALLOY PER ASTM B85 |
| B) RETENTION CLIP | COPPER ALLOY 172 PER ASTM B194 |
| C) ADAPTER SCREW OR CAP SCREW | STAINLESS STEEL PER SAE-AMS-QQ-S-763, 300 SERIES |
| D) ADAPTER NUT OR
RETAINER BUSHING | STAINLESS STEEL PER SAE-AMS-QQ-S-763, 300 SERIES |
| E) PANEL OR LOCK WASHER | STAINLESS STEEL PER SAE-AMS-QQ-S-763 OR ASTM B240, 300 SERIES |
| F) KEYING PIN | HIGH GRADE POLYARYLENE THERMOPLASTIC, MOLDED |
| G) KEY PINS INSERT | HIGH GRADE POLYARYLENE THERMOPLASTIC, MOLDED |
| H) CLAMP BAR | STAINLESS STEEL PER SAE-AMS-QQ-S-763, 300 SERIES |
| J) CLAMP INSERT | SILICONE ELASTOMER PER MIL-R-25988 |
| K) CAPTIVE SCREW | STAINLESS STEEL PER SAE-AMS-QQ-S-763, 300 SERIES |
| L) RETAINING RING | COPPER ALLOY 172 PER ASTM B194 |

3. FINISH:

FINISH:	APPLIES TO NICKEL PLATED CONNECTORS	APPLIES TO CADMIUM PLATED CONNECTORS	APPLIES TO BLACK ANODIZED CONNECTORS
A) SHELL	NICKEL PLATED PER SAE-AMS-C-26074 CLASS 3, GRADE B	CADMIUM PLATED PER SAE-AMS-QQ-P-416 OVER NICKEL UNDERPLATE	BLACK ANODIZED PER MIL-A-8625, TYPE II, CLASS 2
B) RETENTION CLIP	NICKEL PLATED PER SAE-AMS-C-26074 CLASS 2, .00002 MINIMUM	CADMIUM PLATED PER SAE-AMS-QQ-P-416	NICKEL PLATED PER SAE-AMS-C-26074 CLASS 2, .00002 MINIMUM
C) ADAPTER OR CAP SCREW	PASSIVATED PER SAE-AMS-2700	CADMIUM PLATED PER SAE-AMS-QQ-P-416	PASSIVATED PER SAE-AMS-2700
D) ADAPTER NUT OR RETAINER BUSHING	PASSIVATED PER SAE-AMS-2700	CADMIUM PLATED PER SAE-AMS-QQ-P-416	PASSIVATED PER SAE-AMS-2700
E) PANEL OR LOCK WASHER	PASSIVATED PER SAE-AMS-2700	CADMIUM PLATED PER SAE-AMS-QQ-P-416	PASSIVATED PER SAE-AMS-2700
F) CLAMP BAR	PASSIVATED PER SAE-AMS-2700	CADMIUM PLATED PER SAE-AMS-QQ-P-416	PASSIVATED PER SAE-AMS-2700
G) CAPTIVE SCREW	PASSIVATED PER SAE-AMS-2700	CADMIUM PLATED PER SAE-AMS-QQ-P-416	PASSIVATED PER SAE-AMS-2700
H) RETAINING RING	NICKEL PLATED PER SAE-AMS-C-26074	CADMIUM PLATED PER SAE-AMS-QQ-P-416	NICKEL PLATED PER SAE-AMS-C-26074

4. FOR MOUNTING / MATING AND KEYING INFORMATION, SEE RAYCHEM DRAWING D652-0012.

5. DUST CAP SUPPLIED WITH EACH PLUG OR RECEPTACLE.
NO DUST CAPS ARE SUPPLIED WHEN SHELLS
ARE SHIPPED TO CUSTOMER SPECIFICATION
NUMBER 991006.

6. APPROPRIATE PART NUMBER AND DATE CODE ARE STAMPED APPROXIMATELY AS SHOWN.

7. THESE PARTS MEET THE REQUIREMENTS OF RAYCHEM SPECIFICATION C-6111.


8. FLANGED RECEPTACLE CONNECTORS PROPERLY MATED AND TORQUED TO 9 INCH POUNDS WILL EXHIBIT AN AIR LEAK RATE NOT EXCEEDING .5 CC / SECOND AT 30 PSI AND 25° C. (APPLICABLE ONLY TO FLANGED RECEPTACLES WITH PIN INSERTS)

9. THESE ITEMS ARE SUPPLIED UNASSEMBLED.


10. SEE TABLE II & TABLE 4 SHEET 3, WEIGHTS ARE WITHOUT DUST CAP.

1 THIS RECEPTACLE IS REAR PANEL MOUNTED BY REMOVING AS MANY PANEL WASHERS AS REQUIRED TO ACCOMMODATE THE THICKNESS OF THE PANEL BEING USED. (SEE TABLE III)

12 RECEPTACLE ADAPTER SCREWS (CAP SCREWS) ARE TO BE TORQUED TO 15±1 INCH-LBS (1.0±0.07 N-M)




FLAT CABLE CLAMP
VIEW "V"



HOLE CONFIGURATION FOR
ALL "S" TYPE SHELLS AND
FLANGED "J" TYPE RECEPTACLE SHELLS


VIEW "Z"



APPLIES TO -014 MODIFICATION
(see table I)

VIEW “W”

TABLE III		
PANEL THICKNESS	NUMBER OF PANEL WASHERS FOR EACH FASTENER	
0.031/0.036 [0.8]/[0.9]	2	
0.062/0.067 [1.5]/[1.7]	1	
0.093/0.097 [2.3]/[2.4]	0	



MTC50 HARDWARE
APPLIES TO -020 MODIFICATION
(see table 1)

VIEW 

TABLE I (MODIFICATIONS)	
MODIFICATION DASH NUMBER	DESCRIPTION
—001	SAME AS STANDARD ASSEMBLY WITH EARS EXCEPT WITHOUT CABLE CLAMPS
—007	SAME AS STANDARD ASSEMBLY EXCEPT METAL PARTS ARE PLATED CADMIUM OVER NICKEL, SUPPLIED WITH MTC50 MOUNTING/ MATING HARDWARE (SEE VIEW "Y")
—014	SAME AS STANDARD EXCEPT ADDITIONALLY TRIANGULAR KEYING PINS INCLUDED (SEE VIEW "W")
—020	SAME AS STANDARD EXCEPT SUPPLIED WITH MTC50 MOUNTING/MATING HARDWARE (SEE VIEW "Y")
—028	SAME AS STANDARD ASSEMBLY EXCEPT SUPPLIED WITHOUT HARDWARE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 19DEC2013 CHK K.HOGAN 12-19-13		 TE Connectivity			
DIMENSIONS: INCHES [mm]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME SHELL, PLUG AND RECEPTACLE MTC100 SERIES			
		0 PLC ± - 1 PLC ± - 2 PLC ± .02 [0.5] 3 PLC ± .005 [0.13] 4 PLC ± ± - ANGLES					
MATERIAL		FINISH					
-		-					
		DWN C.C.THOMAS 19DEC2013 CHK K.HOGAN 12-19-13		SIZE A2			
		PRODUCT SPEC -		CAGE CODE 00779			
		APPLICATION SPEC -		DRAWING NO C=MTC100-XXH-XXX-XXX			
		WEIGHT -		RESTRICTED TO -			
		CUSTOMER DRAWING				SCALE NTS	
						SHEET 2 of 3	
						REV W	

D

D

C

C

B


B

A

A

THE FOLLOWING TABLE CONSISTS OF WEIGHTS FOR THESE SPECIFIC PART NUMBERS.

TABLE II 	
PART NUMBER	WEIGHT MAXIMUM GRAMS
MTC100-JH1-F32	30.8
MTC100-JH1-P32	23.8
MTC100-JH1-R32	27.3
MTC100-JH2-F32	43.7
MTC100-JH2-P32	34.2
MTC100-JH2-R32	38.3
MTC100-SH1-F33	24.2 *
MTC100-SH1-P33	16.1 *
MTC100-SH1-R33	20.3 *
MTC100-SH2-F33	32.3 *
MTC100-SH2-P33	22.7 *
MTC100-SH2-R33	27.0 *

TABLE 4 	
PART NUMBER	WEIGHT MAXIMUM GRAMS
MTC100-JH1-F22	30.8
MTC100-JH1-P22	23.8
MTC100-JH1-R22	27.3
MTC100-JH2-F22	43.7
MTC100-JH2-P22	34.2
MTC100-JH2-R22	38.3
MTC100-SH1-F23	24.2 *
MTC100-SH1-P23	16.1 *
MTC100-SH1-R23	20.3 *
MTC100-SH2-F23	32.3 *
MTC100-SH2-P23	22.7 *
MTC100-SH2-R23	27.0 *

* = WEIGHT DOES NOT INCLUDE CABLE CLAMP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

C.C.THOMAS

19DEC2013

CHK

K.HOGAN

12-19-13

APVD

K.HOGAN

12-19-13

PRODUCT SPEC

APPLICATION SPEC

MATERIAL

-

FINISH

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

SHELL, PLUG AND RECEPTACLE
MTC100 SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

MTC100-XHX-XXX-XXX

-

SCALE

NTS

SHEET

3 of 3

REV

W

MTC100-XHX-XXX-XXX