











注記: NOTES:

1. 材質: 銅合金 (板厚: 0.15)
MATERIAL: COPPER ALLOY (THICKNESS: 0.15)
2. メッキ仕様
FINISHES
錫メッキ: 0.4 マイクロメートル以上
TIN PLATING: 0.4 MICROMETER MINIMUM
リフロー処理 (前めっき)
REFLOW TREATMENT (PRE-PLATED)
ニッケル下地メッキ: 0.1 マイクロメートル以上
NICKEL (UNDER PLATING): 0.1 MICROMETER MINIMUM
リフロー処理 (前めっき)
REFLOW TREATMENT (PRE-PLATED)
3. 適合ハウジング: 503473シリーズ
APPLICABLE HOUSING: 503473 SERIES
4. 適用電線範囲: AWG#26~28 (0.079~0.141mm)
WIRE RANGE: AWG#26~28 (0.079~0.141mm)
5. 絶縁被覆外径: $\phi 0.93 \sim \phi 1.14$
INSULATION RANGE: $\phi 0.93 \sim \phi 1.14$
6. 圧着仕様については、圧着仕様書CS-503485-001を参照願います。
PLEASE REFER TO CRIMP SPECIFICATION CS-503485-001.
図示の斜線部の範囲は接点部のため、傷、打痕、汚れなどを付けないようにして下さい。
PLEASE DON'T DAMAGE, DON'T DENT, AND DON'T MAKE IT DIRTY.
BECAUSE THE RANGE IN THE SHADED PORTION SHOWN IN FIGURE IS THE CONTACT AREA.
8. 適用圧着工具: 578069-3000 (自動圧着機)
APPLICABLE CRIMPING TOOL: 578069-3000 (AUTOMATIC)
9. ELV及びRoHS適合品
ELV AND RoHS COMPLIANT.



SECTION A-A
(SCALE 20:1)



SECTION B-B
(SCALE 20:1)

連鎖状 CHAIN	503485-0000
端子形状 TERMINAL CONFIGURATION	オーダー番号 ORDER No.
コネクタシリーズ番号 CONNECTOR SERIES No.	503485-****

RELEASED EC NO: J2010-0155 DRWN:HKOBAYASHI CHKD:SSA1003 APPR:NUK1TA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		10 UNDER	± 0.2	DRAWN BY H.KOBAYASHI	DATE 2009/7/24	TITLE 3.7 MULTIPLE CONN. PLUG CRIMP TERMINAL					
		10 OVER 30 UNDER	± 0.25	CHECKED BY S.SATO	DATE 2009/7/24						
		30 OVER	± 0.3	APPROVED BY N.UKITA	DATE 2009/7/24						MOLEX INCORPORATED
		ANGULAR ±1 °		MATERIAL NO. —#—		DOCUMENT NO. SD-503485-001					SHEET NO. 1 OF 1
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
		REV									