

[illegible]

PANDUIT PART NO.	DESCRIPTION	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	MINIMUM LOOP TENSILE 2"/MIN. lbs. (N)	WEIGHT PER TIE OUNCES (g)
		MIN. in. (mm)	MAX. in. (mm)							
DT14EH-LO	48 IN. LONG TIE	.020 (.51)	14.0 (355)	.500 (12.70)	.059 (1.50)	.490 (12.45)	.718 (18.24)	48.0 (1219)	250 (1112)	1.2 (33)
DT15EH-LO	53 IN. LONG TIE	.020 (.51)	15.0 (381)	.500 (12.70)	.059 (1.50)	.490 (12.45)	.718 (18.24)	53.0 (1346)	250 (1112)	1.3 (36)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DURA-TY
EXTRUDED CABLE TIES (EXTRA HEAVY)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ±	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY FAB

MAT'L;
STRAP & HEAD -
BLACK ACETAL
EACH HEAD HAS TWO,
TYPE 302 STAINLESS
STEEL BARBS

SCALE N/A

DRAWING NO.

SS-27518

DWG
A
SIZE

1	8/31/07	JABO		REVISED METRIC DIM 'A' & 'C'	SS-27518	1			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		