


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CF	39		A	REVISION PER ECO-05-006188	29JUN05	TW	RC



- NOTES:
- PACKAGED IN PRINTED ZIPLOCK POLYBAG.
 - LABEL ON POLYBAG TO READ AS FOLLOWS:


621803-__ XX'= LENGTH
XX' DB9 F/F EXTENSION PER TABLE
 - WRAP FOIL OVER PRE-MOLD 360° FROM CONNECTOR SHELL TO SHELL.
 - IF USING ALUMINUM MYLAR FOIL, ALUMINUM MUST BE FACING INWARD.
 - THIS PRODUCT IS PRODUCED IN COMPLIANCE WITH ANSI/ASQC Z1.4-1993, TO AN INSPECTION LEVEL III, WITH A NORMAL SAMPLING PLAN.
 - TEST REQUIREMENT:
CONTINUITY RESISTANCE: SEE TABLE.
INSULATION RESISTANCE: 50 M ohm MIN.
HI-POT TEST: DC 300V/0.01 Sec MIN.
 - PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ENVIRONMENTAL STANDARD 230-702.

621803-3	180.0 $\pm$ ^{6.00} _{2.00}	15	3 OHM MAX
621803-2	120.0 $\pm$ ^{6.00} _{2.00}	10	2 OHM MAX
621803-1	72.0 $\pm$ ^{6.00} _{2.00}	6	1 OHM MAX
TYCO P/N	"L" LENGTH	LABEL XX'	CONTINUITY RESISTANCE

PIN ASSIGNMENT :

P1	1	2	3	4	5	6	7	8	9	SHELL
										DRAIN
P2	1	2	3	4	5	6	7	8	9	SHELL

AR	MR	UL2464 28AWG*9C+DRAIN+AL/MYLAR, COLOR: BEIGE(BG01).	7
4	PC	#4-40 THUMBSCREW.	6
AR	KG	MOLD PVC, 30P, COLOR: BEIGE(BG01).	5
AR	MR	COPPER FOIL, W: 30.0MM, 360° SOLDERED.	4
AR	KG	INNER MOLD PE.	3
AR	KG	OVER MOLD PVC, 40P, COLOR: BEIGE(BG01).	2
2	PC	DB9 FEMALE, CONTACT: GOLD FLASH, SHELL: NICKEL PLATED, INSULATION COLOR: BLACK.	1
Q'TY	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.EISENTRAUT 11-20-96	tyco Tyco Electronics Corporation Electronics Harrisburg, Pa 17105-3608			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK R.CAPP 11-21-96	NAME CABLE ASSY, DB9 FEMALE TO FEMALE, OVERMOLDED —			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD D.WILSON 11-21-96				
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		WEIGHT —				
MATERIAL —	FINISH —	SIZE A3	CAGE CODE 00779	DRAWING NO C-621803	RESTRICTED TO —	
CUSTOMER DRAWING				SCALE N.T.S	SHEET 1 OF 1	REV A