


AT-CUT CRYSTAL UNIT (Metal-can Type)

RoHS compliant

HC-49/U-S





FEATURES

- Available in Tape and reel form.
- Suitable for various applications such as communication devices, AV devices and measuring instruments.

Taping dimension : 2000pcs/Ammo pack [mm]

DIMENSION [mm]



STANDARD SPECIFICATIONS

Item	Model	HC-49/U-S	Conditions
Nominal Frequency	f_0	3.5MHz~30.0MHz (Fundamental)	Need to contact us for the available frequency
		30.0MHz~50.0MHz (3rd Overtone)	
Frequency Tolerance	$\Delta f/f_0$	$\pm 30\text{ppm}$	at 25°C
Frequency Tolerance over Operating Temperature Range	$\Delta f/f_0$	below 6.0MHz: $\pm 50\text{ppm}$	-10°C~+60°C
		above 6.0MHz: $\pm 30\text{ppm}$	
Operating Temperature Range	T_{OPR}	-20°C~+70°C	
Storage Temperature Range	T_{STR}	-40°C~+85°C	
Motional (series) resistance	R_1	Refer to the following table	at 25°C
Load capacitance	C_L	Fundamental: 10.0pF~∞ 3rd Overtone: 5.0pF~∞	Need to specify your requirement
Shunt capacitance	C_0	7.0pF Max.	
Level of drive	D_L	100 μW	
Insulation Resistance	I_R	500MΩ Min.	DC100V±15V
Aging (first year)	$\Delta f/f_0$	$\pm 5\text{ppm Max.}$	25°C±3°C

MOTIONAL (SERIES) RESISTANCE (R_1)

Frequency Range	$3.5\text{MHz} \leq f_0 < 4.0\text{MHz}$	$4.0\text{MHz} \leq f_0 < 6.0\text{MHz}$	$6.0\text{MHz} \leq f_0 < 10\text{MHz}$	$10\text{MHz} \leq f_0 < 14\text{MHz}$	$14\text{MHz} \leq f_0 < 30\text{MHz}$	$30\text{MHz} \leq f_0 < 36\text{MHz}$	$36\text{MHz} \leq f_0 \leq 50\text{MHz}$
Mode	Fundamental	Fundamental	Fundamental	Fundamental	Fundamental	3rd Overtone	3rd Overtone
R_1	200 Ω Max.	150 Ω Max.	100 Ω Max.	80 Ω Max.	50 Ω Max.	140 Ω Max.	100 Ω Max.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Citizen:

[HC49US-18.432MABJB](#) [HC49US-12.288MABJB](#) [HC49US-16.384MABJB](#) [HC49US-50.000MABJB](#) [HC49US-21.47727MABJB](#) [HC49US-40.000MABJB](#) [HC49US-13.560MBBIB](#) [HC49US-33.8688MABJB](#) [HC49US-49.152MABJB](#) [HC49US-18.000MABJB](#) [HC49US-8.192MABJB](#) [HC49US-15.360MABJB](#) [HC49US-3.6864MABKB](#) [HC49US-27.000MABJB](#) [HC49US-12.000MABJB](#) [HC49US-4.000MABJB](#) [HC49US-19.6608MABJB](#) [HC49US-24.000MABJB](#) [HC49US-16.000MABJB](#) [HC49US-9.216MABJB](#) [HC49US-5.000MABJB](#) [HC49US-25.000MABJB](#) [HC49US-32.000MABJB](#) [HC49US-8.000MABJB](#) [HC49US-6.176MABJB](#) [HC49US-20.000MABJB](#) [HC49US-14.31818MABJB](#) [HC49US-4.9152MABJB](#) [HC49US-4.194304MABJB](#) [HC49US-10.000MABJB](#) [HC49US-48.000MABJB](#) [HC49US-9.8304MABJB](#) [HC49US-22.1184MABJB](#) [HC49US-14.7456MBJTR](#) [HC49US-6.000MABJB](#) [HC49US-16.000MBBQB](#) [HC49US-7.680MABJB](#) [HC49US-17.734475MABJB](#) [HC49US-11.0592MABJB](#) [HC49US-3.579545MABJB](#) [HC49US-13.500MABJB](#) [HC49US-28.224MABJB](#) [HC49US-49.152MABJ](#) [HC49US-11.2896MABJB](#) [HC49US-19.6608MABJTR](#) [HC49US-6.144MABJB](#) [HC49US-7.3728MABJB](#) [HC49US-11.0592MBBQB](#) [HC49US-24.000MABKB](#) [HC49US-24.576MABJB](#)