





BRASS Finish: Zinc qq-z-325, type II, cl 3-Clear Chromate				
LENGTH	FOR #4 SCREW	FOR #6 SCREW	FOR #8 SCREW	FOR #10 SCREW
	A: .114 (2.9) B: 1/4 (6.4)	A: .140 (3.5) B: 1/4 (6.4)	A: .166 (4.2) B: 1/4 (6.4)	A: .192 (4.9) B: 3/8 (9.5)
1/4 (6.4)	BRSS4-2	BRSS6-2	BRSS8-2	BRSS10-2
3/8 (9.5)	BRSS4-3	BRSS6-3	BRSS8-3	BRSS10-3
1/2 (12.7)	BRSS4-4	BRSS6-4	BRSS8-4	BRSS10-4
5/8 (15.9)	BRSS4-5	BRSS6-5	BRSS8-5	BRSS10-5
3/4 (19.1)	BRSS4-6	BRSS6-6	BRSS8-6	BRSS10-6
1 (25.4)	BRSS4-8	BRSS6-8	BRSS8-8	BRSS10-8

ALUMINUM Finish: Iridite MIL-C-5541 - Gold #14				
LENGTH	FOR #4 SCREW	FOR #6 SCREW	FOR #8 SCREW	FOR #10 SCREW
	A: .114 (2.9) B: 1/4 (6.4)	A: .140 (3.5) B: 1/4 (6.4)	A: .166 (4.2) B: 1/4 (6.4)	A: .192 (4.9) B: 3/8 (9.5)
1/4 (6.4)	ALSS4-2	ALSS6-2	ALSS8-2	ALSS10-2
3/8 (9.5)	ALSS4-3	ALSS6-3	ALSS8-3	ALSS10-3
1/2 (12.7)	ALSS4-4	ALSS6-4	ALSS8-4	ALSS10-4
5/8 (15.9)	ALSS4-5	ALSS6-5	ALSS8-5	ALSS10-5
3/4 (19.1)	ALSS4-6	ALSS6-6	ALSS8-6	ALSS10-6
1 (25.4)	ALSS4-8	ALSS6-8	ALSS8-8	ALSS10-8

A			CHANGED FILE NO. AND TITLE BLOCK			SM 03.22.02		
REV			DESCRIPTION			ENGR DATE		
TITLE:			ROUND SPACERS			  DWG IN IN (MM) 		
TOLERANCES UNLESS NOTED .XX= ± 0.010 .XXX= ± 0.005 FRAC= $\pm 1/64$ ANG= $\pm 1^\circ$			FILE # ALSS-BRSS			DWN: J.B. APP:		
MAT'L: SEE TABLE			RE: RICHCO, INC.			DT: 09-31-95 DT:		
PART # SEE TABLE			RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060			PRINT TYPE CA		