



THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2005, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.25	W
MAX INPUT POWER	0.5	W
IMPEDANCE	8±15%	OHM
OUTPUT SPL @ 0.1W/0.1M (AT 0.8, 1.0, 1.2, 1.5 kHz)	92±3	dBA
DISTORTION (MAX.)	5%	—
RESONANT FREQUENCY	600±120	Hz
FREQUENCY RANGE	600 ~ 9000	Hz
HOUSING MATERIAL	ABS	—
CONE MATERIAL	MYLAR	—
MAGNET MATERIAL	N35	—
OPERATING TEMPERATURE	-20 ~ +55	°C
WEIGHT	6	grams




REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	2/23/06	



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

FILE NAME
AS03608MR-2-R.DWG

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS, TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.		 projects® unlimited		Dayton , Ohio	
		SPEAKER			
APPROVALS		DATE			
DRAWN J.A.F.		02/06			
CHECKED E.P.		02/06			
APPROVED B.R.		02/06			
DO NOT SCALE DRAWING		SIZE A		DRAWING NO. AS03608MR-2-R	
		SCALE: N.T.S.		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[AS03608MR-2-R](#)