




(1,27 mm) .050"

**TFC SERIES**

COST SAVING RELIABLE HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/TFC

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27 µm) Ni

Current Rating:

2.9 A per pin

(1 pin powered per row)

Voltage Rating:

350 VAC mated with SFC

Operating Temp Range:

-55°C to +125°C

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (03-25)

(0,15 mm) .006" max (30-50)

Mates with:
SFC, SFSD, SFSDT

MATED HEIGHTS

LEAD STYLE		MATED HEIGHT*
TFC	SFC	
-01	-T1	(5,97) .235
-11		(7,75) .305
-21		(9,53) .375
-31		(11,43) .450
-02	-T2	(6,35) .250
-12		(8,13) .320
-22		(9,91) .390
-32		(11,81) .465

*Processing conditions will affect mated height.

Shrouded body for blind mating

(1,27 mm x 1,27 mm)
.050" x .050"
micro pitch

Choice of eight body heights

Surface Mount or Through-hole

Alignment pin option available

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Other sizes
- Contact Samtec.

TAPE & REEL AVAILABILITY

No tooling charges.
Minimum order is the lesser of a full reel quantity or 125 pieces.
Order any quantity above minimum.
In-house design, manufacture.
Quick turn-around.

Call Samtec for specifications and ordering information.

Note: Some sizes, styles and options are non-standard, non-returnable.

TFC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	OPTION
03, 04, 06, 08 (Lead Style -01 & -02 only)			-X1 = Through-hole	-F = Gold flash on post, Matte Tin on tail		-RA = Right Angle (-01 only)
05, 07, 10, 15, 20, 25, 30, 35, 40, 45, 50 (Standard sizes)			-X2 = Surface Mount	-L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail		-A = Alignment Pin
						-LC = Locking Clip (Manual Placement required) (not available with -RA)
						-K = (6,75 mm) .266" DIA Polyimide film Pick & Place Pad
						-P = Plastic Pick & Place Pad (5 positions min.)
						-TR = Tape & Reel (-X2 only)

TH LEAD STYLE	A	B
-01	(5,59) .220	(3,38) .133
-11	(7,37) .290	
-21	(9,14) .360	(3,30) .130
-31	(11,05) .435	

SMT LEAD STYLE	A	B
-02	(5,72) .225	(3,38) .133
-12	(7,49) .295	
-22	(9,27) .365	(3,30) .130
-32	(11,18) .440	

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685