







Copyright FCI.

PLATING CONTACT AREA:		
DASH NR:	PERFORMANCE LEVEL	
-1YY	TELCORDIA CO	OBsolete
-2YY	CUSTOMER SPECIAL	OBsolete
-3YY	CUSTOMER SPECIAL	OBsolete
-9YY	TELCORDIA CO	OBsolete
-2YYLF	CUSTOMER SPECIAL	OBsolete
-9YYLF	TELCORDIA CO	OBsolete
-1YYLF	TELCORDIA CO	OBsolete
-3YYLF	CUSTOMER SPECIAL	

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
89039-X01LF	1.6	2.90
89039-X11LF	2.4	3.53



PRODUCT AFTER PC BOARD APPLICATION.



SEE NOTE 4.

RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 PRODUCT MARKING: PARTNUMBER & BATCH ID.
 - 5 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 6 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION.
 - 7 THE PRODUCT SPECIFICATION GS-12-453.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI  www.fciconnect.com	
ltr	ecn no	dr	date	linear	0.X ±0.30		projection 	title RA FEMALE POWER RECEPTACLE 12mm PRESS PEG		
H	DG04-0104	CLU	2004-12-23		0.XX ±0.15					
J	DG07-0458	CEN	2007-11-15		0.XXX ±0.05					
K	DG08-0171	TER	2008-08-26	angles	0' ±2'		 MM 	product family		code
L	NI1-0131	AZH	2011-05-09	dr	H.BOUWKNEGT	1993-03-05		METRAL		
M	ELX-N-004585	AZH	2011-07-20	engr	H.BOUWKNEGT	1993-03-05		size	dwg no	
N	ELX-N-006420	AZH	2011-09-29	chr	J.WINTJES	1993-03-05	scale	A2	89039	sheet
				appd	H.BOUWKNEGT	1993-03-05	5:1			1 of 2
sheet index		revision sheet		N						
				1-2						






Copyright FCI.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY	TELCORDIA CO
-2YY	CUSTOMER SPECIAL
-3YY	CUSTOMER SPECIAL
-9YY	TELCORDIA CO
-2YYLF	CUSTOMER SPECIAL
-9YYLF	TELCORDIA CO
-1YYLF	TELCORDIA CO
-3YYLF	CUSTOMER SPECIAL



OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE
OBSELETE

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM'A*
89039-X02LF	1.6	2.90
89039-X12LF	2.4	3.53



PC BOARD THICKNESS ±0.20
SEE TABLE

PRODUCT AFTER PC BOARD APPLICATION.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

- NOTES:
- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
 - 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
 - 3 INDICATED HOLES ARE UNPLATED.
 - 4 PRODUCT MARKING: PARTNUMBER & BATCH ID.
 - 5 SET BACK FOR PRESS BLOCK.
 - 6 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 - 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - 8 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
 - 9 THE PRODUCT SPECIFICATION GS-12-453.

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
ltr	ecn no	dr	date	linear	0.X ±0.30		projection		www.fciconnect.com																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																							
N	ELX-N-006420	A.ZH	2011-09-29		0.XX ±0.15				title	RA FEMALE POWER RECEPTACLE 12mm PRESS PEG																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																						
					0.XXX ±0.05																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																											
				angles	0° ±2'			MM	product family METRAL		code																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																					
				dr	H.BOUWKNEGT	1993-03-05			size	dwg no	sheet																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																					
				enrg	H.BOUWKNEGT	1993-03-05						scale	A2	89039	2 of 2																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
				chr	J.WINTJES	1993-03-05	5:1																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																									