

Series 123 Tubular Solenoid



GENERAL DESCRIPTION

● DC operated



● Noise reduction feature

● Tubular solenoid

PERFORMANCE


Electrical	ITEM	SPECIFICATION
	Closed power (continuous ratings)	13.0W
	Maximum permissible voltage	160V DC
	Dielectric strength	1KV RMS 50Hz
	Insulation	1KV
Mechanical	Weight	Total: 295g Plunger: 70g
	Ambient temperature	The information given on this page is based on a working temperature of 20°C.
	Force/stroke curve	This force stroke curve shows average performance only with coil at ambient temperature. In addition to normal manufacturing tolerances, deviations can be expected at some voltages due to the coil winding tolerances.

FORCE/STROKE CURVE AND RESPONSE TIME



DIMENSIONS (mm)

Push type - shown energised



COIL DATA

Pull Type	Push Type	Resistance (20°C) Ω ±10%	Cont. (100%) Vdc	50% Vdc	25% Vdc	10% Vdc
123 420 610 540	123 420 620 540	2.77	6	8.5	12	19
123 420 610 620	123 420 620 620	11.07	12	17	24	38
123 420 610 720	123 420 620 720	44.3	24	34	48	76
Watts at 20°C			13	26	52	130
Max. on time (Secs)			∞	390	60	18

Other voltages available on request

Duty cycle (%) =

“ON” time

“ON” time + “OFF” time

x 100%

