





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER ECO 12-010940	7-31-12	CT	DH
			C	REVISED PER ECO-14-017030	24NOV14	MGM	CT



- △ MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING AND CHICKLET: LCP, COLOR: BLACK
- △ FINISH:
CONTACT: MATING AREA: 1.27μm MIN GOLD OVER
1.27μm MIN NICKEL
- △ FINISH:
COMPLIANT PIN AREA: 0.38μm MIN BRIGHT TIN LEAD OVER
1.27μm MIN NICKEL
- △ FINISH:
COMPLIANT PIN AREA: 0.38μm MIN MATTE TIN OVER
1.27μm MIN NICKEL
- △ --
- △ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △ REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.



2	4	2102315-2
2	3	2102315-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BELACK 24JUN2009	TE TE Connectivity	
DIMENSIONS:		CHK A. TSANG 6-24-2009		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. McALONIS 6-24-2009	NAME Fortis Zd, 3-PAIR, 10-COLUMN, R/A, CENTER MODULE ASSEMBLY, SINGLE ENDED	
	0 PLC ±0.13	PRODUCT SPEC	SIZE	
	1 PLC ±0.05	108-2409	CAGE CODE	
	2 PLC ±	APPLICATION SPEC	DRAWING NO	
	3 PLC ±	114-13267	RESTRICTED TO	
MATERIAL	4 PLC ±	WEIGHT	A100779C=2102315	
	FINISH	~11.16g	REV C	
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	