







FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE

POSITION 1


NOTE 3

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family CONAN
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM scale 5:1 	title
A	V91072	EPK	5/6/99	angles	.XX±.01/.3		CONAN™ CONNECTOR
B	M06-0232	AGS	06/12/06	linear	.xxx±.005/.13 .xxx±.0020/.051		RECEP. ASS'Y (BLACK)
				dr	E.KROPIEWNICK 5/6/99		dwg no
				enr	D. WHITING 5/6/99		sheet 1 of 3 size
				chr	D. WHITING 5/6/99		98209 A3
				app	D. WHITING 5/6/99		type Product Customer Drawing
sheet index	revision	B	B	B			
	sheet	1	2	3			



form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family CONAN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 5:1 FCI	title
B					angles linear .XX±.01/.3		CONAN™ CONNECTOR RECEP. ASS'Y (BLACK)
					0'±2' .xxx±.005/.13		dwg no sheet 2 of 3 size
					.xxxx±.0020/.05		98209 A3
				dr	E.KROPIEWNICK 5/6/99		
				enr	D. WHITING 5/6/99		
				chr	D. WHITING 5/6/99		
				appd	D. WHITING 5/6/99		
sheet index	revision sheet						type Product Customer Drawing

form: A3

PRODUCT NUMBER	POS	DIM A	DIM C	DIM D
98209-31131	31	.800/20.30	.591/15.00	.551/14.00

98209-W	X	Y	ZZ				
			<table><tr><td>ZZ</td><td>NUMBER OF POSITIONS</td></tr><tr><td>31</td><td>31</td></tr></table>	ZZ	NUMBER OF POSITIONS	31	31
ZZ	NUMBER OF POSITIONS						
31	31						
		Y	<table><tr><td>Y</td><td>HEIGHT</td></tr><tr><td>1</td><td>.129/3.28</td></tr></table>	Y	HEIGHT	1	.129/3.28
Y	HEIGHT						
1	.129/3.28						
		X	<table><tr><td>X</td><td>PLATING</td></tr><tr><td>1</td><td>15μ"/0.38μ GXT</td></tr></table>	X	PLATING	1	15μ"/0.38μ GXT
X	PLATING						
1	15μ"/0.38μ GXT						
		W	<table><tr><td>W</td><td>PACKAGING</td></tr><tr><td>3</td><td>TAPE & REEL w/CAP</td></tr></table>	W	PACKAGING	3	TAPE & REEL w/CAP
W	PACKAGING						
3	TAPE & REEL w/CAP						

NOTES :

- MATERIALS :
RECEPTACLE HOUSING - LCP, COLOR : BLACK
PICK & PLACE CAP - LCP, COLOR : NATURAL
RECEPTACLE TERMINALS - 172 BERYLIUM COPPER,
PLATED WITH 15 μ "/.38 μ GXT IN CONTACT AREA
AND 100 μ "/2.54 μ SnPb ON SOLDER LEGS WITH
AN OVERALL 50 μ "/1.27 μ Ni UNDERPLATE.
RETENTION DEVICE - 260 BRASS,
PLATED WITH 100 μ "/2.54 μ SnPb OVER
NICKEL.
- REFERENCE GES-12-006 FOR PRODUCT
PERFORMANCE DATA.
- SEE TA-774 FOR FURTHER DESCRIPTION OF
HOW THIS DIMENSION IS APPLIED.
- RECOMMENDED SOLDER PASTE THICKNESS IS
.006 TO .008 INCHES THICK.
- THE TOE HEIGHT OF THE SOLDER TAIL SHALL BE
MEASURED FROM THE LOWEST POINT OF THE .004
CO-PLANARITY GRAVITY PLANE. THIS MEASUREMENT
IS NOT TO EXCEED A WINDOW OF .000 TO .007.
- THREE SLOTS MAY BE LOCATED AT EITHER END OF
HOUSING.

mat'l. code				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family CONAN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
B					angles linear .XX $\pm$.01/.3	scale 1:1	CONAN™ CONNECTOR RECEP. ASS'Y (BLACK)
					0'±2' .xxx±.005/.13		dwg no
					.xxxx±.0020/.051		sheet 3 of 3 size
			dr	E.KROPIEWNICK	5/6/99		98209 A3
			enr	D. WHITING	5/6/99		
			chr	D. WHITING	5/6/99		
			app	D. WHITING	5/6/99		
sheet	revision						type Product Customer Drawing
index	sheet						