

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0848546041

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

DeviceNet Micro-Change Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), NMEA 2000 Style Cable, 7.0m (22.97') Length, meets NMEA 2000

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

84854

Micro-Change (M12)

Micro-Change (M12)

IP67

Copper Alloy

Brad Micro-Change (M12) Connectors

Micro-Change (M12)

N/A

Europe

Double Ended

822350898362

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - Plating Mating

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

5.72mm (.225")

7.0m (22.97')

Gray

Threaded

Female-Male

Single

No

PVC

PVC

Nickel-plated Brass

Gold

Straight to Straight

5

-20°C to +105°C

22

Thin Standard Cable

Electrical

Current - Maximum per Contact

Voltage - Maximum

4.0A

250V

Material Info

Engineering Number

NMEA-DND22NB-M070

Reference - Drawing Numbers

Sales Drawing

SD-84854-016



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Not Relevant

Not Relevant

Not Reviewed

Search Parts in this Series

84854 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION