

**Features:**

- WWS offers miniature size at higher power rating
- High performance for low cost
- High power to size ratio
- MWW – completely molded construction with welded terminations
- Complete welded terminations
- Tinned copper leads
- Available in non-inductive styles
- High temperature silicone coating
- RoHS compliant
- Higher operating temperatures may be available. Contact factory.




| Electrical Specifications |               |                         |                             |                                    |                                                        |               |
|---------------------------|---------------|-------------------------|-----------------------------|------------------------------------|--------------------------------------------------------|---------------|
| Type / Code               | MIL-R-26 Ref. | Dielectric Strength (V) | Power Rating (Watts) @ 25°C | Resistance Temperature Coefficient | Ohmic Range(Ω) and Tolerance(1)<br>0.1%, 0.5%, 1% & 5% |               |
|                           |               |                         |                             |                                    | Standard                                               | Non-Inductive |
| WW12 / NWW12              | -             | 500V                    | 0.4W                        | < 1Ω = ±90ppm/°C                   | 0.1 - 2K                                               | 0.1 - 1K      |
| WW1 / NWW1                | -             | 500V                    | 1W                          |                                    | 0.1 - 3K                                               | 0.1 - 1.5K    |
| WW1A / NWW1A              | RW-70         | 500V                    | 1W                          |                                    | 0.1 - 7K                                               | 0.1 - 3.5K    |
| WW2 / NWW2                | RW-69         | 1,000V                  | 1.5W                        |                                    | 0.1 - 10K                                              | 0.1 - 5K      |
| WWS2 / NWS2               | -             | 500V                    | 2.5W                        |                                    | 0.1 - 3K                                               | 0.1 - 1.5K    |
| WW2A / NWW2A              | -             | 1,000V                  | 2.5W                        | 1Ω to 10Ω = ±50ppm°C               | 0.1 - 15K                                              | 0.1 - 7.5K    |
| WW3 / NWW3                | RW-79         | 1,000V                  | 3W                          |                                    | 0.1 - 22K                                              | 0.1 - 11K     |
| WWS3 / NWS3               | RW-69         | 1,000V                  | 3W                          |                                    | 0.1 - 10K                                              | 0.1 - 5K      |
| WW3A / NWW3A              | -             | 1,000V                  | 3W                          |                                    | 0.1 - 30K                                              | 0.1 - 15K     |
| WW4 / NWW4                | -             | 1,000V                  | 4W                          |                                    | 0.1 - 40K                                              | 0.1 - 20K     |
| WWS4 / NWS4               | RW-79         | 1,000V                  | 4W                          |                                    | 0.1 - 22K                                              | 0.1 - 11K     |
| WW5 / NWW5                | RW-67, RW-74  | 1,000V                  | 5W                          |                                    | 0.1 - 50K                                              | 0.1 - 25K     |
| WWS5 / NWS5               | -             | 1,000V                  | 5W                          |                                    | 0.1 - 40K                                              | 0.1 - 20K     |
| WW7 / NWW7                | -             | 1,000V                  | 6.5W                        |                                    | 0.1 - 70K                                              | 0.1 - 35K     |
| WWS7 / NWS7               | RW-67, RW-74  | 1,000V                  | 6.5W                        |                                    | 0.1 - 50K                                              | 0.1 - 25K     |
| WW7B / NWW7B              | -             | 1,000V                  | 7W                          | >10Ω = ±20ppm/°C                   | 0.1 - 100K                                             | 0.1 - 50K     |
| WW10 / NWW10              | RW-78         | 1,000V                  | 10W                         |                                    | 0.1 - 150K                                             | 0.1 - 75K     |
| WWS10 / NWS10             | -             | 1,000V                  | 10W                         |                                    | 0.1 - 100K                                             | 0.1 - 50K     |
| MWW1 / NMWW1              | RW-70         | 1,000V                  | 1W                          |                                    | 0.1 - 2K                                               | -             |
| MWW3 / NMWW3              | RW-79         | 1,000V                  | 3W                          |                                    | 0.1 - 20K                                              | -             |
| MWW5 / NMWW5              | RW-67, RW-74  | 1,000V                  | 5W                          |                                    | 0.1 - 40K                                              | -             |
| MWW10 / NMWW10            | RW-68, RW-74  | 1,000V                  | 10W                         |                                    | 0.1 - 150K                                             | -             |

(1) Lesser of √PR or maximum working voltage

Please refer to the High Power Resistor Application Note (page 4) for more information on designing and implementing high power resistor types.

| Performance Characteristics |                                                               |        |
|-----------------------------|---------------------------------------------------------------|--------|
| Test                        | Test Condition                                                | Result |
| Moisture Resistance         | 1000 hours, 95% R.H., 40°C                                    | 1% max |
| Load Life                   | 1000 hours,<br>cycled power 1.5 hours ON, 0.5 hours OFF, 25°C | 1%     |
| Temperature Cycling         | 5 cycles, -55°C to 200°C                                      | 0.5%   |
| Short Time Overload         | 5 times rated power for 5 seconds                             | 1%     |


Operating Temperature Range: -55°C to +350°C



| Mechanical Specifications   |               |               |                   |        |
|-----------------------------|---------------|---------------|-------------------|--------|
| Type / Code                 | A             | B             | C                 | Unit   |
| WW12 / NWW12                | 0.312 ± 0.062 | 0.110 ± 0.031 | 0.025 ± 0.002     | inches |
|                             | 7.92 ± 1.57   | 2.79 ± 0.79   | 0.64 ± 0.05       | mm     |
| WW1, WWS2 / NWW1, NWWS2     | 0.375 ± 0.062 | 0.110 ± 0.031 | 0.025 ± 0.002     | inches |
|                             | 9.53 ± 1.57   | 2.79 ± 0.79   | 0.64 ± 0.05       | mm     |
| WW1A / NWW1A                | 0.420 ± 0.062 | 0.110 ± 0.031 | 0.025 ± 0.002     | inches |
|                             | 10.67 ± 1.57  | 2.79 ± 0.79   | 0.64 ± 0.05       | mm     |
| WW2, WWS3 / NWW2, NWWS3     | 0.370 ± 0.062 | 0.156 ± 0.031 | 0.032 ± 0.002     | inches |
|                             | 9.40 ± 1.57   | 3.96 ± 0.79   | 0.81 ± 0.05       | mm     |
| WW2A / NWW2A                | 0.550 ± 0.062 | 0.156 ± 0.031 | 0.032 ± 0.002     | inches |
|                             | 13.97 ± 1.57  | 3.96 ± 0.79   | 0.81 ± 0.05       | mm     |
| WW3, WWS4 / NWW3, NWWS4     | 0.560 ± 0.062 | 0.187 ± 0.031 | 0.032 ± 0.002     | inches |
|                             | 14.22 ± 1.57  | 4.75 ± 0.79   | 0.81 ± 0.05       | mm     |
| WW3A / NWW3A                | 0.500 ± 0.062 | 0.218 ± 0.031 | 0.032 ± 0.002     | inches |
|                             | 12.70 ± 1.57  | 5.54 ± 0.79   | 0.81 ± 0.05       | mm     |
| WW4, WWS5 / NWW4, NWWS5     | 0.700 ± 0.062 | 0.270 ± 0.031 | 0.036 ± 0.002     | inches |
|                             | 17.78 ± 1.57  | 6.86 ± 0.79   | 0.91 ± 0.05       | mm     |
| WW5, WWS7 / NWW5, NWWS7     | 0.875 ± 0.062 | 0.312 ± 0.031 | 0.036 ± 0.002     | inches |
|                             | 22.23 ± 1.57  | 7.92 ± 0.79   | 0.91 ± 0.05       | mm     |
| WW7 / NWW7                  | 1.000 ± 0.062 | 0.312 ± 0.031 | 0.036 ± 0.002     | inches |
|                             | 25.40 ± 1.57  | 7.92 ± 0.79   | 0.91 ± 0.05       | mm     |
| WW7B, WWS10 / NWW7B, NWWS10 | 1.200 ± 0.062 | 0.312 ± 0.031 | 0.036 ± 0.002     | inches |
|                             | 30.48 ± 1.57  | 7.92 ± 0.79   | 0.91 ± 0.05       | mm     |
| WW10 / NWW10                | 1.780 ± 0.062 | 0.375 ± 0.031 | 0.040 ± 0.002 (1) | inches |
|                             | 45.21 ± 1.57  | 9.53 ± 0.79   | 1.02 ± 0.05 (1)   | mm     |
| MWW1 / NMWW1                | 0.385 ± 0.062 | 0.135 ± 0.031 | 0.032 ± 0.002     | inches |
|                             | 9.78 ± 1.57   | 3.43 ± 0.79   | 0.81 ± 0.05       | mm     |
| MWW3 / NMWW3                | 0.560 ± 0.062 | 0.205 ± 0.031 | 0.032 ± 0.002     | inches |
|                             | 14.22 ± 1.57  | 5.21 ± 0.79   | 0.81 ± 0.05       | mm     |
| MWW5 / NMWW5                | 0.925 ± 0.062 | 0.330 ± 0.031 | 0.036 ± 0.002     | inches |
|                             | 23.50 ± 1.57  | 8.38 ± 0.79   | 0.91 ± 0.05       | mm     |
| MWW10 / NMWW10              | 1.965 ± 0.062 | 0.480 ± 0.031 | 0.040 ± 0.002     | inches |
|                             | 49.91 ± 1.57  | 12.19 ± 0.79  | 1.02 ± 0.05       | mm     |

(1) Available in 0.036" / 0.91mm

### Power Derating Curve:



## How to Order

| 1              |               | 2              |  | 3                      |  | 4         |      | 5         |                      | 6                                                                                                                                           |          | 7                                                                                                               |  | 8 |  | 9 |  |
|----------------|---------------|----------------|--|------------------------|--|-----------|------|-----------|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------|----------|-----------------------------------------------------------------------------------------------------------------|--|---|--|---|--|
| W              |               | W              |  | 1                      |  | F         |      | T         |                      | 1                                                                                                                                           |          | K                                                                                                               |  | 0 |  | 0 |  |
| Product Series |               | Type/Code      |  | Power Rating<br>@ 25°C |  | Tolerance |      | Packaging |                      |                                                                                                                                             |          | Resistance Value                                                                                                |  |   |  |   |  |
| WW             | Standard      |                |  |                        |  | Code      | Tol  | Code      | Description          | Size                                                                                                                                        | Quantity | Four characters<br>with the multiplier<br>used as the<br>decimal holder.<br><br>0.1 ohm = R100<br>2 Kohm = 2K00 |  |   |  |   |  |
| WWS            | Mini          | WW12 / NWW12   |  | 0.4W                   |  | B         | 0.1% | T         | 11" Tape<br>and Reel | WW12 / NWW12<br>WW1 / NWW1<br>WWS2 / NWSWS2<br>WW1A / NWW1A<br>MWW1 / NMWW1                                                                 | 2,500    |                                                                                                                 |  |   |  |   |  |
| MWW            | Molded        | WW1 / NWW1     |  | 1W                     |  | D         | 0.5% |           |                      | WW2 / NWW2<br>WWS3 / NWSWS3<br>WW2A / NWW2A<br>WW3 / NWW3<br>WWS4 / NWSWS4<br>MWW3 / NMWW3                                                  | 2,000    |                                                                                                                 |  |   |  |   |  |
| NWW            | Non-Inductive | WW1A / NWW1A   |  | 1W                     |  | F         | 1%   |           |                      | WW3A / NWW3A<br>WW4 / NWW4<br>WWS5 / NWSWS5<br>WW5 / NWW5<br>WWS7 / NWSWS7<br>WW7 / NWW7<br>WW7B / NWW7B<br>WWS10 / NWSWS10<br>MWW5 / NMWW5 | 500      |                                                                                                                 |  |   |  |   |  |
| NWWS           | Mini          | WW2 / NWW2     |  | 1.5W                   |  | J         | 5%   |           |                      | WW10 / NWW10<br>MWW10 / NMWW10                                                                                                              | 250      |                                                                                                                 |  |   |  |   |  |
| NWWS           | Non-Inductive | WWS2 / NWWS2   |  | 2.5W                   |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW2A / NWW2A   |  | 2.5W                   |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW3 / NWW3     |  | 3W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WWS3 / NWWS3   |  | 3W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW3A / NWW3A   |  | 3W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW4 / NWW4     |  | 4W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WWS4 / NWWS4   |  | 4W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW5 / NWW5     |  | 5W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WWS5 / NWWS5   |  | 5W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW7 / NWW7     |  | 6.5W                   |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WWS7 / NWWS7   |  | 6.5W                   |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW7B / NWW7B   |  | 7W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WW10 / NWW10   |  | 10W                    |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | WWS10 / NWWS10 |  | 10W                    |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | MWW1 / NMWW1   |  | 1W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | MWW3 / NMWW3   |  | 3W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | MWW5 / NMWW5   |  | 5W                     |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |
|                |               | MWW10 / NMWW10 |  | 10W                    |  |           |      |           |                      |                                                                                                                                             |          |                                                                                                                 |  |   |  |   |  |


## Legacy Part Number (before January 3, 2011):

| SEI Type | Code               | Nominal Resistance | Tolerance | Packaging                                                                                                             |       |               |      |
|----------|--------------------|--------------------|-----------|-----------------------------------------------------------------------------------------------------------------------|-------|---------------|------|
| WW       | 1                  | 10K                | 1%        | R                                                                                                                     |       |               |      |
| Type     | Description        |                    | Tolerance | Types                                                                                                                 | Qty   | Description   | Code |
| WW       | Standard           |                    | 0.1%      | WW12, NWW12, WW1, NWW1, WWS2, NWWS2                                                                                   | 2,500 | 11" reel tape | R    |
| WWS      | Mini               |                    | 0.5%      | WW1A, NWW1A, MWW1, NMWW1                                                                                              |       |               |      |
| MWW      | Molded             |                    | 1%        | WW2, NWW2, WWS3, NWWS3, WW2A, NWW2A                                                                                   | 2,000 |               |      |
| NWW      | Non-Inductive      |                    | 5%        | WW3, NWW3, WWS4, NWWS4, MWW3, NMWW3                                                                                   |       |               |      |
| NWWS     | Mini Non-Inductive |                    |           | WW3A, NWW3A, WW4, NWW4, WWS5, NWWS5<br>WW5, NWW5, WWS7, NWWS7, WW7, NWW7<br>WW7B, NWW7B, WWS10, NWWS10<br>MWW5, NMWW5 | 500   |               |      |
|          |                    |                    |           | WW10, NWW10, MWW10, NMWW10                                                                                            | 250   |               |      |

### High Power Chip Resistors and Thermal Management

Stackpole has developed several surface mount resistor series in addition to our current sense resistors, which have had higher power ratings than standard resistor chips. This has caused some uncertainty and even confusion by users as to how to reliably use these resistors at the higher power ratings in their designs.

The data sheets for the RHC, RMCP, RNCP, CSR, CSRN, CSRF, CSS, and CSSH state that the rated power assumes an ambient temperature of no more than 100 degrees C for the CSS / CSSH series and 70 degrees C for all other high power resistor series. In addition, IPC and UL best practices dictate that the combined temperature on any resistor due to power dissipated and ambient air shall be no more than 105C. At first glance this wouldn't seem too difficult, however the graph below shows typical heat rise for the CSR ½ 100 milliohm at full rated power. The heat rise for the RMCP and RNCP would be similar. The RHC with its unique materials, design, and processes would have less heat rise and therefore would be easier to implement for any given customer.



The 102 degrees C heat rise shown here would indicate there will be additional thermal reduction techniques needed to keep this part under 105C total hot spot temperature if this part is to be used at 0.75 watts of power. However, this same part at the usual power rating for this size would have a heat rise of around 72 degrees C. This additional heat rise may be dealt with using wider conductor traces, larger solder pads and land patterns under the solder mask, heavier copper in the conductors, vias through PCB, air movement, and heat sinks, among many other techniques. Because of the variety of methods customers can use to lower the effective heat rise of the circuit, resistor manufacturers simply specify power ratings with the limitations on ambient air temperature and total hot spot temperatures and leave the details of how to best accomplish this to the design engineers. Design guidelines for products in various market segments can vary widely so it would be unnecessarily constraining for a resistor manufacturer to recommend the use of any of these methods over another.

**Note:** The final resistance value can be affected by the board layout and assembly process, especially the size of the mounting pads and the amount of solder used. This is especially notable for resistance values  $\leq 50$  m $\Omega$ . This should be taken into account when designing.