

Technical drawing of a mechanical part showing two views: a top view and a side view.

Top View:

- E:** Total width of the part.
- F REF.:** Reference length of the part.
- B $\pm .01 (.25)$:** Thickness of the part.

Side View:

- D:** Height of the part.
- C REF.:** Reference width of the circular feature.
- A $\pm .01 (.25)$:** Height of the tapered end.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
BT1M	.06 (1.5)	0.90 (23)	.036 (0.9)	.095 (2.4)	.110 (2.8)	.156 (4.0)	.172 (4.4)	4.0 (102)	18 (80)	MINIATURE	.05 (22)
BT1.5M	.06 (1.5)	1.5 (38)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	6.3 (160)	18 (80)	MINIATURE	.09 (43)
BT2M	.06 (1.5)	2.0 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	18 (80)	MINIATURE	.12 (53)
BT4M	.06 (1.5)	4.00 (102)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	14.2 (361)	18 (80)	MINIATURE	.21 (93)

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										DOME-TOP Barb Ty CABLE TIES BT SERIES	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .10 (2.5) (.XXX) ± .020 (.5) (.XX) ± .02 (.5) ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY PMH	MAT'L: NYLON 6.6
10	5/2/06	JABO		REMOVED STRAIGHT TIP REFERENCE & TIP STYLE COLUMN	0037	10				DATE 6-24-93	DRAWING NO. BT-0037 SHEET 1 OF 3
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D JVL	DWG A SIZE