



Product Number: NBF-32204

NBF Series - Clear Door Plastic Boxes



Design Features

- Designed to IP66 of IEC 529 and NEMA 1, 2, 4, 4x, 12, and 13 specifications
- All plastic construction including hinge pins
- Comes complete with stainless steel wall mounting brackets and hardware
- Style A has two or three plastic latches
- **Indoor Versions:**
 - ABS plastic enclosures are molded out of light gray material with UL94-HB flammability rating. (Not UL Listed)
 - ABS/PC blended plastic enclosures are molded out of light gray material with UL94-5VA flammability rating. Suggested service temperature range -40C to +70C.
 - Clear doors, for all models, are molded out of polycarbonate material with UL94-V0 flammability rating
- **Nominal External Dimensions Inches (Millimeters):**
 - A: 5.90" (150 mm)
 - B: 3.93" (100 mm)
 - C: 2.75" (70 mm)
 - D: 1.97" (50 mm)

- **Actual Internal Dimensions Inches (+/- 0.06):**

- E: 5.37
- F: 3.42
- G: 2.52

- **Weight:**

- 0.7 Lbs