



NOTES:

1. OPERATING TEMPERATURE: -65°F TO +300°F
2. FINISH: PARTS SHALL HAVE A SMOOTH APPEARANCE, WITH NO GATES AND ALL FLASH REMOVED
3. U.S. & FOREIGN PATENT ISSUED

REVISIONS					
ECN #	REV.	DESCRIPTION	DATE	INITIALS	CHK'D
	N/A	INITIAL RELEASE	7/12/01	JS	-
	1	CHG DUROMETER FROM 70 TO 60	9/27/02	JS	-
	001	REVISED PER ECR111009AZ01	2/12/10	KH	DPZ




SECTION A-A



ISOMETRIC VIEW

DIMENSION STYLE: INCHES [MM] GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED		
	INCHES	MM
.X	± .020	± .508
.XX	± .010	± .254
.XXX	± .005	± .127

ANGLE ± 1°



THIRD ANGLE PROJECTION

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS
DRAWING IS THE SOLE PROPERTY OF
VISUAL COMMUNICATIONS COMPANY, INC.
ANY REPRODUCTION IN PART OR AS
A WHOLE WITHOUT THE WRITTEN
PERMISSION OF VISUAL
COMMUNICATIONS COMPANY, INC IS
PROHIBITED.

APPROVAL		DATE
DRAWN	KHOWARD	2/12/10
CHECKED	DPZ	2/12/10
MATERIAL		
(EPDM) ETHYLENE PROPYLENE DIENE RUBBER, 60 DUROMETER, BLACK		
FINISH		
SEE NOTES		
DO NOT SCALE DRAWING		

 OPTOELECTRONICS 190 BOSSTICK BLVD. SUITE 101 SAN MARCOS, CA 92069 U.S.A PHONE: (760) 560-1300, FAX: (760) 560-1301 EMAIL: vccsales@vccclite.com		
TITLE:		
LENS SPACER SPC 060		
SIZE	DWG. NO.	REV
A	SPC 060_E	001
SCALE: 5:1		SHEET 1 OF 1