


# SMD OVEN CONTROLLED CRYSTAL OSCILLATOR

AOCJY Series



RoHS/RoHS II compliant



25.4 x 22.1 x 12.7 mm

**Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = 1**

## FEATURES:

- 25.4 x 22.1 x 12.7 mm True SMT- RoHS Compliant Reflow-able Package
- SC-Cut, High “Q” resonator based design
- Either Sinewave or CMOS RF output
- Available with  $\pm 30$  ppb over  $-40^{\circ}\text{C}$  to  $+75^{\circ}\text{C}$  operating temperature Range
- Tighter Stabilities to  $\pm 5.0$  ppb over  $0^{\circ}\text{C}$  to  $+50^{\circ}\text{C}$  also available
- Exceptional long-term Aging of  $\pm 500$  ppb over 10-Year Product Life
- Excellent close-in phase noise ( $-135$  dBc/Hz Typical @100 Hz offset from 10MHz carrier)

## APPLICATIONS:

- Cellular Infrastructure
- Radar Systems
- Test & Measurement Equipment
- GPS Tracking with precision hold-over accuracy
- WiMax / WLAN

## STANDARD SPECIFICATIONS:

| Parameters                                                                           | Minimum                                                                    | Typical | Maximum      | Units              | Notes                        |
|--------------------------------------------------------------------------------------|----------------------------------------------------------------------------|---------|--------------|--------------------|------------------------------|
| <b>RF Output</b>                                                                     |                                                                            |         |              |                    |                              |
| Frequency                                                                            | 10.00                                                                      |         | 100.00       | MHz                | CMOS output                  |
|                                                                                      | 10.00                                                                      |         | 100.00       | MHz                | Sinewave output              |
| Standard Available Frequencies                                                       | 10.00, 12.80, 13.00, 16.384, 20.00, 26.00, 38.40, 38.88, 40.00, 100.00 MHz |         |              |                    |                              |
| <b>Operable Temperature Range</b>                                                    | 0                                                                          |         | 50           | $^{\circ}\text{C}$ | <i>See Stability Options</i> |
| <b>Frequency Stability Options</b>                                                   |                                                                            |         |              |                    |                              |
| 0 $^{\circ}\text{C}$ to $+50^{\circ}\text{C}$                                        |                                                                            |         | $\pm 5.00$   | ppb                | Default Spec.                |
| $-20^{\circ}\text{C}$ to $+70^{\circ}\text{C}$                                       |                                                                            |         | $\pm 10.00$  | ppb                | Option “E”                   |
| $-40^{\circ}\text{C}$ to $+75^{\circ}\text{C}$                                       |                                                                            |         | $\pm 30.00$  | ppb                | Option “F”                   |
|                                                                                      |                                                                            |         |              |                    |                              |
| <b>Frequency Stability vs. Supply Voltage (Vdd <math>\pm 5\%</math>)</b>             |                                                                            |         | $\pm 20.00$  | ppb                |                              |
| <b>Warm-Up @ 25 <math>^{\circ}\text{C}</math></b>                                    |                                                                            |         | $\pm 100.00$ | ppb                | In $\leq 3$ -minutes         |
|                                                                                      |                                                                            |         |              |                    |                              |
| Power Consumption @ turn on                                                          |                                                                            |         | 3.60         | Watts              |                              |
| Power Consumption Steady State                                                       |                                                                            |         | 1.40         | Watt               |                              |
| Supply Voltage (Vdd)                                                                 | 3.135                                                                      | 3.30    | 3.465        | Volts              | <i>See Options</i>           |
| Reference Voltage (Vref)<br>(available as an output to facilitate oscillator tuning) | 2.60                                                                       | 2.80    | 3.00         | Volts              | <i>For Vdd=+3.3V version</i> |
|                                                                                      | 4.30                                                                       | 4.50    | 4.70         | Volts              | <i>For Vdd=+5.0V version</i> |
| <b>Aging</b>                                                                         |                                                                            |         |              |                    |                              |
| Daily aging (after 30 days)                                                          |                                                                            |         | $\pm 1.0$    | ppb                |                              |
| Yearly                                                                               |                                                                            |         | $\pm 100$    | ppb                |                              |
| 10-Years                                                                             |                                                                            |         | $\pm 500$    | ppb                |                              |
| <b>Waveform</b>                                                                      | <b>LVC MOS</b>                                                             |         |              |                    |                              |
| Level "1" (Logic High)                                                               | 0.9*Vdd                                                                    |         |              | Volts              |                              |
| Level "0" (Logic Low)                                                                |                                                                            |         | 0.1*Vdd      | Volts              |                              |
| Load                                                                                 |                                                                            | 15      |              | pf                 |                              |
| Rise & Fall Time                                                                     |                                                                            |         | 5.0          | ns                 |                              |
| Duty Cycle                                                                           | 45                                                                         |         | 55           | %                  |                              |




# SMD OVEN CONTROLLED CRYSTAL OSCILLATOR

AOCJY Series



RoHS/RoHS II compliant



25.4 x 22.1 x 12.7 mm

## STANDARD SPECIFICATIONS contd.

| Parameters                             | Minimum      | Typical  | Maximum      | Units      | Notes |
|----------------------------------------|--------------|----------|--------------|------------|-------|
| <b>Waveform</b>                        | Sinewave     |          |              |            |       |
| Peak Power                             | 2.00         |          |              | dBm        |       |
| Output Load                            |              | 50       |              | $\Omega$   |       |
| <b>Spectral Content</b>                |              |          |              |            |       |
| Spurious Response                      |              |          | -70          | dBc        |       |
| Phase Noise @ 10MHz Carrier (Vdd=3.3V) |              |          |              |            |       |
| @ 1 Hz offset                          |              |          | -90          | dBc / Hz   |       |
| @ 10 Hz offset                         |              |          | -120         | dBc / Hz   |       |
| @ 100 Hz offset                        |              |          | -135         | dBc / Hz   |       |
| @ 1,000 Hz offset                      |              |          | -145         | dBc / Hz   |       |
| @ 10,000 Hz offset                     |              |          | -150         | dBc / Hz   |       |
| @ 100,000 Hz offset                    |              |          | -150         | dBc / Hz   |       |
| @ 1,000,000 Hz offset                  |              |          | -150         | dBc / Hz   |       |
| <b>Electrical Frequency Adjustment</b> |              |          |              |            |       |
| Control Voltage Range (Vc)             | 0.0          |          | Vdd          | Volts      |       |
| Frequency Pull Range                   | $\pm 0.7$    |          |              | ppm        |       |
| Frequency Pull Slope                   |              | Positive |              |            |       |
| Control Voltage Port Impedance         | 10           |          |              | k $\Omega$ |       |
| Center Control Voltage                 | (Vdd/2) -0.5 | Vdd/2    | (Vdd/2) +0.5 | Volts      |       |

## OPTIONS AND PART IDENTIFICATION (Left blank if standard)

AOCJY -  -  MHz -  -

### Supply Voltage Option

Blank: 3.30V $\pm 5\%$

A: 5.00V $\pm 5\%$

### Frequency in MHz

Such as; 10.000 MHz

26.000 MHz

100.000 MHz

### Temperature Options

Blank:  $\pm 5.0$ ppb/0°C to +50°C

E:  $\pm 10.0$ ppb/-20°C to +70°C

F:  $\pm 30.0$ ppb/-40°C to +75°C



### RF Output Options

Blank: CMOS

SW: Sinewave

## OUTLINE DIMENSIONS

### Recommended Soldering Pattern



| Pin | Function         |
|-----|------------------|
| 1   | Control Voltage  |
| 2   | V <sub>REF</sub> |
| 3   | Supply Voltage   |
| 4   | RF-output        |
| 5   | Ground. Case     |

Dimensions: Inches (mm)

ABRACON IS  
ISO9001:2008  
CERTIFIED



**ABRACON**  
CORPORATION


Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 05.24.13**  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

# SMD OVEN CONTROLLED CRYSTAL OSCILLATOR

AOCJY Series




RoHS/RoHS II compliant



25.4 x 22.1 x 12.7 mm


## REFLOW PROFILE:



|                                          |                           |
|------------------------------------------|---------------------------|
| $T_s$ max to $T_L$ (Ramp-up Rate)        | 3°C/second max.           |
| Preheat                                  |                           |
| Temperature Min. ( $T_s$ Min.)           | 150°C                     |
| Temperature Typical ( $T_s$ Typ.)        | 175°C                     |
| Temperature Max. ( $T_s$ Max.)           | 200°C                     |
| Time ( $t_s$ )                           | 60 ~ 180 seconds          |
| Ramp-up rate ( $T_L$ to $T_p$ )          | 3°C/second max.           |
| Time Maintained Above:                   |                           |
| --Temperature ( $T_L$ )/Time ( $t_L$ )   | 217°C/60 ~ 150 seconds    |
| Peak Temperature ( $T_p$ )               | 250°C max. for 10 seconds |
| Target Peak Temperature ( $T_p$ Target)  | 250°C +0/-5°C             |
| Time within 5°C of actual peak ( $t_p$ ) | 20 ~ 40 seconds           |
| Ramp-down Rate                           | 6°C/second max.           |
| Time 25°C to Peak Temperature (t)        | 8 minutes max.            |

## PACKAGING:

(15) units per tray



**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO9001:2008  
CERTIFIED



**ABRACON**  
CORPORATION

Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 05.24.13**  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)