







E I DUPONT DE NEMOURS & CO INC
DUPONT POLYMERS, ENGINEERING POLYMERS
NYLON RESINS PO BOX 80713, CHESTNUT RUN
PLAZA, WILMINGTON DE 19880

E41938 (M)



Mtl Dsg	Col	Min Thk mm	UL94 Flame Class	Elec	RTI Mech with Imp	w/o Imp	H W I	H A I	H V T R	D 4 9 5	C T I
Polyamide, Type 66 nylon (PA66), designated "Zytel", furnished in the form of pellets.											
132F.	All	0.71	94V-2	125	65	65	4	0	—	—	—
133L, 135F		1.5	94V-2	125	75	85	3	0	0	—	—
		3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
✓ 101(2), 101F, 101L, E101L, E101(1)	All	0.71	94V-2	125	65	65	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
101(2), 101F, 101L, E101L, E101(1)	All	3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
EFE1068	All	0.71	94V-2	125	65	65	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
		3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
EFE1030	All	0.71	94V-2	125	—	—	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
		3.0	94V-2	125	75	85	2	0	0	—	—
		6.0	94V-2	125	75	85	2	0	0	6	0
FE-3370	NC, GY	0.84	94HB	65	65	65	—	—	—	—	—
FE-3397	NC, GY	0.85	94HB	65	65	65	—	—	—	—	—

300-9051

TOLERANCE: L ≤ 10 ±0.2 10 < L ≤ 30 ±0.3 30 < L ≤ 50 ±0.5 50 < L ≤ 100 ±0.7 100 < L ≤ 250 ±1.2 ABOVE 250 ±1.5	APPROVED BY 張道陽		87.8.21.	 品固企業有限公司 品基電子塑膠製品廠 鑽隆有限公司 PINGOOD ENTERPRISE CO., LTD.
	REVIEWED BY 蕭存桂		87.8.21.	
	DRAWN BY 蕭存桂		87.8.21.	
	MATERIAL: NYLON 66(UL) FLAME CLASS: 94V-2 COLOR: NATURAL			
 UNIT mm	SCALE		PART NO: LED-10	SHEET 1 OF 1

EF0404505