



RECOMMENDED PANEL MOUNTING

PANEL THICKNESS	X
0.75-1.25	19.2-19.3
1.25-2.00	19.3-19.4
2.00-3.00	19.5-19.6





SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	OFF
1-1a	N/A	OPEN



CIRCUIT: SPST

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REF. ONLY
- RATING: 8A @ 250VAC
15A @ 125VAC
- CONTACT MATERIAL: SILVER
- ELECTRICAL LIFE: 10,000 CYCLES MIN.
- CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
- DIELECTRIC STRENGTH: >1,500VAC FOR 1 MIN.
- ▲ DENOTES CRITICAL PARAMETER.
- 2002/95/EC (ROHS) COMPLIANT

▲ ACTUATOR COLOR:
BLACK▲ HOUSING COLOR:
BLACK

E-SWITCH®



TITLE R1966ABLKBLKAS

SCALE 1.5:1

DATE 9/7/2006

DR BO

DWG M300011

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED