

GT5Y Series — ON Delay Timers



Key features of the GT5Y series include:

- 4PDT, 3A or DPDT, 5A contacts
- 4 time ranges
- Repeat error $\pm 0.2\%$ maximum
- Control settings by hand or screwdriver
- Power ON and timing out LED indicators
- Uses the same sockets and hold-down clips as IDEC's RY4S and RU series relays



UL, c-uL Listed
File No. E55996



		GT5Y-2	GT5Y-4
Specifications	Rated Operating Voltage	100 to 120V AC (50/60Hz) 200 to 240V AC (50/60Hz) 24V DC 24V AC 12V DC	
	Contact Form	DPDT	4PDT
	Rated Load	Resistive Load	220V AC, 5A 30V DC, 5A
		Inductive Load	220V AC, 2A 30V DC, 2.5A
	Allowable Contact Power	Resistive Load	1100VA AC 150W DC
		Inductive Load Cos $\phi = 0.3$ L/r = 7msec	660VA AC 90W DC
	Allowable Voltage	250V AC, 125V DC	
	Allowable Current	5A	3A
	Temperature Error	$\pm 3\%$ maximum (over -10 to 50°C , reference temperature 20°C)	
	Setting Error	$\pm 10\%$ maximum	
	Reset Time	When turning power off after time up: 0.1 second maximum When turning power off <u>before</u> time up: 1 second maximum	
	Insulation Resistance	100M Ω minimum	
	Dielectric Strength	2,000V AC, 1 minute (except between contacts of the same pole)	
	Vibration Resistance	100N (approximate 10G)	
	Shock Resistance	Operating extremes: 100N (approximate 10G) Damage limits: 500N (approximate 50G)	
	Power Consumption	100V AC type: 1.5VA (at 50Hz) 200V AC type: 1.6VA (at 50Hz) 24V DC type: 0.9W	
	Electrical Life	500,000 operations minimum (220V AC, 5A)	200,000 operations minimum (110V AC, 3A)
	Mechanical Life	50,000,000 operations minimum	50,000,000 operations minimum
	Operating Temperature	-10 to $+50^{\circ}\text{C}$	
	Operating Humidity	45 to 85% RH	



1. Minimum applicable load: GT5Y-2: 5V DC, 20mA (reference value); GT5Y-4: 5V DC, 10mA (reference value).
2. Inductive load: $\cos \theta = .3$, L/R=7msec.

GT5Y Table of Contents

Part Number List — G-64
Timing Diagrams — G-65
GT5Y Accessories — G-66
GT5Y Dimensions — G-67

Part Numbering List

Mode of Operation	Contact	Output	Rated Voltage	Time Range	Complete Part No.
ON-Delay	DPDT	220V AC/ 30V DC, 5A	100 to 120V AC	1S/10S/1M/10M	GT5Y-2SN1A100
				3S/30S/3M/30M	GT5Y-2SN3A100
				6S/60S/6M/60M	GT5Y-2SN6A100
			200 to 240V AC	1S/10S/1M/10M	GT5Y-2SN1A200
				3S/30S/3M/30M	GT5Y-2SN3A200
				6S/60S/6M/60M	GT5Y-2SN6A200
			12V DC	1S/10S/1M/10M	GT5Y-2SN1D12
				3S/30S/3M/30M	GT5Y-2SN3D12
				6S/60S/6M/60M	GT5Y-2SN6D12
			24V DC	1S/10S/1M/10M	GT5Y-2SN1D24
				3S/30S/3M/30M	GT5Y-2SN3D24
				6S/60S/6M/60M	GT5Y-2SN6D24
			24V AC	1S/10S/1M/10M	GT5Y-2SN1A24
				3S/30S/3M/30M	GT5Y-2SN3A24
				6S/60S/6M/60M	GT5Y-2SN6A24
	4PDT	220V AC/ 30V DC, 3A	100 to 120V AC	1S/10S/1M/10M	GT5Y-4SN1A100
				3S/30S/3M/30M	GT5Y-4SN3A100
				6S/60S/6M/60M	GT5Y-4SN6A100
			200 to 240V AC	1S/10S/1M/10M	GT5Y-4SN1A200
				3S/30S/3M/30M	GT5Y-4SN3A200
				6S/60S/6M/60M	GT5Y-4SN6A200
			12V DC	1S/10S/1M/10M	—
				3S/30S/3M/30M	GT5Y-4SN3D12
				6S/60S/6M/60M	—
			24V DC	1S/10S/1M/10M	GT5Y-4SN1D24
				3S/30S/3M/30M	GT5Y-4SN3D24
				6S/60S/6M/60M	GT5Y-4SN6D24
			24V AC	1S/10S/1M/10M	GT5Y-4SN1A24
				3S/30S/3M/30M	GT5Y-4SN3A24
				6S/60S/6M/60M	GT5Y-4SN6A24



1. For sockets and accessories, see page G-66.



Timing Ranges

Code	Scale	Time Range Indication		Time Range
1S	0 to 10	x 0.1	S	0.1 second to 1 second
10S		x 1	S	0.2 second to 10 seconds
1M		x 0.1	M	1.2 seconds to 1 minute
10M		x 1	M	12 seconds to 10 minutes
3S	0 to 3	x 1	S	0.1 second to 3 seconds
30S		x 10	S	0.5 second to 30 seconds
3M		x 1	M	3 seconds to 3 minutes
30M		x 10	M	30 seconds to 30 minutes
6S	0 to 6	x 1	S	0.1 second to 6 seconds
60S		x 10	S	1 second to 60 seconds
6M		x 1	M	6 seconds to 6 minutes
60M		x 10	M	1 minute to 60 minutes

Timing Diagram/Schematics/Electrical Life Curves

	GT5Y-2	GT5Y-4																		
	DPDT	4PDT																		
Internal Connections (bottom view)																				
Operation Mode: ON-Delay	<table border="1"> <thead> <tr> <th>Item</th><th>Terminal No.</th><th>Operation</th></tr> </thead> <tbody> <tr> <td>Power (Power)</td><td>13-14</td><td></td></tr> <tr> <td>Delayed Contact</td><td>(NC) 1-9, 2-10, 3-11, 4-12</td><td></td></tr> <tr> <td></td><td>(NO) 5-9, 6-10, 7-11, 8-12</td><td></td></tr> <tr> <td>Indicator</td><td>POWER</td><td></td></tr> <tr> <td></td><td>OUT</td><td></td></tr> </tbody> </table> For an explanation of timing modes, see page E-4.		Item	Terminal No.	Operation	Power (Power)	13-14		Delayed Contact	(NC) 1-9, 2-10, 3-11, 4-12			(NO) 5-9, 6-10, 7-11, 8-12		Indicator	POWER			OUT	
Item	Terminal No.	Operation																		
Power (Power)	13-14																			
Delayed Contact	(NC) 1-9, 2-10, 3-11, 4-12																			
	(NO) 5-9, 6-10, 7-11, 8-12																			
Indicator	POWER																			
	OUT																			

Electrical Life Curves



Dimensions

GT5Y Timer, Blade with SY4S-05

