









REV.	DATE	DESCRIPTION
A	03/18/05	UPDATE DRAWING FORMAT



RECOMMENDED
MOUNTING HOLE



RECOMMENDED
CABLE STRIPPING DIM'S



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. NICKEL PL. 100 MIN. OVER COPPER PL. 50 MIN.
OVER COPPER PL. 50 MIN.
2. GOLD PL. 30 MIN. OVER NICKEL PL. 50 MIN.
3. TEFLON MIL-P-19468.

					APPROVALS		DATE	Amphenol Connex			
B					DRAWN	G.R.S.	03/18/05				
7	FERRULE	COPPER	NICKEL	1	CHECKED			PART DESCRIPTION BNC BULKHEAD CRIMP JACK (FOR AT&T 734A CABLE - 75ohm)			
6	HEX NUT	BRASS	NICKEL	1	ISSUED						
5	LOCK WASHER	BRASS	NICKEL	1	SHEET	1 OF 1		PART NO. 112970			
4	GASKET	SILICONE	RED	1							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1				DWG. NO. 112970.DWG			
2	INSULATOR	TEFLON	NATURAL	1							
1	BODY	BRASS	NICKEL	1				REV. A SIZE A SCALE NA			
DESCRIPTION				MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING				

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
 0.5 - 8mm ± 0.20mm
 8 - 30mm ± 0.40mm
 30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
 .020 - .315 ± 0.007"
 .315 - 1.180 ± 0.015"
 1.180 - 4.724 ± 0.020"

CAD FILE
C:/112/112970.DWG