


PRODUCT NUMBER
95228-XXXLF

RoHS COMPATIBLE, SEE NOTE 7

PLATING




3=0.76µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
1.27µm NI MIN UNDERPLATING

STYLE	SIZE	OMIT PIN POSITION
01	2x17	A5;A6;A7;A9;A10;A12;A13;A15;A16 B5;B6;B7;B9;B10;B12;B13;B15;B16



NOTES:

1. BODY MATERIAL: POLYESTER 30% GLASSFILLED COLOR BLUE, FLAME RETARDANT PER UL-94 VO.
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. 22N MIN PIN RETENTION IN EITHER DIRECTION
4. 0.6 MAX PROTRUSION PERMITTED AT 4 PLACES
5. PACKAGING :
 - POLYBAGS FROM 2 x 02 TO 2 x 06 POSITIONS
 - TUBE FROM 2 x 07 TO 2 x 36 POSITIONS
6. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS
- a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 245°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code		surface		tolerance		projection		product family	
ltr	ecm no	dr	date	ISO 1302	ISO 406	ISO 1101	mm	DUBOX HDR	
SEE NOTES									
A	F50603	PNZ	95.08.18	tolerances unless otherwise specified					
B	F05-0117	LMU	05.01.31	linear	.XX	±0.15			
C	F05-0244	J00	05-09.06	linear	XXX	±0.05	scale 4:1		
D	F06-0228	LMU	06.07.11	dr	P	NIZI			
E	F08-0147	YOV	08.04.14	engr	JM	PHAMVAN			
F	B-19285	AMA	14.11.03	chr	P	NIZI			
				appd	JMP				
sheet		revision							
index		sheet							
FCI									
title		DUBOX,DR,STR		dwg no		sheet 1 of 1		size	
DUBOX,DR,STR		SELECTIVELY LOADED		95228		A3		CUSTOMER Drawing	



FCIconnect.com

Copyright FCI