


Metal Film Resistors, Axial, High Precision, High Stability



FEATURES

- Extremely low temperature coefficient of resistance
- Very low noise and voltage coefficient
- Very good high frequency characteristics
- Can replace wirewound bobbins
- Proprietary epoxy coating provides superior moisture protection
- For surface mount product, see Vishay Dale's PSF datasheet (www.vishay.com/doc?30162)
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	HISTORICAL MODEL	POWER RATING ⁽³⁾ $P_{85^{\circ}\text{C}}$ W	LIMITING ELEMENT VOLTAGE MAX. ⁽¹⁾ V	TEMPERATURE COEFFICIENT $\pm$ ppm/ $^{\circ}\text{C}$	TOLERANCE $\pm$ %	RESISTANCE RANGE Ω
PTF51	PTF-51	0.05	200	5, 10, 15	0.02, 0.05, 0.1, 0.25, 0.5, 1	15 to 100K
PTF56	PTF-56	0.125	300	5, 10, 15	0.01, 0.02, 0.05, 0.1, 0.25, 0.5, 1	15 to 500K
PTF65	PTF-65	0.25	500	5, 10, 15	0.05, 0.1, 0.25, 0.5, 1	15 to 1M

Notes

- DSCC has created a drawing to support the need for a precision axial-leaded product. Vishay Dale is listed as a resource on this drawing as follows:

DSCC DRAWING NUMBER	VISHAY DALE MODEL	POWER RATING $P_{85^{\circ}\text{C}}$ W	RESISTANCE RANGE Ω	TOLERANCE $\pm$ %	TEMPERATURE COEFFICIENT $\pm$ ppm/ $^{\circ}\text{C}$	MAXIMUM WORKING VOLTAGE ⁽¹⁾ V
89088	PTF56..31, PTF56..32 ⁽²⁾	0.100	15 to 100K	0.01, 0.05, 0.1, 0.5, 1	5, 10	200
90038	PTF65..16, PTF65..14 ⁽²⁾	0.250	15 to 100K	0.05, 0.1, 0.5, 1	5, 10	200

This drawing can be viewed at: www.landandmaritime.dla.mil/Programs/MilSpec/ListDwgs.aspx?DocTYPE=DSCCdwg

- (1) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.
- (2) Hot solder dipped leads.
- (3) For operation of the PTF resistors at higher power ratings, see the Load Life Shift Due to Power and Derating table. This table gives a summary of the effects of using the PTF product at the more common combinations of power rating and case size, as well as quantifies the load life stability under those conditions.

TEMPERATURE COEFFICIENT CODES

GLOBAL TC CODE	HISTORICAL TC CODE	TEMPERATURE COEFFICIENT
Z	T-16	5 ppm/ $^{\circ}\text{C}$
Y	T-13	10 ppm/ $^{\circ}\text{C}$
X	T-10	15 ppm/ $^{\circ}\text{C}$

GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: PTF5620K500BYRE (preferred part numbering format)

GLOBAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING	SPECIAL
PTF51 PTF56 PTF65	R = Ω K = k Ω M = M Ω 15R000 = 15 Ω 500K00 = 500 k Ω 1M0000 = 1.0 M Ω	T = ± 0.01 % ⁽¹⁾ Q = ± 0.02 % ⁽¹⁾ A = ± 0.05 % B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1 %	Z = 5 ppm Y = 10 ppm X = 15 ppm 0 = special	EK = lead (Pb)-free, bulk EA = lead (Pb)-free, T/R (full) EB = lead (Pb)-free, T/R (1000 pieces) BF = tin/lead, bulk RE = tin/lead, T/R (full) R6 = tin/lead, T/R (1000 pieces)	Blank = standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable

Historical Part Number example: PTF-5620K5BT-13R36 (will continue to be accepted)

PTF-56	20K5	B	T-13	R36
HISTORICAL MODEL	RESISTANCE VALUE	TOLERANCE CODE	TEMP. COEFFICIENT	PACKAGING

Notes


- For additional information on packaging, refer to the Through-Hole Resistor Packaging document (www.vishay.com/doc?31544).

- (1) Historical tolerance codes were BB for 0.01 % and BC for 0.02 %.

TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	PTF51	PTF56	PTF65
Rated Dissipation at 85 °C	W	0.05	0.125	0.25
Limiting Element Voltage	$V_{\leq}$	200	300	500
Insulation Voltage (1 Min)	V_{eff}	> 500	> 500	> 500
Thermal Resistance	K/W	< 1300	< 520	260
Terminal Strength, Axial	N	> 150	> 50	> 50
Insulation Resistance	Ω	$\geq 10^{11}$	$\geq 10^{11}$	$\geq 10^{11}$
Category Temperature Range	°C	-55 to +150	-55 to +150	-55 to +150
Failure Rate	$10^{-9}/h$	< 1	< 1	< 1
Weight (Max.)	g	0.11	0.35	0.75

DIMENSIONS



GLOBAL MODEL	DIMENSIONS in inches (millimeters)			
	L	D	L _{1 max.}	d
PTF51	0.150 ± 0.020 (3.81 ± 0.51)	0.070 ± 0.010 (1.78 ± 0.25)	0.200 (5.08)	0.016 (0.41)
PTF56	0.250 ± 0.031 (6.35 ± 0.79)	0.091 ± 0.009 (2.31 ± 0.23)	0.300 (7.62)	0.025 (0.64)
PTF65	0.375 ± 0.062 (9.53 ± 1.57)	0.145 ± 0.016 (3.68 ± 0.41)	0.475 (12.07)	0.025 (0.64)

Note

- (1) Lead length for product in bulk pack. For product supplied in tape and reel, the actual lead length would be based on the body size, tape spacing and lead trim.

PERFORMANCE

TEST	CONDITIONS OF TEST	TEST RESULTS (TYPICAL TEST LOTS)
Life (at Standard Power Ratings)	MIL-PRF-55182 Paragraph 4.8.18 1000 h rated power at +85 °C	$\leq \pm 0.04 \%$
Thermal Shock	MIL-STD-202, Method 107 -55 °C to +85 °C	$\leq \pm 0.02 \%$
Short Time Overload	MIL-R-10509, Paragraph 4.7.6	$\leq \pm 0.01 \%$
Low Temperature Operation	MIL-PRF-55182, Methods 4.8.10	$\leq \pm 0.02 \%$
Moisture	MIL-PRF-55182, Paragraph 4.8.15	$\leq \pm 0.08 \%$
Resistance to Soldering Heat	MIL-STD-202, Methods 210	$\leq \pm 0.02 \%$
Damp Heat IEC 60068-2-3	56 days at 40 °C and 92 % RH	$\leq \pm 0.08 \%$
Dielectric Withstanding Voltage	MIL-STD-202, Methods 301 and 105	$\leq \pm 0.01 \%$

MATERIAL SPECIFICATIONS

Element	Precision deposited nickel chrome alloy with controlled annealing
Encapsulation	Specially formulated epoxy compounds. Coated construction
Core	Fire-cleanded high purity ceramic
Termination	Standard lead material is solder-coated copper. Solderable and weldable per MIL-STD-1276, Type C.

MARKING

Temperature coefficient: T10 = 15 ppm, T13 = 10 ppm, T16 = 5 ppm
Tolerance: F = 1 %, D = 0.5 %, C = 0.25 %, B = 0.1 %, A = 0.05 %, BC = 0.02 %, BB = 0.01 %

PTF51: (3 lines)

PTF51 Style and size
37K4 Value
BC T13 Tolerance and TC



PTF56, PTF65: (4 lines)

PTF56 Style and size
49K9 Value
BB T16 Tolerance and TC
1211 4-digit date code

LOAD LIFE SHIFT DUE TO POWER AND DERATING (AT 85 °C)

The power rating for the PTF parts is tied to the derating temperature, the heat rise of the parts, and the ΔR for the load life performance. When the tables/graphs below are used together they show that when the parts are run at higher power ratings, the parts will run hotter, which has the potential of causing the resistance of the parts to shift more over the life of the part.

LOAD LIFE SHIFT VS. POWER RATING					
LOAD LIFE	CONDITIONS OF TEST	MAXIMUM ΔR (TYPICAL TEST LOTS)			
	MIL-PRF-55182 Paragraph 4.8.18 1000 h rated power at +85 °C	$\leq \pm 0.04 \%$	$\leq \pm 0.15 \%$	$\leq \pm 0.5 \%$	$\leq \pm 1.0 \%$
MODEL		POWER RATING AT + 85 °C			
PTF51		1/20 W	1/10 W	1/8 W	1/4 W
PTF56		1/8 W	-	1/4 W	1/2 W
PTF65		1/4 W	-	1/2 W	3/4 W



Example: When a PTF56 part is run at 1/8 W in a 70 °C ambient environment, the resistor will generate enough heat that the surface temperature of the part will reach about 17 °C over the ambient temperature, and over the life of the part this could cause the resistance value to shift up to $\pm 0.04 \%$.

If the same resistor was instead run at 1/4 W in a 70 °C environment, the element will heat up to about 30 °C over ambient, and over the life of the part the resistance value could shift roughly $\pm 0.5 \%$.

And if the resistor was run at its maximum power rating of 1/2 W in a 70 °C environment, it will heat up to about 61 °C over ambient, and you could see the resistance value shift roughly $\pm 1 \%$ over the life of the part.


TEMPERATURE COEFFICIENT OF RESISTANCE

Temperature coefficient (TC) of resistance is normally stated as the maximum amount of resistance change from the original +25 °C value as the ambient temperature increases or decreases. This is most commonly expressed in parts per million per degree centigrade (ppm/°C).

The resistance curve over the operating temperature range is usually a non-linear curve within predictable maximum limits. PTF resistors have a very uniform resistance temperature characteristic when measured over the operating range of -20 °C to +85 °C. The standard temperature coefficients available are

X = ± 15 ppm/°C, Y = ± 10 ppm/°C and Z = ± 5 ppm/°C.

Some applications of the PTF require operation beyond the specifications of -20 °C to +85 °C. The change in temperature coefficient of resistance is very small (less than ± 0.05 ppm/°C) over the expanded temperature range of -55 °C to +150 °C. Therefore, when operating outside the range -20 °C to +85 °C, the designer can plan for a worst case addition of ± 0.05 ppm/°C for each degree centigrade beyond either -20 °C or +85 °C as indicated in the graph. This applies to all three temperature coefficient codes.



Example: Assume the operating characteristics demand a temperature range from -55 °C to +125 °C. This requires a ± 35 °C Δ below -20 °C and a ± 40 °C Δ above +85 °C. The extreme Δ being ± 40 °C means that the worst case addition to the specified TC limit of ± 0.05 ppm/°C times ± 40 °C or ± 2 ppm/°C. Therefore, a Z which is characterized by a base TC limit of ± 5 ppm/°C over the temperature range of -20 °C to +85 °C will exhibit a maximum temperature coefficient of ± 7 ppm/°C over the expanded portion of the temperature range of -55 °C to +125 °C.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

PTF5682K500BXXBF	PTF5649K900BZBF	PTF562K0000BYBF	PTF5675K000BZBF	PTF562K4500BYBF
PTF5640R200AZBF	PTF56250R00AYBF	PTF5618K000BZBF	PTF5618K700BZBF	PTF65200R00FZBF
PTF565K0000QXBF	PTF5612K440BYBF	PTF5610K000AXBF	PTF5615K400BZBF	PTF5615K000BZBF
PTF5614K700BZBF	PTF561K2100BZBF	PTF561K8700BZBF	PTF561K0500BZBF	PTF561K0700BZBF
PTF561K9600BZBF	PTF56200R00AYBF	PTF561K0000BZBF	PTF561K5000BZBF	PTF5620K800BYBF
PTF561K4000BZBF	PTF56250R00BYBF	PTF569K3100BYBF	PTF569K0000BYBF	PTF561K2000BXXBF
PTF569K2000BYBF	PTF561K0000BXXBF	PTF561K0000TZBF	PTF569K4500BYBF	PTF56750R00BZBF
PTF56237K00FZBF	PTF56100R00BZBF	PTF5620K000BYR6	PTF5632K400BYBF	PTF5634K000BYBF
PTF567K9420BYBF	PTF5649K900BYR6	PTF5615K800BYBF	PTF5661K900CXBF	PTF56866R00FZBF
PTF656K8100FZBF	PTF568K0600BYBF	PTF568K0000BYBF	PTF5645K900BYBF	PTF5649R900BYBF
PTF5649K900BYBF	PTF5640K920BYBF	PTF5695K300BZBF	PTF562K4900BZBF	PTF5610K000AYBF
PTF56114K00BYBF	PTF563K2310BYBF	PTF563K3210BYBF	PTF5624K900BZBF	PTF65500K00BZBF
PTF56123K00BYBF	PTF5630K900FZBF	PTF56165K00BYBF	PTF568K2500FZBF	PTF569K7600BZBF
PTF565K0000BYBF	PTF565K0500BYBF	PTF56549R00BZBF	PTF565K6000TXBF	PTF56549R00FZBF
PTF561K8900BZBF	PTF654K7000BXXBF	PTF564K9900BXXBF	PTF564K5900BXXBF	PTF56118K00FYBF
PTF56300K00BZBF	PTF56200K00FZBF	PTF56100R00TXBF	PTF5117R400FYBF	PTF5686K600BZBF
PTF56100R00TZBF	PTF56249K00QZBF	PTF56350R00TZBF	PTF5616K000FZBF	PTF565K9350BYBF
PTF51287R00FXBF	PTF56100R00TYBF	PTF56125K00FZBF	PTF56100K00BYR6	PTF56100R00BYBF
PTF56500R00BYBF	PTF6575K000BXXBF	PTF5686K600BYBF	PTF5686K000BYBF	PTF56169R00FZBF
PTF654K9900BYBF	PTF56191R00FZBF	PTF56182R00DZBF	PTF56160R00FZBF	PTF6530K000AYBF