

NOTES:

① MAT'L: COPPER (STOCK TKN. $\frac{.031}{.79}$)

PLATING: ELECTRO-TIN (.0003 MIN.)

② INSULATION: MOLDED PVC (BLUE)

STUD SIZES: (1,005)

02 - .094

04-119

 0.146


08. = 173

101.

14 = 265

50 - 528

38 = .390



"UI" LISTING # E32244

"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

MWID = MAXIMUM WIRE
INSULATION DIAMETER

WIRE SIZE: 16 - 14 AWG
1.0 - 2.5MM²

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.				AVAILABLE STUD SIZES	
BB-281-	.420 <u>10.67</u>	.235 <u>5.97</u>	.875 <u>22.23</u>				06X, 08X, 10X	
BB-284-	.375 <u>9.53</u>	.235 <u>5.97</u>	.870 <u>22.10</u>				06X, 08X, 10X	
BB-287-	.325 <u>8.26</u>	.235 <u>5.97</u>	.868 <u>22.05</u>				04X, 06X, 08X	
BB-2471-	.245 <u>6.22</u>	.224 <u>5.69</u>	.785 <u>19.94</u>				04X, 06X	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE:	NTS	DATE	TITLE:	EICmolex INCORPORATED	DWG. NO.
FAC. DEC. ANG.			DRWN. BY:	JJ	11-6-84	SPADE TONGUE TERMINAL INSULKRIMP 200 SERIES	A	CUSTOMER DWG.
± ± ±			CHKD. BY:	GZ	11-14-84			
			APPRD. BY:					