

Ultra High Precision Z-Foil Power Current Sensing Resistor with Absolute TCR of $\pm 0.05 \text{ ppm/}^\circ\text{C}$, ESD Immunity up to 25 kV and Tolerance of $\pm 0.02 \%$, Power Rating up to 2 W



INTRODUCTION

Today, designers of analog circuits are demanding discrete power current sense resistors that approach the ideal in performance ... stable, high speed, high accuracy components that will operate with assured, predictable reliability for years in a variety of environments. Foil is meeting those demands with the VCS232Z of unequalled performances.

These four fundamental factors determine how "ideal" a precision power current sense resistor will be:

1. Initial resistance value or how closely the absolute resistance value can be achieved
2. How precisely the value of individual resistors can be controlled
3. How precisely the end of life tolerance is maintained under a wide range of operating conditions and stress factors (temperature, humidity, load, etc.)
4. Fast response without ringing and fast thermal stabilization - and the ability of the resistor to react to rapid switching without adversely affecting the circuit function.

Until the development of Foil resistors, precise control of all four factors was virtually impossible.

Foil VCS232Z resistor containing the latest version of Z-foil achieves maximum stability, a near zero temperature coefficient and the ability to remove errors due to temperature gradients. This superior performance is built-in for every unit and does not rely on culling or other artificial means for uniform excellence.

TABLE 1 - TOLERANCE AND TCR


RESISTANCE RANGE (Ω)	TIGHTEST RESISTANCE TOLERANCE	TYPICAL TCR AND MAX. SPREAD ($\text{ppm/}^\circ\text{C}$) ⁽¹⁾
0.25 to < 10	$\pm 0.05 \%$	$\pm 0.2 \pm 2.8$
10 to 500	$\pm 0.02 \%$	$\pm 0.2 \pm 1.8$

Notes

⁽¹⁾ - -55°C to $+125^\circ\text{C}$, $+25^\circ\text{C}$ ref.

- Contact applications engineering for other available values

FIGURE 1 - POWER DERATING CURVE



* Pb containing terminations are not RoHS compliant, exemptions may apply

FEATURES

- Temperature coefficient of resistance (TCR):
 $\pm 0.05 \text{ ppm/}^\circ\text{C}$ typical (0°C to 60°C)
 $\pm 0.2 \text{ ppm/}^\circ\text{C}$ typical (-55°C to $+125^\circ\text{C}$, $+25^\circ\text{C}$ ref.)
- Power coefficient " ΔR due to self heating":
4 ppm/W typical
- Power rating at $+25^\circ\text{C}$: 2 W (free air)
- Tolerance: to $\pm 0.02 \%$
- Load life stability: to $\pm 0.005 \%$, 25°C for 2000 h at rated power
- Maximum current: 3 A
- Resistance range: 0.25Ω to 500Ω
- Foil resistors are not restricted to standard values; specific "as required" values can be supplied at no extra cost or delivery (e.g. 100.234Ω vs. 100Ω)
- Electrostatic discharge (ESD) up to 25 000 V
- Short time overload $\leq 0.005 \%$
- Non inductive, non capacitive design
- Rise time: 1 ns effectively no ringing
- Thermal stabilization time $< 1 \text{ s}$
- Current noise $< -40 \text{ dB}$
- Thermal EMF: $0.05 \mu\text{V/}^\circ\text{C}$
- Voltage coefficient $< 0.1 \text{ ppm/V}$
- Non inductive: $0.08 \mu\text{H}$
- Non hot spot design
- Terminal finish: lead (Pb)-free or tin/lead alloy
- Compliant to RoHS directive 2002/95/EC
- For better performances please contact us
- Prototype quantities available in just 5 working days or sooner. For more information, please contact foil@vishaypg.com



RoHS*
COMPLIANT

APPLICATIONS

- Automatic test equipment (ATE)
- High precision instrumentation
- Electron beam application
- Medical
- Current sensing applications
- Pulse applications
- Military
- Power amplifier
- Power supplies







FIGURE 2 - TRIMMING TO VALUES

(conceptual illustration)

**FIGURE 3 - TYPICAL RESISTANCE/TEMPERATURE CURVE**

(for more details, see table 1)

**FIGURE 4 - DIMENSIONS** in inches (millimeters)

MODEL	L MAX.	H MAX.	W MAX.	LL MIN.	LS ± 0.20 (± 0.5)	LT ± 0.20 (± 0.5)	D ₁ NOM.	D ₂ NOM.
VCS232Z	1.240 (31.50)	0.512 (13.00)	0.177 (4.50)	0.500 (12.70)	0.688 (17.48)	1.083 (27.51)	0.040 (1.02)	0.032 (0.81)

TABLE 2 - VCS232Z PERFORMANCE SPECIFICATIONS

TEST (Conditions per MIL-PRF-49465)	CONDITIONS	MIL-PRF-49465C ΔR LIMITS	TYPICAL ΔR LIMITS	MAXIMUM ΔR LIMITS
Thermal Shock	- 55 °C to + 125 °C, 5 cycles	± (0.5 % + 0.0005R)	± 0.01 %	± 0.02 %
Short Time Overload	5 x rated power for 5 s	± (0.5 % + 0.0005R)	± 0.005 %	± 0.01 %
Resistance to Soldering Heat	10 s to 12 s at + 260 °C	± (0.25 % + 0.0005R)	± 0.01 %	± 0.02 %
Terminal Strength	Pull test at 5 lb	± (1.0 % + 0.0005R)	± 0.002 %	± 0.005 %
High Temperature Exposure	2000 h, + 150 °C	± (1.0 % + 0.0005R)	± 0.01 %	± 0.02 %
Low Temperature Storage	MIL-PRF-49465, 24 h at - 55 °C	± (0.5 % + 0.0005R)	± 0.002 %	± 0.005 %
Moisture Resistance	MIL-STD-202, method 106, + 65 °C to - 10 °C, 90 % to 98 % RH, rated power, 240 h	± (0.5 % + 0.0005R)	± 0.01 %	± 0.02 %
Shock (Specified Pulse)	100 g, 6 ms	± (0.1 % + 0.0005R)	± 0.01 %	± 0.02 %
Vibration (High Frequency)	(10 Hz to 2000 Hz) 20 g	± (0.1 % + 0.0005R)	± 0.01 %	± 0.02 %
Load Life Stability	2000 h, + 25 °C at rated power	± (1.0 % + 0.0005R)	± 0.005 %	± 0.02 %
Solderability	MIL-STD-202	95 % coverage	-	-


POST MANUFACTURING OPERATIONS OR PMO FOR IMPROVED EOL

Many analog applications can include requirements for performance under conditions of stress beyond the norm and over extended periods of time. This calls for more than just selecting a standard device and applying it to a circuit. The standard device may turn out to be all that is needed but an analysis of the projected service conditions should be made and it may well dictate a routine of stabilization known as post manufacturing operations or PMO. The PMO operations that will be discussed are only applicable to Bulk Metal Foil resistors. They stabilize Bulk Metal Foil resistors while they

may be harmful to other types. Short time overload, accelerated load life, and temperature cycling are the three PMO methods that do the most to remove the anomalies down the road. Bulk Metal Foil resistors are inherently stable as manufactured. These PMO methods are only of value on Bulk Metal Foil resistors and they improve the performance by small but significant amounts. Users are encouraged to contact Foil applications engineering for assistance in choosing the PMO operations that are right for their application.

TABLE 3 - GLOBAL PART NUMBER INFORMATION ⁽¹⁾

NEW GLOBAL PART NUMBER: Y160845R2361Q9L (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y1608 45R2361 Q 9 L:

TYPE: VCS232Z


VALUES: 45.2361 Ω

ABSOLUTE TOLERANCE: $\pm 0.02\%$

TERMINATION: lead (Pb)-free

PACKAGING: bulk pack

HISTORICAL PART NUMBER: VCS232ZT 45R2361 TCR0.2 Q B (will continue to be used)



Note

⁽¹⁾ For non-standard requests, please contact application engineering.

Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase.

To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.