



50T $5.2^{\phi} \times 20$



LOW-BREAKING CAPACITY GLASS TUBE FUSE (TIME-LAG)



50T RoHS I-T CHARACTERISTICS CURVE
50T RoHS



CATALOG NO.	AMPERE RATING	mv MAX VOLTAGE DROP	APPROVALS										REFERENCE (A ² .S) (RoHS)
			CCC	CQC	SMKO	VDE	BSI	IMQ	UR	CSA	PSE	KT	
50T-0100H	100mA	2500	●									0.0946	
50T-0125H	125mA	2000			●		●	●	●		●	0.113	
50T-0160H	160mA	1900	●			●	●	●	●		●	0.126	
50T-0200H	200mA	1500	●			●	●	●	●		●	0.303	
50T-0250H	250mA	1300	●			●	●	●	●		●	0.461	
50T-0315H	315mA	1100	●			●	●	●	●		●	0.673	
50T-0400H	400mA	1000	●			●	●	●	●		●	1.337	
50T-0500H	500mA	900	●			●	●	●	●		●	2.004	
50T-0630H	630mA	300	●			●	●	●	●		●	2.208	
50T-0800H	800mA	250	●			●	●	●	●		●	3.048	
50T-010H	1A	150	●			●	●	●	●	●	●	6.682	
50T-013H	1.25A	150	●			●	●	●	●	●	●	4.571	
50T-016H	1.6A	150	●			●	●	●	●	●	●	9.550	
50T-020H	2A	150	●			●	●	●	●	●	●	19.95	
50T-025H	2.5A	120	●			●	●	●	●	●	●	33.11	
50T-032H	3.15A	100	●			●	●	●	●	●	●	47.86	
50T-040H	4A	100	●			●	●	●	●	●	●	80.54	
50T-050H	5A	100	●			●	●	●	●	●	●	125.3	
50T-063H	6.3A	100	●			●	●	●	●	●	●	237.7	
50T-080H	8A	100	●	●				●	●	●	●	489.9	
50T-100H	10A	100	●	●				●	●	●	●	874.6	
50T-120H	12A	100	●					●	●	●	●	1901	
50T-125H	12.5A	100		●				●	●	●	●	2150	
50T-150H	15A	100	●					●	●	●	●	3042	
50T-160H	16A			●									

H DENOTES FOR 250V

● DENOTES FOR APPROVED

BREAKING CAPACITY:
35A OR 10In WHICHEVER IS GREATER

ELECTRICAL CHARACTERISTICS:

RATING		BLOWING TIME	
		32-100mA	125mA-15A
2.1In	Max	2min	2min
	Min	200ms	600ms
2.75In	Max	10sec	10sec
	Min	40ms	150ms
4In	Max	3sec	3sec
	Min	10ms	20ms
10In	Max	300ms	300ms
	Min		