





EQUIPMENT FEATURES

- Universal use for sanding wood, plastics, metals and stone
- Also suitable for louvre sanding and for sanding varnished surfaces
- Robust gear design for severe applications
- Spindle with dustproof triple bearing
- Sanding plate holder and base body in sturdy aluminium
- High stock removal rate
- Variospeed (V) electronics
- Thumbwheel for speed preselection
- PU-foamed sanding plate enables flexible adjustment to the work-piece surface
- Sanding plate with Velcro
- High suction output
- Ideal handling by slim handle and handy recessed grips
- Low housing
- Rotatable sanding plate without tools (360°)
- External dust extraction outlet



	300 Watt Electronic Triangular Base- Plate Sander DSE 300	300 Watt Electronic Triangular Base- Plate Sander DSE 300 Intec
Special advantages		
■ Dust extraction unit		•
Comparative device characteristics		
Sanding plate, dimension (corner to corner)	93 mm	93 mm
Orbital frequency at no-load	14.000 - 22.000 /min	14.000 - 22.000 /min
Orbital frequency at rated load	18.000 /min	18.000 /min
Rated input power	300 W	300 W
Oscillating circuit	1,8 mm	1,8 mm
Weight (without mains cable)	1,2 kg	1,3 kg
Standard equipment	3 perforated sanding sheets (P 60, P 100, P 240), special louvre base-plate, carry case	3 perforated sanding sheets (P 60, P 100, P 240), carry case
Type	DSE 300	DSE 300 Intec
Order no.	6.00310	6.00311

Grinding plates with Velcro			
			Order no.
	Perforated velcro-faced base-plate for the triangular base-plate sander DS E 300 and DS E 300 Intec (as spare) Dimension from corner to corner: 90 mm		6.24992
	Laminated sanding with velcro on the bottom The self-adhesive velcro-faced liner supplied can be fitted to the top of this base-plate so that cling-fit sanding sheets can be fitted for top and bottom sanding of louvres.		6.24971
	Self-adhesive liner self-adhesive, velcro-faced liner (as spare for lamellar sanding plate 6.24971)		6.24972
Perforated cling-fit sanding sheets, silicone carbide			
	For: Non-ferrous metals, Stone, Glass, Varnished surfaces		
Dimension from corner to corner mm	Grit	Packing unit	Order no.
93	P 120	5	6.24950
93	P 180	5	6.24951
93	P 240	5	6.24952
93	P 320	5	6.24953
93	P 400	5	6.24954
93	P 600	5	6.24955
93	P 1200	5	6.24956

HAMMERS
IMPACT DRILLS
DRILLS
CORDLESS DEVICES
SCREW-DRIVERS
ANGLE GRINDERS
SANDING MACHINES
ROUTERS AND PLANERS
SAWS
SPECIAL MACHINES
HEDGE TRIMMERS
METABOXES