



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	REVISED PER ECR-16-005334	19APR16	RS	EW




- 1 APPLICABLE HDR HSG: 172520(2.5 PITCH)
172890(2.0 PITCH)
- 2 PRODUCT SPEC: 108-5163
- 3 CRIMPING SPEC: 114-5062
COMMON APPLICATOR FOR 2.5mm PITCH
HDR HSG: P/N 755765-□
EXCLUSIVE APPLICATOR FOR 25mm PITCH
HDR HSG: P/N 752830-□

4


TOLERANCES: UNLESS OTHERWISE SHOWN,
DIM <10 mm ±0.20; DIM 10-20 mm ±0.25,
ANGLES ±3 DEGREES



0.95	∅0.8±0.1, 1.2~1.6	—	POST-TINNED PHOS-BRO, 0.2t	172782-9
0.95	∅0.8±0.1, 1.2~1.6	—	POST-TINNED, HIGH HEAT RESISTANCE COPPER ALLOY	1-172782-2
1.2	∅1 ^{+0.05} _{-0.1} , 1.2~1.6	—	POST-TINNED BRASS 0.2t	172782-7
0.95	∅0.8±0.1, 1.2~1.6	—	POST-TINNED BRASS 0.2t	172782-5
1.2	∅1 ^{+0.05} _{-0.1} , 1.2~1.6	172798-2	PRE-TINNED BRASS 0.2t	172782-2
0.95	∅0.8±0.1, 1.2~1.6	172798-1		172782-1
"A" REF	APPLICABLE PCB HOLE AND THK	LOOSE PIECE CONTACT P/N	MATERIAL	PART NO.



SEC A-A



SEC B-B

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [in]

WIRE RANGE
0.14-0.40 mm2
[22-26] AWG

INSULATION DIA
1.4-1.5

MATERIAL
SEE TABLE

FINISH
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

4

DWN
BASVESH WARAD
14JAN2016

CHK
JACONO, GENE
14JAN2016

APVD
JACONO, GENE
14JAN2016

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
0

CUSTOMER DRAWING

TE Connectivity

LOW PROFILE MINI AMP IN CONTACT

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-172782

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 1

REV
G3