








STYLE A



STYLE B



PART NUMBER	SEE DETAIL	"A" +/- .062	"B"	"C"	MARKER ACROSS	TUBING COLOR	SEE STYLE
H200X034F1T	A	2.00 [50.80]	3.50 [88.90]	.75 [19.1]	1	WHITE	A
H100X034F1T	B	1.00 [25.40]		.75 [19.1]	2	WHITE	
H050X034F1T	C	0.50 [12.70]		.75 [19.1]	4	WHITE	
H150X034F1T	A	1.50 [38.10]		1.00 [25.4]	1	WHITE	
H075X034F1T	B	0.75 [19.05]		1.00 [25.4]	2	WHITE	A
H200X034F2T	A	2.00 [50.80]		.75 [19.1]	1	YELLOW	
H100X034F2T	B	1.00 [25.40]		.75 [19.1]	2	YELLOW	
H050X034F2T	C	0.50 [12.70]		.75 [19.1]	4	YELLOW	
H200X034F1T-B	A	2.00 [50.80]		.75 [19.1]	1	WHITE	B
H100X034F1T-B	B	1.00 [25.40]		.75 [19.1]	2	WHITE	
H050X034F1T-B	C	0.50 [12.70]		.75 [19.1]	4	WHITE	
H150X034F1T-B	A	1.50 [38.10]		1.00 [25.4]	1	WHITE	
H075X034F1T-B	B	0.75 [19.05]		1.00 [25.4]	2	WHITE	



NOTE:
1. DIMENSION IN () ARE IN MILLIMETERS.

CAD FILENAME/LAYERS

100923NV_DC_C10220/01F

5	5/21/09	RVU		+/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: .335 +/- .032 WAS .335. MAT'L. HSK TUBING GMHS31, 3.5 WIDE LINER WAS GMHS. ADD "A" +/- .062. ADD STYLE B VIEW FOR BULK BOX. VIEW UPDATE.	5593	R			
4				VOID					
3	12/21/07	RVU		REVISED TUBING MATERIAL. ADDED H150X034F1T-B AND H075X034F1T-B.	5244	R			
2	12/4/07	RVU		(.XX) +/- .032 WAS (.XX) +/- .015.	5219	R			
1	1-31-07	RVU		REVISED VIEW OF BOX, & TOL. ADDE NOTES 1 & 2.	4859	R			
0	2-24-04	RVU		DRAWING RELEASE	0000	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING H***X034F** OPTIMUM
COMPUTER PRINTABLE HEAT SHRINK MARKERS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .020
(.XX) ± .062 ANGLES ±



UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RVU

DATE
9-29-04

CHK'D

MAT'L:
HEATSHRINK
TUBING GMHS31,
3.5 WIDE LINER

SCALE
NTS

DRAWING NO.
C10220

DWG
A
SIZE