



TRG30RA V SERIES

30W SWITCHING ADAPTER



Features

- * Universal Input Range 90~264VAC
 - * Interchangeable AC Plugs
 - * Meets EN61204-3 Class B and CISPR/FCC Class B
 - * Continuous Short Circuit Protection
 - * Over Voltage Protection
 - * Meet CEC & ErP Level V
- (Output Cable Length $\leq$ 1800mm)

Ordering information

TRG30RAXXXV	-	XX	E	XX	-	XX	-BK
Model No.	DC Plug Type		DC Cable Length and Type		Color of Overmold Case		
			01: 720mm		BE: Blue		
			02: 1220mm		GY: Gray		
			03: 1800mm		RD: Red		
			11: 720mm with Ferrite Core		PE: Purple		
			12: 1220mm with Ferrite Core		OR: Orange		
			13: 1800mm with Ferrite Core				
			* 18AWG / UL1185				
			* 16AWG / UL1185 for 5V - 9V				



MODEL	OUTPUT VOLTAGE	OUTPUT CURRENT	RIPPLE & NOISE NOTE 2	VOLTAGE ACCURACY NOTE 1	LINE REGULATION NOTE 3	LOAD REGULATION NOTE 4	% EFF. (Typ.) NOTE 5
TRG30RA050V	5 V	4.0 A	1%	±2%	±1%	±6%	80%
TRG30RA090V	9 V	3.0 A	1%	±2%	±1%	±3%	84%
TRG30RA120V	12 V	2.5 A	1%	±2%	±1%	±2%	84%
TRG30RA150V	15 V	2.0 A	1%	±2%	±1%	±2%	85%
TRG30RA180V	18 V	1.67 A	1%	±2%	±1%	±2%	85%
TRG30RA240V	24 V	1.25 A	1%	±2%	±1%	±2%	86%

Specifications

INPUT SPECIFICATIONS:

Voltage 90~264Vac
 Frequency 47 to 63Hz
 Input Current 100Vac/0.8A max., 240Vac/0.4A max.
 Inrush Current Cold start@25°C 100A max. @240Vac
 Leakage Current 0.25mA max

OUTPUT SPECIFICATIONS:

Hold-up Time 10ms typ. @115Vac
 Short Circuit Protection Hiccup Mode Continuous(Auto Recovery)
 Over Voltage Protection TVS Component to Clamp

GENERAL SPECIFICATIONS:


Isolation Input to output = 3,000VAC(4,242VDC)
 Operating Temperature 0 ~ 60°C(see derating curve)
 Storage Temperature -20~85°C
 Humidity 93% RH max. Non condensing
 Cooling Natural Convection
 Switching Frequency 70KHz Typical
 MTBF MIL-HDBK-217F, GB, 25°C/115VAC 200Khrs min.
 Altitude 2000m
 Dimensions 4.278x2.440x1.445 inches (108.67x61.98x36.70mm)
 Weight 300g(0.66 Pounds)

SAFETY AND EMC:


Emission and Immunity EN61204-3, EN 61000-3-2, EN 61000-3-3
 FCC CFR Title 47 Part 15 Subpart B
 Safety IEC60950-1, UL60950-1, EN60950-1

Mechanical Specification

All Dimensions are in inches(mm)
 Tolerance: Inches: X.XXX±0.02
 Millimeters: X.XX±0.5




TRG30RA-V Series Derating Curve



NOTE:

1. Voltage accuracy is set at 60% load and 25°C Ta.
2. Add a 0.1uF ceramic capacitor and a 10uF E.L. capacitor to output for Ripple & Noise measuring @20MHz BW.
3. Line regulation is measured from 100Vac to 240Vac with full load.
4. Load regulation is measured from 60% to full load and from 60% to 20% load (60% +/- 40% load).
5. Typical efficiency with 230 VAC and max. load at 25°C.
6. "Various TR Series adapters are PSE certified. PSE certification alone is not sufficient for importation into Japan. A valid PSE mark must contain the name of the importer as shown in the example below. If PSE mark is required, the name of the registered importer must be supplied to Cincon on order placement. Product labels will not contain PSE mark if importer name is not supplied. Consult factory or local representative for details"



Typical at 25°C, nominal line and 75% load, unless otherwise Specified

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cincon:

[TRG30RA120V-01E03-GY-BK-Level-V](#)