



NOTES:

1. ALL DIMENSION IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERM. NOS. FOR REF. ONLY
 4. CONTACT RATING SWITCHING: 150mA, 250V AC/DC
350mA, 110V AC/DC
 5. CONTACT RATING (NON-SWITCHING) 5A
 6. CONTACT MATERIAL: SILVER OVER COPPER ALLOY
 7. OPERATING FORCE: 425±100 CM/STANDARD
 8. OPERATING TEMP: -30° to 85°C
 9. CIRCUIT DP: 4 POSITIONS, 30° INDEX.
 10. DIELECTRIC STRENGTH 1000V RMS min.⊗ SEA LEVEL
 11. DESIGNATE MAJOR DIMENSIONS
 12. HARDWARE SUPPLIED ON SWITCH-SEE BELOW
- STOPRING, LOCKWASHER, & HEXNUT





CONTACT CONFIGURATION

Timing: Non-Shorting



TERMINATION DETAIL

SCALE 2X



E-SWITCH®				
TITLE				
KC-24A (10.0mm) 01-N-L-S				
SCALE		DATE	DR	REV
1.5:1		11/19/02	CJB	B

B	12821	REVISED NOTE 12	11/19/02	CJB
A	12579	RELEASED FOR PRODUCTION	11/19/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				